



- Ⓧ DE Montageanleitung
- Ⓧ FR Notice d'instructions
- Ⓧ GB Mounting instructions
- Ⓧ NL Montage instructie
- Ⓧ DK Monteringsvejledning
- Ⓧ FI Asennusohje
- Ⓧ NO Montasjeanvisning
- Ⓧ SE Monteringsinstruktioner
- Ⓧ IT Istruzioni di montaggio
- Ⓧ ES Instrucciones de montaje
- Ⓧ PT Instruções de montagem
- Ⓧ CZ Montážní návod
- Ⓧ BA Uputstvo za montažu
- Ⓧ UK Інструкції з установки

- Ⓧ HR Upute za montažu
- Ⓧ HU Szerelési útmutató
- Ⓧ LT Montavimo instrukcija
- Ⓧ LV Montāžas instrukcija
- Ⓧ PL Instrukcja montażowa
- Ⓧ RO Instrucțiuni de montare
- Ⓧ SK Návod na montáž
- Ⓧ RU Указания по установке **EAC**
- Ⓧ BG Инструкции за монтаж
- Ⓧ GR Οδηγίες χώνευσης
- Ⓧ SI Navodilo za montažo
- Ⓧ EE Paigaldusjuhised
- Ⓧ IS Leiðbeiningar
- Ⓧ AR دليل التركيب

CLE-45

	H	L min	L max
45360	2560	2700	3000
45366	2560	2700	3000
45362	2860	3000	3300
45368	2860	3000	3300
45364	3160	3300	3600
45370	3160	3300	3600

