



6LE001635Ab

h3

x630

3P - 4P

x1	x6 (3P) x8 (4P)	x4 (3P) x6 (4P)
----	--------------------	--------------------

AX	AX	AX-AL
AX	AX	SHT
AL	AL	UVT

M6 x 100

x4

3P - 4P

3P - 4P

	A (mm)
3P	140
4P	185

mm

3P - 4P

PH2 \oplus
6 Nm

mm

3P - 4P

TRIP →

OFF

→

ON

→

TRIP

→

OFF














A

B

Click!


C

D

















HYW011H 3P (400A)
HYW014H 3P (630A)




HYW012H 4P (400A)
HYW015H 4P (630A)



HYD031H 3P (400A)
HYD033H 3P (630A)
HYD032H 4P (400A)
HYD034H 4P (630A)







0 HYW001H 3P
HYW002H 4P

Cu
Al

	min.	max.
	400 A - 630 A	
	35□	300□

	35□ → 95□	120□ → 300□
	L = 28 mm x3 (x4)	L = 21 mm x3 (x4)





0 HYW007H 3P
HYW008H 4P

Cu
Al


	min.	max.
	400 A - 630 A	
	35□	300□

	35□ → 95□	120□ → 300□
	L = 28 mm x6 (x8)	L = 21 mm x6 (x8)




⚡ HYW019H

x3







HYW050H 3P
HYW051H 4P




HYW021H 3P
HYW022H 4P




HYW052H 3P
HYW053H 4P











HYW023H 3P
HYW024H 4P



HYW025H 3P
HYW026H 4P









HXW033H





AX	AX	AX-AL
AX	AX	SHT
AL	AL	UVT



HXA039H

