

## Slotted Trunking HNG-V0



Fig. 1: HNG37037



- certified for application within rolling stocks according to EN 45545-2
- certified according to EN 50085-2-3
- halogen free
- wiring duct dimensions according to DIN 43659
- base holes according to EN 50085
- self-extinguishing according to UL94 V0
- temperature-resistant - 25°C bis + 90°
- UL listed File-Nr.: E48414 (all colors)
- CSA listed File-Nr.: 22009 (all colors)

Base+Cover			
Reference	Height	Width	Length
HNG25025	25 mm	25 mm	2000 mm
HNG37025	37 mm	25 mm	2000 mm
HNG37037	37 mm	37 mm	2000 mm
HNG37050	37 mm	50 mm	2000 mm
HNG50025	50 mm	25 mm	2000 mm
HNG50037	50 mm	37 mm	2000 mm
HNG50050	50 mm	50 mm	2000 mm
HNG50075	50 mm	75 mm	2000 mm
HNG50100	50 mm	100 mm	2000 mm
HNG50125	50 mm	125 mm	2000 mm
HNG75037	75 mm	37 mm	2000 mm
HNG75050	75 mm	50 mm	2000 mm
HNG75075	75 mm	75 mm	2000 mm
HNG75100	75 mm	100 mm	2000 mm
HNG75125	75 mm	125 mm	2000 mm





Fig. 2: HNG75075

Cover		
Reference	Width	Length
HNG0252	25 mm	2000 mm
HNG0372	37 mm	2000 mm
HNG0502	50 mm	2000 mm
HNG0752	75 mm	2000 mm
HNG1002	100 mm	2000 mm
HNG1252	125 mm	2000 mm




Fig. 3: HN500503


Wire Retainer	
Reference	matches to
HN370503	HNG37050
HN500503	HNG50050
HN500753	HNG50075
HN501003	HNG50100
HN501253	HNG50125
HN750373	HNG75037
HN750503	HNG75050
HN750753	HNG75075
HN751003	HNG75100
HN751253	HNG75125




for width 25 mm




for width 37 mm




for width 50 mm




for width 75 mm




for width 100 mm




for width 125mm




for height 25 mm



for height 37 mm



for height 50 mm



for height 75 mm