

## Zählerplatz-Innenausbausträger

Best.-Nr.	P <sub>v</sub> Watt	U <sub>i</sub>	U <sub>imp</sub>
KU9S10HE	-	6 kV	-
KU9S10HZ	-	6 kV	-
KU9S115SBE	-	6 kV	-
KU9S115SBZ	-	6 kV	-
KU9S15ES	-	6 kV	-
KU9S15HE	-	6 kV	-
KU9S15HZ	-	6 kV	-
KU9S80SBE	-	6 kV	-
KU9S80SBZ	-	6 kV	-
ZY20MS	-	6 kV	-
ZY3N1LS	-	6 kV	-
ZY3N1SA	-	6 kV	-
ZY3N1SLS	-	6 kV	-
ZY3N2LS	-	6 kV	-
ZY3N2SA	-	6 kV	-
ZY3N2SLS	-	6 kV	-
ZY3R1SI	-	6 kV	-
ZY3R2SI	-	6 kV	-
ZY5N1LS	-	6 kV	-
ZY5N1SA	-	6 kV	-
ZY5N2LS	-	6 kV	-
ZY5N2SA	-	6 kV	-
ZY5R1SI	-	6 kV	-
ZY5R2SI	-	6 kV	-
ZZ45WAN040	-	6 kV	6 kV
ZZ45WAN100	-	6 kV	6 kV
ZZ45WAN150	-	6 kV	6 kV
ZZ45WAN200	-	6 kV	6 kV
ZZ45WAN500	-	6 kV	6 kV
ZZ45WAN50R	-	6 kV	6 kV

## Elektronische Haushaltszähler eHZ

Best.-Nr.	P <sub>v</sub> Watt	U <sub>i</sub>	U <sub>imp</sub>
EZH363LA	0,35 VA	-	-
EZH363LAR	0,35 VA	-	-
EZH363WA	0,35 VA	-	-
EZH363ZA	0,35 VA	-	-
KU9B43GBE	0,35 VA	6 kV	-
KU9B43GBZ	0,35 VA	6 kV	-
KU9B43GVE	0,35 VA	6 kV	-
KU9B43GVZ	0,35 VA	6 kV	-
KU9S30SVE	0,35 VA	6 kV	-
KU9S30SVZ	0,35 VA	6 kV	-
KU9S40SBE	0,35 VA	6 kV	-
KU9S40SBZ	0,35 VA	6 kV	-
KU9S46GBE	0,35 VA	6 kV	-
KU9S46GBZ	0,35 VA	6 kV	-
KU9S46GVE	0,35 VA	6 kV	-
KU9S46GVZ	0,35 VA	6 kV	-
KU9S80VBE	0,35 VA	6 kV	-
KU9S80VBZ	0,35 VA	6 kV	-

## Kleinverteiler

Best.-Nr.	P <sub>v</sub> Watt	U <sub>i</sub>	U <sub>imp</sub>
KN00A	-	400 V	-

## Sicherungsmaterial

Best.-Nr.	P <sub>v</sub> Watt	U <sub>i</sub>	U <sub>imp</sub>
KB180Q	-	-	4 kV
KB199Q	-	-	4 kV
KB309N	-	-	4500 V
KB380Q	-	-	4 kV
KB399Q	-	-	4 kV
KD199D	1,6 W	-	400 V
L00	4,95 W	8000 V	-
L00C	10,6 W	8 V	-
L00M	4,35 W	8 V	-
L00R	6,51 W	8 V	-
L00T	10,8 W	8 V	-
L00V	4,26 W	8 V	-
L01R	2,06 W	2500 V	-
L063L	4,86 W	800 V	6000 V
L063L1	4,86 W	800 V	6000 V
L063M	4,5 W	500 V	6000 V
L066M	5,6 W	800 V	6000 V
L14	4,5 W	800 V	-
L14D	4,3 W	800 V	-
L17B	4,3 W	800 V	-
L250E	5 W	800 V	-
L25L	1,5 W	800 V	-
L45	2 W	-	-
L501PV	1,1 W	690 V	-
L502PV	2,2 W	690 V	-
L54	2 W	690 V	-
L54D	2 W	690 V	-
L630E	8 W	690 V	-
L63L	4,68 W	690 V	-
L71M	1,8 W	800 V	6000 V
L72M	3,6 W	800 V	6000 V
L73M	5,4 W	800 V	6000 V
L74M	7,2 W	800 V	6000 V
L75M	3 W	800 V	6000 V
L76M	6,6 W	800 V	6000 V
LD01-02AD-1	3 W	800 V	6000 V
LD01-02AD-3	9 W	800 V	6000 V
LD01K16-1AS	3 W	-	-
LD01K16-3AS	9 W	-	-
LD02K63-1KS	9,5 W	-	-
LD02K63-1SS	9,5 W	-	-
LD02K63-3KS	28,5 W	-	-
LD02K63-3SS	28,5 W	-	-
LD042	2,9 W	460 V	6 kV
LD043	9,5 W	-	-
LD046	28,5 W	-	-
LD047	8,7 W	-	-
LE1835	3,9 W	-	-
LF301G	2,77 W	-	-
LF302G	0,6 W	-	-
LF302PV	1,54 W	-	-
LF303PV	1,35 W	-	-
LF304G	0,7 W	-	-
LF304PV	1,84 W	-	-

Best.-Nr.	P <sub>v</sub> Watt	U <sub>i</sub>	U <sub>imp</sub>
LF306G	0,85 W	-	-
LF306PV	2,4 W	-	-
LF308PV	2,55 W	-	-
LF310G	1 W	-	-
LF310PV	2,58 W	-	-
LF312PV	2,6 W	-	-
LF316G	1,6 W	-	-
LF316PV	2,7 W	-	-
LF320G	2 W	-	-
LF320PV	2,9 W	-	-
LF325G	2,6 W	-	-
LF332G	2,9 W	-	-
LF402G	0,9 W	-	-
LF404G	1 W	-	-
LF406G	1,15 W	-	-
LF410G	1,3 W	-	-
LF416G	2 W	-	-
LF420G	2,5 W	-	-
LF425G	3,3 W	-	-
LF432G	3,5 W	-	-
LF440G	4,75 W	-	-
LF516G	2,1 W	-	-
LF520G	2,7 W	-	-
LF525G	3,3 W	-	-
LF532G	3,5 W	-	-
LF540G	4 W	-	-
LF550G	5,5 W	-	-
LF563G	6,9 W	-	-
LF580G	7,8 W	-	-
LF599G	11,4 W	-	-
LL217U	115 W	-	-
LNH000006M6A	0,3 W	-	-
LNH000010M6A	0,5 W	-	-
LNH000016M6A	0,8 W	-	-
LNH000020M6A	1 W	-	-
LNH000025M6A	1,3 W	-	-
LNH000035M6A	1,8 W	-	-
LNH000040M6A	2,1 W	-	-
LNH000050M6A	2,5 W	-	-
LNH000063M6A	3,3 W	-	-
LNH00010M6	1,7 W	-	-
LNH00016M6	2,5 W	-	-
LNH00020M6	2,6 W	-	-
LNH00025M6	2,8 W	-	-
LNH0002M	1,9 W	-	-
LNH00035M6	3,1 W	-	-
LNH0004M	1,5 W	-	-
LNH00050M6	4,1 W	-	-
LNH00050M6A	2,7 W	-	-
LNH00063M6	5,6 W	-	-
LNH00063M6A	3,4 W	-	-
LNH0006M	1,6 W	-	-
LNH0006MK	1,6 W	-	-
LNH00080M6	6,8 W	-	-
LNH00080M6A	4,1 W	-	-
LNH00100M6	7,5 W	-	-
LNH00100M6A	5,5 W	-	-
LNH0010M	1,1 W	-	-
LNH0010MK	1,1 W	-	-
LNH0016M	1,8 W	-	-
LNH0016M6	3,2 W	-	-

Best.-Nr.	P <sub>v</sub> Watt	U <sub>i</sub>	U <sub>imp</sub>
LNH0016M6A	0,9 W	-	-
LNH0016MK	1,8 W	-	-
LNH0020M	2,3 W	-	-
LNH0020M6	3,5 W	-	-
LNH0020M6A	1,1 W	-	-
LNH0020MK	2,3 W	-	-
LNH0025M	2,4 W	-	-
LNH0025M6	3,6 W	-	-
LNH0025M6A	1,4 W	-	-
LNH0025MK	2,4 W	-	-
LNH0032M	3,1 W	-	-
LNH0032MK	3,1 W	-	-
LNH0035M	3 W	-	-
LNH0035M6	3,9 W	-	-
LNH0035M6A	1,9 W	-	-
LNH0035MK	3 W	-	-
LNH0040M	3,7 W	-	-
LNH0040MK	3,7 W	-	-
LNH0050M	4,1 W	-	-
LNH0050M6	4,8 W	-	-
LNH0050M6A	2,7 W	-	-
LNH0050MK	4,1 W	-	-
LNH0063M	5,4 W	-	-
LNH0063M6	6,6 W	-	-
LNH0063M6A	3,4 W	-	-
LNH0063MK	5,4 W	-	-
LNH0080M	6,5 W	-	-
LNH0080M6	8 W	-	-
LNH0080M6A	4,1 W	-	-
LNH0080MK	6,5 W	-	-
LNH00TM	1 W	-	-
LNH0100M	7,5 W	-	-
LNH0100M6	9,4 W	-	-
LNH0100M6A	5,5 W	-	-
LNH0100MK	7,5 W	-	-
LNH010M	1,1 W	-	-
LNH0125M	10 W	-	-
LNH0125M6	11,8 W	-	-
LNH0125M6A	7,9 W	-	-
LNH0125MK	10 W	-	-
LNH0160M	12 W	-	-
LNH0160MK	12 W	-	-
LNH016M	1,8 W	-	-
LNH020M	2,3 W	-	-
LNH025M	2,4 W	-	-
LNH032M	3,1 W	-	-
LNH035M	3 W	-	-
LNH040M	3,7 W	-	-
LNH050M	4,1 W	-	-
LNH063M	6,6 W	-	-
LNH080M	8 W	-	-
LNH0TM	3,5 W	-	-
LNH100M	9,4 W	-	-
LNH1025M	2,4 W	-	-
LNH1025M6	3,6 W	-	-
LNH1025M6A	1,5 W	-	-
LNH1025MK	2,4 W	-	-
LNH1032M	3,1 W	-	-
LNH1032MK	3,1 W	-	-
LNH1035M	3 W	-	-
LNH1035M6	3,9 W	-	-

Best.-Nr.	P <sub>v</sub> Watt	U <sub>i</sub>	U <sub>imp</sub>
LNH1035M6A	2,1 W	-	-
LNH1035MK	3 W	-	-
LNH1040M	3,7 W	-	-
LNH1040MK	3,7 W	-	-
LNH1050M	4,1 W	-	-
LNH1050M6	4,8 W	-	-
LNH1050M6A	3,1 W	-	-
LNH1050MK	4,1 W	-	-
LNH1063M	6,6 W	-	-
LNH1063M6	6,6 W	-	-
LNH1063M6A	4 W	-	-
LNH1063MK	6,6 W	-	-
LNH1080M	8 W	-	-
LNH1080M6	8 W	-	-
LNH1080M6A	5 W	-	-
LNH1080MK	8 W	-	-
LNH1100M	9,4 W	-	-
LNH1100M6	9,4 W	-	-
LNH1100M6A	6,3 W	-	-
LNH1100MK	9,4 W	-	-
LNH1125M	11,8 W	-	-
LNH1125M6	11,8 W	-	-
LNH1125M6A	8 W	-	-
LNH1125MK	11,8 W	-	-
LNH1160M	14,6 W	-	-
LNH1160M6	14,6 W	-	-
LNH1160M6A	10,5 W	-	-
LNH1160MK	14,6 W	-	-
LNH1200M	18 W	-	-
LNH1200M6	19 W	-	-
LNH1200M6A	12,5 W	-	-
LNH1200MK	18 W	-	-
LNH1224M	19 W	-	-
LNH1224M6	21 W	-	-
LNH1224M6A	13,5 W	-	-
LNH1224MK	19 W	-	-
LNH1250M	20 W	-	-
LNH1250M6	22 W	-	-
LNH1250M6A	18 W	-	-
LNH1250MK	20 W	-	-
LNH125M	11,8 W	-	-
LNH160M	14,6 W	-	-
LNH1TM	3,5 W	-	-
LNH20108M4T	9,4 W	-	-
LNH20144M4T	12,2 W	-	-
LNH20180M4T	13,5 W	-	-
LNH20231M4T	18 W	-	-
LNH2025M	2,4 W	-	-
LNH2025MK	2,4 W	-	-
LNH20289M4T	18,6 W	-	-
LNH2032M	3,1 W	-	-
LNH2032MK	3,1 W	-	-
LNH2035M	3 W	-	-
LNH2035MK	3 W	-	-
LNH20361M4T	22,5 W	-	-
LNH2040M	3,7 W	-	-
LNH2040MK	3,7 W	-	-
LNH20455M4T	38,6 W	-	-
LNH2050M	4,1 W	-	-
LNH2050MK	4,1 W	-	-
LNH2063M	6,8 W	-	-

Best.-Nr.	P <sub>v</sub> Watt	U <sub>i</sub>	U <sub>imp</sub>
LNH2063MK	6,8 W	-	-
LNH2080M	8,3 W	-	-
LNH2080M6	8,3 W	-	-
LNH2080M6A	4,7 W	-	-
LNH2080MK	8,3 W	-	-
LNH2100M	10,7 W	-	-
LNH2100M6	10,7 W	-	-
LNH2100M6A	5,9 W	-	-
LNH2100MK	10,7 W	-	-
LNH2125M	12,2 W	-	-
LNH2125M6	12,2 W	-	-
LNH2125M6A	7,9 W	-	-
LNH2125MK	12,2 W	-	-
LNH2160M	15 W	-	-
LNH2160M6	15,5 W	-	-
LNH2160M6A	9,8 W	-	-
LNH2160MK	15 W	-	-
LNH2200M	18,5 W	-	-
LNH2200M6	19 W	-	-
LNH2200M6A	12,5 W	-	-
LNH2200MK	18,5 W	-	-
LNH2224M	19,2 W	-	-
LNH2224M6	21 W	-	-</



Best.-Nr.	P <sub>v</sub> Watt	U <sub>i</sub>	U <sub>imp</sub>
HMT040GR	1,14 W	800 V	8 kV
HMT040JR	1,14 W	800 V	8 kV
HMT040NR	1,14 W	800 V	8 kV
HMT041GR	1,14 W	800 V	8 kV
HMT041JR	1,14 W	800 V	8 kV
HMT041NR	1,14 W	800 V	8 kV
HMT050DR	15 W	800 V	8 kV
HMT051DR	15 W	800 V	8 kV
HMT063DR	13,95 W	800 V	8 kV
HMT064DR	13,95 W	800 V	8 kV
HMT100DR	18 W	800 V	8 kV
HMT100GR	7,2 W	800 V	8 kV
HMT100JR	7,2 W	800 V	8 kV
HMT100NR	7,2 W	800 V	8 kV
HMT101DR	18 W	800 V	8 kV
HMT101GR	7,2 W	800 V	8 kV
HMT101JR	7,2 W	800 V	8 kV
HMT101NR	7,2 W	800 V	8 kV
HMT125DR	27,9 W	800 V	8 kV
HMT126DR	27,9 W	800 V	8 kV
HMT160DR	29,1 W	800 V	8 kV
HMT160GR	18,42 W	800 V	8 kV
HMT160JR	18,42 W	800 V	8 kV
HMT160NR	18,42 W	800 V	8 kV
HMT161DR	29,1 W	800 V	8 kV
HMT161GR	18,42 W	800 V	8 kV
HMT161JR	18,42 W	800 V	8 kV
HMT161NR	18,42 W	800 V	8 kV
HMT200DR	36 W	800 V	8 kV
HMT201DR	36 W	800 V	8 kV
HMT250DR	50,7 W	800 V	8 kV
HMT250GR	45 W	800 V	8 kV
HMT250JR	45 W	800 V	8 kV
HMT250NR	45 W	800 V	8 kV
HMT251DR	50,7 W	800 V	8 kV
HMT251GR	45 W	800 V	8 kV
HMT251JR	45 W	800 V	8 kV
HMT251NR	45 W	800 V	8 kV
HMW250JR	36,8 W	800 V	8 kV
HMW250NR	36,8 W	800 V	8 kV
HMW251JR	36,8 W	800 V	8 kV
HMW251NR	36,8 W	800 V	8 kV
HMW400JR	90 W	800 V	8 kV
HMW400NR	90 W	800 V	8 kV
HMW401JR	90 W	800 V	8 kV
HMW401NR	90 W	800 V	8 kV
HMW630JR	190,5 W	800 V	8 kV
HMW630NR	190,5 W	800 V	8 kV
HMW631JR	190,5 W	800 V	8 kV
HMW631NR	190,5 W	800 V	8 kV
HNE800H	153,6 W	800 V	8 kV
HNE801H	153,6 W	800 V	8 kV
HNE970H	186 W	800 V	8 kV
HNE971H	186 W	800 V	8 kV
HNF980H	187,5 W	800 V	8 kV
HNF981H	187,5 W	800 V	8 kV
HNF990H	168,9 W	800 V	8 kV
HNF991H	168,9 W	800 V	8 kV
HNJ250DR	71,4 W	800 V	8 kV
HNJ250GR	36,8 W	800 V	8 kV
HNJ251DR	71,4 W	800 V	8 kV

Best.-Nr.	P <sub>v</sub> Watt	U <sub>i</sub>	U <sub>imp</sub>
HNJ251GR	36,8 W	800 V	8 kV
HNJ320DR	75 W	800 V	8 kV
HNJ321DR	75 W	800 V	8 kV
HNJ400DR	116 W	800 V	8 kV
HNJ400GR	90 W	800 V	8 kV
HNJ401DR	116 W	800 V	8 kV
HNJ401GR	90 W	800 V	8 kV
HNJ630DE	176,3 W	800 V	8 kV
HNJ630GR	190,5 W	800 V	8 kV
HNJ631DE	176,3 W	800 V	8 kV
HNJ631GR	190,5 W	800 V	8 kV
HNS025DC	19,5 W	800 V	8 kV
HNS026DC	19,5 W	800 V	8 kV
HNS040DC	27,9 W	800 V	8 kV
HNS040GC	1,68 W	800 V	8 kV
HNS040JC	1,68 W	800 V	8 kV
HNS040NC	1,68 W	800 V	8 kV
HNS041DC	27,9 W	800 V	8 kV
HNS041GC	1,68 W	800 V	8 kV
HNS041JC	1,68 W	800 V	8 kV
HNS041NC	1,68 W	800 V	8 kV
HNS063DC	10,5 W	800 V	8 kV
HNS064DC	10,5 W	800 V	8 kV
HNS080DC	17,7 W	800 V	8 kV
HNS081DC	17,7 W	800 V	8 kV
HNS100DC	20,1 W	800 V	8 kV
HNS100GC	10,5 W	800 V	8 kV
HNS100JC	10,5 W	800 V	8 kV
HNS100NC	10,5 W	800 V	8 kV
HNS101DC	20,1 W	800 V	8 kV
HNS101GC	10,5 W	800 V	8 kV
HNS101JC	10,5 W	800 V	8 kV
HNS101NC	10,5 W	800 V	8 kV
HNS125DC	32,1 W	800 V	8 kV
HNS126DC	32,1 W	800 V	8 kV
HNS160DC	42,3 W	800 V	8 kV
HNS160GC	27 W	800 V	8 kV
HNS160JC	27 W	800 V	8 kV
HNS160NC	27 W	800 V	8 kV
HNS161DC	42,3 W	800 V	8 kV
HNS161GC	27 W	800 V	8 kV
HNS161JC	27 W	800 V	8 kV
HNS161NC	27 W	800 V	8 kV
HNT040GR	1,14 W	800 V	8 kV
HNT040JR	1,14 W	800 V	8 kV
HNT040NR	1,14 W	800 V	8 kV
HNT041GR	1,14 W	800 V	8 kV
HNT041JR	1,14 W	800 V	8 kV
HNT041NR	1,14 W	800 V	8 kV
HNT050DR	15 W	800 V	8 kV
HNT051DR	15 W	800 V	8 kV
HNT063DR	13,95 W	800 V	8 kV
HNT064DR	13,95 W	800 V	8 kV
HNT100DR	18 W	800 V	8 kV
HNT100GR	7,2 W	800 V	8 kV
HNT100JR	7,2 W	800 V	8 kV
HNT100NR	7,2 W	800 V	8 kV
HNT101DR	18 W	800 V	8 kV
HNT101GR	7,2 W	800 V	8 kV
HNT101JR	7,2 W	800 V	8 kV
HNT101NR	7,2 W	800 V	8 kV

Best.-Nr.	P <sub>v</sub> Watt	U <sub>i</sub>	U <sub>imp</sub>
HNT125DR	27,9 W	800 V	8 kV
HNT126DR	27,9 W	800 V	8 kV
HNT160DR	29,1 W	800 V	8 kV
HNT160GR	18,42 W	800 V	8 kV
HNT160JR	18,42 W	800 V	8 kV
HNT160NR	18,42 W	800 V	8 kV
HNT161DR	29,1 W	800 V	8 kV
HNT161GR	18,42 W	800 V	8 kV
HNT161JR	18,42 W	800 V	8 kV
HNT161NR	18,42 W	800 V	8 kV
HNT200DR	36 W	800 V	8 kV
HNT201DR	36 W	800 V	8 kV
HNT250DR	50,7 W	800 V	8 kV
HNT250GR	45 W	800 V	8 kV
HNT250JR	45 W	800 V	8 kV
HNT250NR	45 W	800 V	8 kV
HNT251DR	50,7 W	800 V	8 kV
HNT251GR	45 W	800 V	8 kV
HNT251JR	45 W	800 V	8 kV
HNT251NR	45 W	800 V	8 kV
HNW250JR	36,8 W	800 V	8 kV
HNW250NR	36,8 W	800 V	8 kV
HNW251JR	36,8 W	800 V	8 kV
HNW251NR	36,8 W	800 V	8 kV
HNW400JR	90 W	800 V	8 kV
HNW400NR	90 W	800 V	8 kV
HNW401JR	90 W	800 V	8 kV
HNW401NR	90 W	800 V	8 kV
HNW630JR	190,5 W	800 V	8 kV
HNW630NR	190,5 W	800 V	8 kV
HNW631JR	190,5 W	800 V	8 kV
HNW631NR	190,5 W	800 V	8 kV
HPW250JR	36,8 W	800 V	8 kV
HPW250NR	36,8 W	800 V	8 kV
HPW251JR	36,8 W	800 V	8 kV
HPW251NR	36,8 W	800 V	8 kV
HPW400JR	90 W	800 V	8 kV
HPW400NR	90 W	800 V	8 kV
HPW401JR	90 W	800 V	8 kV
HPW401NR	90 W	800 V	8 kV
HPW630JR	190,5 W	800 V	8 kV
HPW630NR	190,5 W	800 V	8 kV
HPW631JR	190,5 W	800 V	8 kV
HPW631NR	190,5 W	800 V	8 kV
HW1E306DB	190,5 W	1000 V	12 kV
HW1E306FB	190,5 W	1000 V	12 kV
HW1E308DB	190,5 W	1000 V	12 kV
HW1E308FB	190,5 W	1000 V	12 kV
HW1E310DB	190,5 W	1000 V	12 kV
HW1E310FB	190,5 W	1000 V	12 kV
HW1E312DB	190,5 W	1000 V	12 kV
HW1E312FB	190,5 W	1000 V	12 kV
HW1E316DB	190,5 W	1000 V	12 kV
HW1E316FB	190,5 W	1000 V	12 kV
HW1E406DB	190,5 W	1000 V	12 kV
HW1E406FB	190,5 W	1000 V	12 kV
HW1E408DB	190,5 W	1000 V	12 kV
HW1E408FB	190,5 W	1000 V	12 kV
HW1E410DB	190,5 W	1000 V	12 kV
HW1E410FB	190,5 W	1000 V	12 kV
HW1E412DB	190,5 W	1000 V	12 kV

Best.-Nr.	P <sub>v</sub> Watt	U <sub>i</sub>	U <sub>imp</sub>
HW1E412FB	190,5 W	1000 V	12 kV
HW1E416DB	190,5 W	1000 V	12 kV
HW1E416FB	190,5 W	1000 V	12 kV
HW1M306DB	190,5 W	1000 V	12 kV
HW1M306FB	190,5 W	1000 V	12 kV
HW1M308DB	190,5 W	1000 V	12 kV
HW1M308FB	190,5 W	1000 V	12 kV
HW1M310DB	190,5 W	1000 V	12 kV
HW1M310FB	190,5 W	1000 V	12 kV
HW1M312DB	190,5 W	1000 V	12 kV
HW1M312FB	190,5 W	1000 V	12 kV
HW1M316DB	190,5 W	1000 V	12 kV
HW1M316FB	190,5 W	1000 V	12 kV
HW1M406DB	190,5 W	1000 V	12 kV
HW1M406FB	190,5 W	1000 V	12 kV
HW1M408DB	190,5 W	1000 V	12 kV
HW1M408FB	190,5 W	1000 V	12 kV
HW1M410DB	190,5 W	1000 V	12 kV
HW1M410FB	190,5 W	1000 V	12 kV
HW1M412DB	190,5 W	1000 V	12 kV
HW1M412FB	190,5 W	1000 V	12 kV
HW1M416DB	190,5 W	1000 V	12 kV
HW1M416FB	190,5 W	1000 V	12 kV
HW1N306DB	190,5 W	1000 V	12 kV
HW1N306FB	190,5 W	1000 V	12 kV
HW1N308DB	190,5 W	1000 V	12 kV
HW1N308FB	190,5 W	1000 V	12 kV
HW1N310DB	190,5 W	1000 V	12 kV
HW1N310FB	190,5 W	1000 V	12 kV
HW1N312DB	190,5 W	1000 V	12 kV
HW1N312FB	190,5 W	1000 V	12 kV
HW1N316DB	190,5 W	1000 V	12 kV
HW1N316FB	190,5 W	1000 V	12 kV
HW1N406DB	190,5 W	1000 V	12 kV
HW1N406FB	190,5 W	1000 V	12 kV
HW1N408DB	190,5 W	1000 V	12 kV
HW1N408FB	190,5 W	1000 V	12 kV
HW1N410DB	190,5 W	1000 V	12 kV
HW1N410FB	190,5 W	1000 V	12 kV
HW1N412DB	190,5 W	1000 V	12 kV
HW1N412FB	190,5 W	1000 V	12 kV
HW1N416DB	190,5 W	1000 V	12 kV
HW1N416FB	190,5 W	1000 V	12 kV
HW1W304DS	190,5 W	1000 V	12 kV
HW1W304FS	190,5 W	1000 V	12 kV
HW1W306DS	190,5 W	1000 V	12 kV
HW1W306FS	190,5 W	1000 V	12 kV
HW1W308DS	190,5 W	1000 V	12 kV
HW1W308FS	190,5 W	1000 V	12 kV
HW1W310DS	190,5 W	1000 V	12 kV
HW1W310FS	190,5 W	1000 V	12 kV
HW1W312DS	190,5 W	1000 V	12 kV
HW1W312FS	190,5 W	1000 V	12 kV
HW1W316DS	190,5 W	1000 V	12 kV
HW1W316FS	190,5 W	1000 V	12 kV
HW1W404DS	190,5 W	1000 V	12 kV
HW1W404FS	190,5 W	1000 V	12 kV
HW1W406DS	190,5 W	1000 V	12 kV
HW1W406FS	190,5 W	1000 V	12 kV
HW1W408DS	190,5 W	1000 V	12 kV
HW1W408FS	190,5 W	1000 V	12 kV

Best.-Nr.	P <sub>v</sub> Watt	U <sub>i</sub>	U <sub>imp</sub>
HW1W410DS	190,5 W	1000 V	12 kV
HW1W410FS	190,5 W	1000 V	12 kV
HW1W412DS	190,5 W	1000 V	12 kV
HW1W412FS	190,5 W	1000 V	12 kV
HW1W416DS	190,5 W	1000 V	12 kV
HW1W416FS	190,5 W	1000 V	12 kV
HXE040H	24 W	1000 V	12 kV
HXE042H	24 W	1000 V	12 kV
HXF040H	24 W	1000 V	12 kV
HXF042H	24 W	1000 V	12 kV
HYW001H	211,2 W	1000 V	12 kV
HYW002H	211,2 W	1000 V	12 kV
HYW007H	321,49 W	1000 V	12 kV
HYW008H	321,49 W	1000 V	12 kV
HYW010H	12,6 W	1000 V	12 kV
HYW011H	13,8 W	1000 V	12 kV
HYW012H	13,8 W	1000 V	12 kV
HYW013H	16,7 W	1000 V	12 kV
HYW014H	19 W	1000 V	12 kV
HYW015H	19 W	1000 V	12 kV
SB432PV	19 W	1000 V	12 kV

## Selektive Hauptleitungsschutzschalter

Best.-Nr.	P <sub>v</sub> Watt	U <sub>i</sub>	U <sub>imp</sub>
-----------	------------------------	----------------	------------------



Best.-Nr.	P <sub>v</sub> Watt	U <sub>i</sub>	U <sub>imp</sub>
HTS332C	-	690 V	-
HTS332E	-	690 V	-
HTS335C	-	690 V	-
HTS335E	-	690 V	-
HTS340C	-	690 V	-
HTS340E	-	690 V	-
HTS350C	-	690 V	-
HTS350E	-	690 V	-
HTS363C	-	690 V	-
HTS363E	-	690 V	-
HTS380C	-	690 V	-
HTS380E	-	690 V	-
HTS390C	-	690 V	-
HTS390E	-	690 V	-
HTS635E	-	690 V	-
HTS640E	-	690 V	-
HTS650E	-	690 V	-
HTS663E	-	690 V	-
HTU325E	-	690 V	-
HTU335E	-	690 V	-
HTU340E	-	690 V	-
HTU350E	-	690 V	-
HTU363E	-	690 V	-

## Leitungsschutzschalter

Best.-Nr.	P <sub>v</sub> Watt	U <sub>i</sub>	U <sub>imp</sub>
BDH280E	7,5 W	500 V	6000 V
BDH380E	11,25 W	500 V	6000 V
BDH480E	15 W	500 V	6000 V
BTH280E	7,5 W	500 V	6000 V
BTH380E	11,25 W	500 V	6000 V
BTH480E	15 W	500 V	6000 V
HMC180	6,18 W	500 V	6000 V
HMC190	6,48 W	500 V	6000 V
HMC199	9,93 W	500 V	6000 V
HMC280	11,98 W	500 V	6000 V
HMC290	16,33 W	500 V	6000 V
HMC299	21 W	500 V	6000 V
HMC380	20,32 W	500 V	6000 V
HMC390	21,66 W	500 V	6000 V
HMC399	34,93 W	500 V	6000 V
HMC480	25,71 W	500 V	6000 V
HMC490	28,1 W	500 V	6000 V
HMC499	42,25 W	500 V	6000 V
HMD180	6,18 W	500 V	6000 V
HMD190	6,48 W	500 V	6000 V
HMD199	9,93 W	500 V	6000 V
HMD280	11,98 W	500 V	6000 V
HMD290	16,33 W	500 V	6000 V
HMD299	21 W	500 V	6000 V
HMD380	20,32 W	500 V	6000 V
HMD390	21,66 W	500 V	6000 V
HMD399	34,93 W	500 V	6000 V
HMD480	25,71 W	500 V	6000 V
HMD490	28,1 W	500 V	6000 V
HMD499	42,25 W	500 V	6000 V
KB163A	42,25 W	500 V	4500 V
KB163N	42,25 W	500 V	4 kV

Best.-Nr.	P <sub>v</sub> Watt	U <sub>i</sub>	U <sub>imp</sub>
KB163P	42,25 W	500 V	4 kV
KC125	0,2 W	500 V	4 kV
KC150	0,3 W	500 V	4 kV
KC325	0,6 W	500 V	4 kV
KC350	0,9 W	500 V	4 kV
KCL363L	0,9 W	500 V	4 kV
KCL363R	0,9 W	500 V	4 kV
KCL368L	0,9 W	500 V	4 kV
KCL368R	0,9 W	500 V	4 kV
MB197	1,87 W	500 V	6000 V
MB199	1,33 W	500 V	6000 V
MBN106	1,3 W	500 V	4000 V
MBN110	2,75 W	500 V	4000 V
MBN113	2,2 W	500 V	4000 V
MBN116	2,44 W	500 V	4000 V
MBN120	2,79 W	500 V	4000 V
MBN125	3 W	500 V	4000 V
MBN132	4,4 W	500 V	4000 V
MBN140	4,8 W	500 V	4000 V
MBN150	5,2 W	500 V	4000 V
MBN163	7,4 W	500 V	4000 V
MBN206	2,5 W	500 V	4000 V
MBN210	3,8 W	500 V	4000 V
MBN213	4,6 W	500 V	4000 V
MBN216	4,2 W	500 V	4000 V
MBN220	5,6 W	500 V	4000 V
MBN225	6 W	500 V	4000 V
MBN232	9 W	500 V	4000 V
MBN240	10,5 W	500 V	4000 V
MBN250	9,2 W	500 V	4000 V
MBN263	11,4 W	500 V	4000 V
MBN306	3,8 W	500 V	4000 V
MBN310	5,8 W	500 V	4000 V
MBN313	6,7 W	500 V	4000 V
MBN316	6,33 W	500 V	4000 V
MBN320	8,9 W	500 V	4000 V
MBN325	10,1 W	500 V	4000 V
MBN332	13 W	500 V	4000 V
MBN340	16,9 W	500 V	4000 V
MBN350	16,3 W	500 V	4000 V
MBN363	18,3 W	500 V	4000 V
MBN406	5 W	500 V	4000 V
MBN410	7,8 W	500 V	4000 V
MBN413	9,1 W	500 V	4000 V
MBN416	10,8 W	500 V	4000 V
MBN420	11,7 W	500 V	4000 V
MBN425	13,4 W	500 V	4000 V
MBN432	17,6 W	500 V	4000 V
MBN440	22,4 W	500 V	4000 V
MBN450	19,8 W	500 V	4000 V
MBN463	25,6 W	500 V	4000 V
MBN506	2,5 W	500 V	4000 V
MBN510	3,8 W	500 V	4000 V
MBN513	-	500 V	4000 V
MBN516	4,2 W	500 V	4000 V
MBN520	5,6 W	500 V	4000 V
MBN525	6 W	500 V	4000 V
MBN532	9 W	500 V	4000 V
MBN540	10,5 W	500 V	4000 V
MBN550	9,2 W	500 V	4000 V
MBN563	11,4 W	500 V	4000 V

Best.-Nr.	P <sub>v</sub> Watt	U <sub>i</sub>	U <sub>imp</sub>
MBN606	3,8 W	500 V	4000 V
MBN610	5,8 W	500 V	4000 V
MBN613	6,7 W	500 V	4000 V
MBN616	8,2 W	500 V	4000 V
MBN620	8,9 W	500 V	4000 V
MBN625	10,1 W	500 V	4000 V
MBN632	13 W	500 V	4000 V
MBN640	16,9 W	500 V	4000 V
MBN650	16,3 W	500 V	4000 V
MBN663	18,3 W	500 V	4000 V
MBS106	1,3 W	500 V	4000 V
MBS110	2,75 W	500 V	4000 V
MBS113	2,2 W	500 V	4000 V
MBS116	2,44 W	500 V	4000 V
MBS120	2,79 W	500 V	4000 V
MBS125	3 W	500 V	4000 V
MBS132	4,4 W	500 V	4000 V
MBS140	4,8 W	500 V	4000 V
MBS150	5,2 W	500 V	4000 V
MBS163	7,4 W	500 V	4000 V
MBS306	3,8 W	500 V	4000 V
MBS310	5,8 W	500 V	4000 V
MBS313	6,7 W	500 V	4000 V
MBS316	6,33 W	500 V	4000 V
MBS320	8,9 W	500 V	4000 V
MBS325	10,1 W	500 V	4000 V
MBS332	13 W	500 V	4000 V
MBS340	16,9 W	500 V	4000 V
MBS350	16,3 W	500 V	4000 V
MBS363	18,3 W	500 V	4000 V
MCN100	0,1 W	500 V	4000 V
MCN101	0,1 W	500 V	4000 V
MCN102	1,3 W	500 V	4000 V
MCN103	1,9 W	500 V	4000 V
MCN104	1,9 W	500 V	4000 V
MCN106	1,3 W	500 V	4000 V
MCN110	1,63 W	500 V	4000 V
MCN113	2,29 W	500 V	4000 V
MCN116	2,32 W	500 V	4000 V
MCN120	2,7 W	500 V	4000 V
MCN125	3 W	500 V	4000 V
MCN132	4,4 W	500 V	4000 V
MCN140	4,8 W	500 V	4000 V
MCN150	5,2 W	500 V	4000 V
MCN163	7,4 W	500 V	4000 V
MCN200	2,2 W	500 V	4000 V
MCN201	2,8 W	500 V	4000 V
MCN202	2,7 W	500 V	4000 V
MCN203	4 W	500 V	4000 V
MCN204	3,8 W	500 V	4000 V
MCN206	2,5 W	500 V	4000 V
MCN210	3,11 W	500 V	4000 V
MCN213	4,6 W	500 V	4000 V
MCN216	5,2 W	500 V	4000 V
MCN220	5,6 W	500 V	4000 V
MCN225	6 W	500 V	4000 V
MCN232	9 W	500 V	4000 V
MCN240	10,5 W	500 V	4000 V
MCN250	9,2 W	500 V	4000 V
MCN263	11,4 W	500 V	4000 V
MCN300	3,4 W	500 V	4000 V

Best.-Nr.	P <sub>v</sub> Watt	U <sub>i</sub>	U <sub>imp</sub>
MCN301	4,3 W	500 V	4000 V
MCN302	4,1 W	500 V	4000 V
MCN303	6 W	500 V	4000 V
MCN304	5,7 W	500 V	4000 V
MCN306	3,8 W	500 V	4000 V
MCN310	4,58 W	500 V	4000 V
MCN313	6,27 W	500 V	4000 V
MCN316	6,99 W	500 V	4000 V
MCN320	8,9 W	500 V	4000 V
MCN325	10,1 W	500 V	4000 V
MCN332	13 W	500 V	4000 V
MCN340	16,9 W	500 V	4000 V
MCN350	16,3 W	500 V	4000 V
MCN363	18,3 W	500 V	4000 V
MCN400	4,5 W	500 V	4000 V
MCN401	5,7 W	500 V	4000 V
MCN402	5,4 W	500 V	4000 V
MCN403	8 W	500 V	4000 V
MCN404	7,7 W	500 V	4000 V
MCN406	5 W	500 V	4000 V
MCN410	7,8 W	500 V	4000 V
MCN413	9,1 W	500 V	4000 V
MCN416	10,8 W	500 V	4000 V
MCN420	11,7 W	500 V	4000 V
MCN425	13,4 W	500 V	4000 V
MCN432	17,6 W	500 V	4000 V
MCN440	22,4 W	500 V	4000 V
MCN450	19,8 W	500 V	4000 V
MCN463	25,6 W	500 V	4000 V
MCN500	2,2 W	500 V	4000 V
MCN501	2,8 W	500 V	4000 V
MCN502	2,7 W	500 V	4000 V
MCN503	4 W	500 V	4000 V
MCN504	3,8 W	500 V	4000 V
MCN506	2,5 W	500 V	4000 V
MCN510	3,8 W	500 V	4000 V
MCN513	4,18 W	500 V	4000 V
MCN516	4,41 W	500 V	4000 V
MCN520	5,6 W	500 V	4000 V
MCN525	6 W	500 V	4000 V
MCN532	9 W	500 V	4000 V
MCN540	10,5 W	500 V	4000 V
MCN550	9,2 W	500 V	4000 V
MCN563	11,4 W	500 V	4000 V
MCN600	3,4 W	500 V	4000 V
MCN601	4,3 W	500 V	4000 V
MCN602	4,1 W	500 V	4000 V
MCN603	6 W	500 V	4000 V
MCN604	5,7 W	500 V	4000 V
MCN606	3,8 W	500 V	4000 V
MCN610	5,8 W	500 V	4000 V
MCN613	6,7 W	500 V	4000 V
MCN616	8,2 W	500 V	4000 V
MCN620	8,9 W	500 V	4000 V
MCN625	10,1 W	500 V	4000 V
MCN632	13 W	500 V	4000 V
MCN640	16,9 W	500 V	4000 V
MCN650	16,3 W	500 V	4000 V
MCN663	18,3 W	500 V	4000 V
MCS106	1,3 W	500 V	4000 V
MCS110	1,63 W	500 V	4000 V

Best.-Nr.	P <sub>v</sub> Watt	U <sub>i</sub>	U <sub>imp</sub>
MCS113	2,29 W	500 V	4000 V
MCS116	2,32 W	500 V	4000 V
MCS120	2,7 W	500 V	4000 V
MCS125	3 W	500 V	4000 V
MCS132	4,4 W	500 V	4000 V
MCS140	4,8 W	500 V	4000 V
MCS150	5,2 W	500 V	4000 V
MCS163	7,4 W	500 V	4000 V
MCS306	3,8 W	500 V	4000 V
MCS310	4,58 W	500 V	4000 V
MCS313	6,27 W	500 V	4000 V
MCS316	6,99 W	500 V	4000 V
MCS320	8,9 W	500 V	4000 V
MCS325	10,1 W	500 V	4000 V
MCS332	13 W	500 V	4000 V
MCS340	16,9 W	500 V	4000 V
MCS350	16,3 W	500 V	4000 V
MCS363	18,3 W	500 V	4000 V
MZ201	0,1 W	4000 V	-
MZ202	0,2 W	4000 V	-
MZ203	25,3 W	4000 V	-
MZ204	24,3 W	4000 V	-
MZ205	2 W	4000 V	-
MZ206	2 W	4000 V	-
NBN106	1,33 W	500 V	6000 V
NBN110	1,87 W	500 V	6000 V
NBN113	2,31 W	500 V	6000 V
NBN116	2,62 W	500 V	6000 V
NBN120	2,56 W	500 V	6000 V
NBN125	3,37 W	500 V	6000 V
NBN132	3,65 W	500 V	6000 V
NBN140	3,71 W	500 V	6000 V
NBN150	4,7 W	500 V	6000 V
NBN163	5,73 W	500 V	6000 V
NBN206	2,68 W	500 V	6000 V
NBN210	4,13 W	500 V	6000 V
NBN213			

Best.-Nr.	P <sub>v</sub> Watt	U <sub>i</sub>	U <sub>imp</sub>
NCN316	8,27 W	500 V	6000 V
NCN320	8,04 W	500 V	6000 V
NCN325	11 W	500 V	6000 V
NCN332	12,3 W	500 V	6000 V
NCN340	10,1 W	500 V	6000 V
NCN350	15,4 W	500 V	6000 V
NCN363	19,9 W	500 V	6000 V
NCN400	5,72 W	500 V	6000 V
NCN401	4,24 W	500 V	6000 V
NCN402	8,63 W	500 V	6000 V
NCN403	8,86 W	500 V	6000 V
NCN404	10,9 W	500 V	6000 V
NCN406	5,44 W	500 V	6000 V
NCN410	8,29 W	500 V	6000 V
NCN413	8,9 W	500 V	6000 V
NCN416	11,08 W	500 V	6000 V
NCN420	10,87 W	500 V	6000 V
NCN425	14,75 W	500 V	6000 V
NCN432	16,5 W	500 V	6000 V
NCN440	15 W	500 V	6000 V
NCN450	20,3 W	500 V	6000 V
NCN463	25,7 W	500 V	6000 V
NCN506	2,68 W	500 V	6000 V
NCN510	4,13 W	500 V	6000 V
NCN513	4,58 W	500 V	6000 V
NCN516	5,34 W	500 V	6000 V
NCN520	5,29 W	500 V	6000 V
NCN525	7,2 W	500 V	6000 V
NCN532	8 W	500 V	6000 V
NCN540	6,7 W	500 V	6000 V
NCN550	10,6 W	500 V	6000 V
NCN563	13,1 W	500 V	6000 V
NCN606	5,44 W	500 V	6000 V
NCN610	8,29 W	500 V	6000 V
NCN613	8,9 W	500 V	6000 V
NCN616	11,08 W	500 V	6000 V
NCN620	10,87 W	500 V	6000 V
NCN625	14,75 W	500 V	6000 V
NCN632	16,5 W	500 V	6000 V
NCN640	15 W	500 V	6000 V
NCN650	20,3 W	500 V	6000 V
NCN663	25,7 W	500 V	6000 V
NDN100	0,14 W	500 V	6000 V
NDN101	0,13 W	500 V	6000 V
NDN102	1,89 W	500 V	6000 V
NDN103	2,24 W	500 V	6000 V
NDN104	2,62 W	500 V	6000 V
NDN106	1,33 W	500 V	6000 V
NDN110	1,87 W	500 V	6000 V
NDN113	2,31 W	500 V	6000 V
NDN116	2,62 W	500 V	6000 V
NDN120	2,56 W	500 V	6000 V
NDN125	3,37 W	500 V	6000 V
NDN132	3,65 W	500 V	6000 V
NDN140	3,71 W	500 V	6000 V
NDN150	4,7 W	500 V	6000 V
NDN163	5,73 W	500 V	6000 V
NDN200	2,91 W	500 V	6000 V
NDN201	2,11 W	500 V	6000 V
NDN202	4,1 W	500 V	6000 V
NDN203	4,41 W	500 V	6000 V

Best.-Nr.	P <sub>v</sub> Watt	U <sub>i</sub>	U <sub>imp</sub>
NDN204	5,36 W	500 V	6000 V
NDN206	2,68 W	500 V	6000 V
NDN210	4,13 W	500 V	6000 V
NDN213	4,58 W	500 V	6000 V
NDN216	5,34 W	500 V	6000 V
NDN220	5,29 W	500 V	6000 V
NDN225	7,2 W	500 V	6000 V
NDN232	8 W	500 V	6000 V
NDN240	6,7 W	500 V	6000 V
NDN250	10,6 W	500 V	6000 V
NDN263	13,1 W	500 V	6000 V
NDN300	4,35 W	500 V	6000 V
NDN301	3,24 W	500 V	6000 V
NDN302	6,16 W	500 V	6000 V
NDN303	6,6 W	500 V	6000 V
NDN304	8,18 W	500 V	6000 V
NDN306	4,06 W	500 V	6000 V
NDN310	6,13 W	500 V	6000 V
NDN313	6,37 W	500 V	6000 V
NDN316	8,27 W	500 V	6000 V
NDN320	8,04 W	500 V	6000 V
NDN325	11 W	500 V	6000 V
NDN332	12,3 W	500 V	6000 V
NDN340	10,1 W	500 V	6000 V
NDN350	15,4 W	500 V	6000 V
NDN363	19,9 W	500 V	6000 V
NDN400	5,72 W	500 V	6000 V
NDN401	4,24 W	500 V	6000 V
NDN402	8,63 W	500 V	6000 V
NDN403	8,86 W	500 V	6000 V
NDN404	10,9 W	500 V	6000 V
NDN406	5,44 W	500 V	6000 V
NDN410	8,29 W	500 V	6000 V
NDN413	8,9 W	500 V	6000 V
NDN416	11,08 W	500 V	6000 V
NDN420	10,87 W	500 V	6000 V
NDN425	14,75 W	500 V	6000 V
NDN432	16,5 W	500 V	6000 V
NDN440	15 W	500 V	6000 V
NDN450	20,3 W	500 V	6000 V
NDN463	25,7 W	500 V	6000 V
NQN306	4,06 W	500 V	6000 V
NQN310	6,13 W	500 V	6000 V

## Fehlerstrom-/ Leitungsschutzschalter

Best.-Nr.	P <sub>v</sub> Watt	U <sub>i</sub>	U <sub>imp</sub>
ACA516D	-	500 V	4000 V
ACA566D	-	500 V	4000 V
ACS916D	-	500 V	4000 V
ACS966D	4,74 W	500 V	4000 V
ACS967D	-	500 V	4000 V
ADA506D	1,9 W	500 V	4000 V
ADA510D	3,4 W	500 V	4000 V
ADA513D	3,8 W	500 V	4000 V
ADA516D	5,2 W	500 V	4000 V
ADA520D	6,6 W	500 V	4000 V
ADA525D	9,3 W	500 V	4000 V
ADA532D	8,3 W	500 V	4000 V

Best.-Nr.	P <sub>v</sub> Watt	U <sub>i</sub>	U <sub>imp</sub>
ADA556D	1,9 W	500 V	4000 V
ADA560D	3,4 W	500 V	4000 V
ADA563D	3,8 W	500 V	4000 V
ADA566D	5,2 W	500 V	4000 V
ADA570D	6,6 W	500 V	4000 V
ADA575D	9,3 W	500 V	4000 V
ADA582D	8,3 W	500 V	4000 V
ADH463QC	10,1 W	500 V	4 kV
ADH466QC	10,9 W	500 V	4 kV
ADH906QC	3,8 W	500 V	4000 V
ADH910QC	3,8 W	500 V	4000 V
ADH913QC	3,8 W	500 V	4000 V
ADH916QC	5,2 W	500 V	4000 V
ADH920QC	3,8 W	500 V	4000 V
ADM406QC	6,8 W	500 V	4 kV
ADM410QC	9,7 W	500 V	4 kV
ADM413QC	10,1 W	500 V	4 kV
ADM416QC	10,9 W	500 V	4 kV
ADM420QC	11,7 W	500 V	4 kV
ADM456QC	6,8 W	500 V	4 kV
ADM460QC	9,7 W	500 V	4 kV
ADM463QC	10,1 W	500 V	4 kV
ADM466QC	10,9 W	500 V	4 kV
ADM470QC	11,7 W	500 V	4 kV
ADR406C	6,8 W	500 V	4 kV
ADR410C	9,7 W	500 V	4 kV
ADR413C	10,1 W	500 V	4 kV
ADR416C	10,9 W	500 V	4 kV
ADR420C	11,7 W	500 V	4 kV
ADR425C	12,3 W	500 V	4 kV
ADR432C	14,6 W	500 V	4 kV
ADR440C	17,7 W	500 V	4 kV
ADR456C	6,8 W	500 V	4 kV
ADR460C	9,7 W	500 V	4 kV
ADR463C	10,1 W	500 V	4 kV
ADR466C	10,9 W	500 V	4 kV
ADR470C	11,7 W	500 V	4 kV
ADR475C	12,3 W	500 V	4 kV
ADR482C	14,6 W	500 V	4 kV
ADR490C	17,7 W	500 V	4 kV
ADS906D	1,9 W	500 V	4000 V
ADS910D	3,4 W	500 V	4000 V
ADS913D	3,8 W	500 V	4000 V
ADS916D	5,2 W	500 V	4000 V
ADS917D	5,2 W	500 V	4000 V
ADS920D	6,6 W	500 V	4000 V
ADS925D	9,3 W	500 V	4000 V
ADS932D	8,3 W	500 V	4000 V
ADS940D	11,1 W	500 V	4000 V
ADS956D	1,9 W	500 V	4000 V
ADS960D	3,4 W	500 V	4000 V
ADS963D	3,8 W	500 V	4000 V
ADS966D	5,2 W	500 V	4000 V
ADS967D	5,2 W	500 V	4000 V
ADS970D	6,6 W	500 V	4000 V
ADS975D	9,3 W	500 V	4000 V
ADS982D	8,3 W	500 V	4000 V
ADS990D	11,1 W	500 V	4000 V
ADX406D	6,8 W	500 V	4 kV
ADX410D	9,7 W	500 V	4 kV
ADX413D	10,1 W	500 V	4 kV

Best.-Nr.	P <sub>v</sub> Watt	U <sub>i</sub>	U <sub>imp</sub>
ADX416D	10,9 W	500 V	4 kV
ADX420D	11,7 W	500 V	4 kV
ADX425D	12,3 W	500 V	4 kV
ADX432D	14,6 W	500 V	4 kV
ADX440D	17,7 W	500 V	4 kV
ADX456D	6,8 W	500 V	4 kV
ADX460D	9,7 W	500 V	4 kV
ADX463D	10,1 W	500 V	4 kV
ADX466D	10,9 W	500 V	4 kV
ADX470D	11,7 W	500 V	4 kV
ADX475D	12,3 W	500 V	4 kV
ADX482D	14,6 W	500 V	4 kV
ADX490D	17,7 W	500 V	4 kV
ADZ310D	7,7 W	500 V	4000 V
ADZ313D	9,6 W	500 V	4000 V
ADZ316D	10,9 W	500 V	4000 V
ADZ360D	7,7 W	500 V	4000 V
ADZ363D	9,6 W	500 V	4000 V
ADZ366D	10,9 W	500 V	4000 V
AFR406C	6,8 W	500 V	4 kV
AFR410C	9,7 W	500 V	4 kV
AFR416C	10,9 W	500 V	4 kV
AFR420C	11,7 W	500 V	4 kV
AFR425C	12,3 W	500 V	4 kV
AFR432C	14,6 W	500 V	4 kV
AFR440C	17,7 W	500 V	4 kV
AFR456C	6,8 W	500 V	4 kV
AFR460C	9,7 W	500 V	4 kV
AFR463C	10,1 W	500 V	4 kV
AFR466C	10,9 W	500 V	4 kV
AFR470C	11,7 W	500 V	4 kV
AFR475C	12,3 W	500 V	4 kV
AFR482C	14,6 W	500 V	4 kV
AFR490C	17,7 W	500 V	4 kV
AFX406D	6,8 W	500 V	4 kV
AFX410D	9,7 W	500 V	4 kV
AFX413D	10,1 W	500 V	4 kV
AFX416D	10,9 W	500 V	4 kV
AFX420D	11,7 W	500 V	4 kV
AFX425D	12,3 W	500 V	4 kV
AFX432D	14,6 W	500 V	4 kV
AFX440D	17,7 W	500 V	4 kV
AFX456D	6,8 W	500 V	4 kV
AFX460D	9,7 W	500 V	4 kV
AFX463D	10,1 W	500 V	4 kV
AFX466D	10,9 W	500 V	4 kV
AFX470D	11,7 W	500 V	4 kV
AFX475D	12,3 W	500 V	4 kV
AFX482D	14,6 W	500 V	4 kV
AFX490D	17,7 W	500 V	4 kV
KC125	0,2 W	500 V	4 kV
KC150	0,3 W	500 V	4 kV
KC325	0,6 W	500 V	4 kV
KC350	0,9 W	500 V	4 kV
KCF563L	0,9 W	500 V	4 kV
KCF563R	0,9 W	500 V	4 kV
KCF663S	0,9 W	500 V	4 kV
KCF668S	0,9 W	500 V	4 kV
KCF863L	0,9 W	500 V	4 kV
KCF863R	0,9 W	500 V	4 kV
KCF963L	0,9 W	500 V	4 kV

Best.-Nr.	P <sub>v</sub> Watt	U <sub>i</sub>	U <sub>imp</sub>
KCF963R	0,9 W	500 V	4 kV
MZ201	0,1 W	4000 V	-
MZ202	0,2 W	4000 V	-
MZ203	25,3 W	4000 V	-
MZ204	24,3 W	4000 V	-
MZ205	2 W	4000 V	-
MZ206	2 W	4000 V	-

## Fehlerstromschutzschalter

Best.-Nr.	P <sub>v</sub> Watt	U <sub>i</sub>	U <sub>imp</sub>
CCA216D	2,4 W	500 V	4000 V
CCA225D	7,1 W	500 V	4000 V
CDA216D	0,95 W	500 V	4000 V
CDA225D	2,32 W	500 V	4000 V
CDA240D	6,24 W	500 V	4000 V
CDA263D	8,1 W	500 V	4000 V
CDA425D	4,5 W	500 V	4000 V
CDA440D	6,5 W	500 V	4000 V
CDA441D	6,5 W	500 V	4000 V
CDA463D	18,5 W	500 V	4000 V
CDA516D	0,51 W	500 V	4000 V
CDA525D	1,77 W	500 V	4000 V
CDA540D	3,31 W	500 V	4000 V
CDA563D	6,64 W	500 V	4000 V
CDA625D	1,98 W	500 V	4000 V
CDA640D	4,39 W	500 V	4000 V
CDA663D	9,29 W	500 V	4000 V
CDA680D	15,8 W	500 V	4000 V
CDA684D	21,48 W	500 V	4000 V
CD525D	1,77 W	500 V	4000 V
CD540D	3,31 W	500 V	4000 V

Best.-Nr.	P <sub>v</sub> Watt	U <sub>i</sub>	U <sub>imp</sub>
ARC570D	5,2 W	500 V	-
ARC575D	6,48 W	500 V	-
ARC906D	2,16 W	500 V	4 kV
ARC910D	2,65 W	500 V	4 kV
ARC913D	4,24 W	500 V	4 kV
ARC916D	5,22 W	500 V	4 kV
ARC920D	5,2 W	500 V	4 kV
ARC925D	6,48 W	500 V	4 kV
ARC956D	2,16 W	500 V	4 kV
ARC960D	2,65 W	500 V	4 kV
ARC963D	4,24 W	500 V	4 kV
ARC966D	5,22 W	500 V	4 kV
ARC970D	5,2 W	500 V	4 kV
ARC975D	6,48 W	500 V	4 kV
ARF506D	2,2 W	500 V	4000 V
ARF510D	3,18 W	500 V	4000 V
ARF513D	4,88 W	500 V	4000 V
ARF516D	5,76 W	500 V	4000 V
ARF520D	6,08 W	500 V	4000 V
ARF525D	7,95 W	500 V	4000 V
ARF556D	2,2 W	500 V	4000 V
ARF560D	3,18 W	500 V	4000 V
ARF563D	4,88 W	500 V	4000 V
ARF566D	5,76 W	500 V	4000 V
ARF570D	6,08 W	500 V	4000 V
ARF575D	7,95 W	500 V	4000 V
ARF906D	2,2 W	500 V	4000 V
ARF910D	3,18 W	500 V	4000 V
ARF913D	4,88 W	500 V	4000 V
ARF916D	5,76 W	500 V	4000 V
ARF920D	6,08 W	500 V	4000 V
ARF956D	2,2 W	500 V	4000 V
ARF960D	3,18 W	500 V	4000 V
ARF963D	4,88 W	500 V	4000 V
ARF966D	5,76 W	500 V	4000 V
ARF970D	6,08 W	500 V	4000 V

## Schalt- und Meldegeräte

Best.-Nr.	P <sub>v</sub> Watt	U <sub>i</sub>	U <sub>imp</sub>
EE960	1 W	-	-
EN145	2 W	250 V	-
EN146	2 W	250 V	-
EP400	1,2 W	-	-
EP411	1,2 W	250 V	-
EPN050	0,1 W	-	-
EPN051	0,1 W	250 V	-
EPN052	0,1 W	-	-
EPN053	0,1 W	-	-
EPN501	1,2 W	250 V	-
EPN503	1,2 W	250 V	-
EPN510	1,2 W	250 V	-
EPN511	1,2 W	250 V	-
EPN512	1,2 W	250 V	-
EPN513	1,2 W	250 V	-
EPN515	1,2 W	250 V	-
EPN518	1,2 W	250 V	-
EPN519	1,2 W	250 V	-
EPN520	2,4 W	250 V	-

Best.-Nr.	P <sub>v</sub> Watt	U <sub>i</sub>	U <sub>imp</sub>
EPN521	2,4 W	250 V	-
EPN522	2,4 W	250 V	-
EPN524	2,4 W	250 V	-
EPN525	2,4 W	400 V	-
EPN526	2,4 W	250 V	-
EPN528	2,4 W	400 V	-
EPN540	4,8 W	400 V	-
EPN541	4,8 W	400 V	-
EPN546	3,6 W	400 V	-
EPN548	4,8 W	400 V	-
EPS410B	1,2 W	-	-
EPS450B	1,2 W	-	-
ERC216	4,9 W	250 V	4 kV
ERC218	3,9 W	250 V	4 kV
ERC418	5,4 W	440 V	4 kV
ERD216	4,9 W	250 V	4 kV
ERD218	3,9 W	250 V	4 kV
ERD418	5,4 W	440 V	4 kV
ERL216	4,9 W	250 V	4 kV
ERL218	3,9 W	250 V	4 kV
ERL418	5,4 W	440 V	4 kV
ESC080	0,1 W	240 V	4 kV
ESC125	4,4 W	250 V	4 kV
ESC225	5,9 W	250 V	4 kV
ESC225S	5,2 W	250 V	4 kV
ESC226	2,9 W	250 V	4 kV
ESC227	4,4 W	250 V	4 kV
ESC240S	10,9 W	440 V	4 kV
ESC263S	14,5 W	440 V	4 kV
ESC325	7,9 W	440 V	4 kV
ESC325S	7,3 W	440 V	4 kV
ESC340	15,35 W	440 V	4 kV
ESC340S	14,1 W	440 V	4 kV
ESC425	9,4 W	440 V	4 kV
ESC425S	8,8 W	440 V	4 kV
ESC426	3,4 W	440 V	4 kV
ESC426S	2,8 W	440 V	4 kV
ESC427	6,4 W	250 V	4 kV
ESC428	7,9 W	440 V	4 kV
ESC428S	7,3 W	440 V	4 kV
ESC440	18,55 W	440 V	4 kV
ESC440S	17,3 W	440 V	4 kV
ESC441	18,55 W	440 V	4 kV
ESC443	18,55 W	440 V	4 kV
ESC463	25,75 W	440 V	4 kV
ESC463S	24,5 W	440 V	4 kV
ESC464	25,75 W	440 V	4 kV
ESD225	5,9 W	250 V	4 kV
ESD425	9,4 W	440 V	4 kV
ESD440	15 W	440 V	4 kV
ESD463	22,2 W	440 V	4 kV
ESL225	5,9 W	250 V	4 kV
ETC225S	5,2 W	250 V	4 kV
KB163A	5,2 W	250 V	4500 V
KB163N	5,2 W	250 V	4 kV
KB163P	5,2 W	250 V	4 kV
SBM216	0,8 W	440 V	4000 V
SBM225	1,8 W	440 V	4000 V
SBN116	0,4 W	440 V	4000 V
SBN125	0,9 W	440 V	4000 V
SBN140	1,1 W	440 V	6000 V

Best.-Nr.	P <sub>v</sub> Watt	U <sub>i</sub>	U <sub>imp</sub>
SBN163	2,3 W	440 V	6000 V
SBN216	0,8 W	440 V	4000 V
SBN225	1,8 W	440 V	4000 V
SBN240	2,2 W	440 V	6000 V
SBN263	4,6 W	440 V	6000 V
SBN280	5,4 W	440 V	6000 V
SBN290	11 W	440 V	6000 V
SBN316	1,2 W	440 V	4000 V
SBN325	2,7 W	440 V	4000 V
SBN340	3,3 W	440 V	6000 V
SBN363	6,9 W	440 V	6000 V
SBN380	8,1 W	440 V	6000 V
SBN390	16,5 W	440 V	6000 V
SBN416	1,6 W	440 V	4000 V
SBN425	3,6 W	440 V	4000 V
SBN440	4,4 W	440 V	6000 V
SBN463	9,2 W	440 V	6000 V
SBN480	1,8 W	440 V	6000 V
SBN490	22 W	440 V	6000 V
SBT116	0,4 W	440 V	4000 V
SBT125	0,9 W	440 V	4000 V
SFB116	0,4 W	440 V	4000 V
SFB125	0,9 W	440 V	4000 V
SFB216	0,8 W	440 V	4000 V
SFB225	1,8 W	440 V	4000 V
SFL116	0,4 W	440 V	4000 V
SFL125	0,9 W	440 V	4000 V
SFL225	1,8 W	440 V	4000 V
SFM125	0,9 W	440 V	4000 V
SH363K	7,8 W	-	4000 V
SH363N	7,8 W	-	4000 V
SH363S	7,8 W	-	4000 V
SH463B	7,8 W	-	4000 V
SH463N	7,8 W	-	4000 V
ST301	1,8 W	4000 V	4000 V
ST303	2,2 W	4000 V	4000 V
ST303N	7 W	4000 V	4000 V
ST305	1,8 W	4000 V	4000 V
ST309	2 W	4000 V	4000 V
ST310	2 W	4000 V	4000 V
ST312	1,8 W	4000 V	4000 V
ST313	1,5 W	4000 V	4000 V
ST314	2,1 W	4000 V	4000 V
ST315	4,5 W	4000 V	4000 V
ST320	2,07 W	4000 V	4000 V
SVN121	0,8 W	250 V	4000 V
SVN122	0,8 W	250 V	4000 V
SVN123	0,8 W	250 V	4000 V
SVN124	0,8 W	250 V	4000 V
SVN125	0,8 W	250 V	4000 V
SVN126	0,8 W	250 V	4000 V
SVN127	0,8 W	250 V	4000 V
SVN131	0,33 W	250 V	2000 V
SVN132	0,33 W	250 V	2000 V
SVN133	0,33 W	250 V	2000 V
SVN134	0,33 W	250 V	2000 V
SVN135	0,33 W	250 V	2000 V
SVN311	-	250 V	4000 V
SVN312	-	250 V	4000 V
SVN321	-	250 V	4000 V
SVN322	-	250 V	4000 V

Best.-Nr.	P <sub>v</sub> Watt	U <sub>i</sub>	U <sub>imp</sub>
SVN331	-	250 V	4000 V
SVN332	-	250 V	4000 V
SVN341	-	250 V	4000 V
SVN342	-	250 V	4000 V
SVN351	-	250 V	4000 V
SVN352	-	250 V	4000 V
SVN371	-	250 V	4000 V
SVN391	-	250 V	4000 V
SVN411	0,8 W	250 V	4000 V
SVN413	0,8 W	250 V	4000 V
SVN422	0,8 W	250 V	4000 V
SVN432	0,8 W	250 V	4000 V
SVN433	0,8 W	250 V	4000 V
SVN441	0,8 W	250 V	4000 V
SVN452	0,8 W	250 V	4000 V
SVN461	0,8 W	250 V	4000 V
SVN462	0,8 W	250 V	4000 V
SVN463	0,8 W	250 V	4000 V
SVN464	0,8 W	250 V	4000 V

## Zähler und Messgeräte

Best.-Nr.	P <sub>v</sub> Watt	U <sub>i</sub>	U <sub>imp</sub>
EC100	1,5 W	-	-
ECA180D	1 W	-	-
ECA180T	1 W	-	-
ECA300C	0,6 W	-	-
ECA310D	0,6 W	-	-
ECA380D	0,6 W	-	-
ECM140D	1 W	-	-
ECM180D	1 W	-	-
ECM180T	1 W	-	-
ECM300C	0,6 W	-	-
ECM310D	0,6 W	-	-
ECM380D	0,6 W	-	-
ECN140D	1 W	-	-
ECP140D	1 W	-	-
ECP180D	1 W	-	-
ECP180T	1 W	-	-
ECP300C	0,6 W	-	-
ECP310D	0,6 W	-	-
ECP380D	0,6 W	-	-
ECR140D	1 W	-	-
ECR180D	1 W	-	-
ECR180T	1 W	-	-
ECR300C	0,6 W	-	-
ECR310D	0,6 W	-	-
ECR380D	0,6 W	-	-
EU100	4 W	-	-
EU101	4 W	-	-
EU102	4 W	-	-
EU103	4 W	-	-
EU300	4 W	-	-
EU301	4 W	-	-
EU302	4 W	-	-
SK600	0,7 W	690 V	-
SK602	1 W	690 V	-
SK603	1 W	690 V	-
SK606	1 W	440 V	-

Best.-Nr.	P <sub>v</sub> Watt	U <sub>i</sub>	U <sub>imp</sub>
SM005	1,1 W	2000 V	-
SM015	1,1 W	2000 V	-
SM020	1 W	-	-
SM030	1,1 W	2000 V	-
SM050	1,1 W	2000 V	-
SM100	1,1 W	2000 V	-
SM101C	5 W	-	-
SM101E	5 W	-	-
SM102E	10 W	4 kV	-
SM103E	10 W	4 kV	-
SM150	1,1 W	2000 V	-
SM151	1 W	-	-
SM200	-	4 kV	-
SM201	-	4 kV	-
SM202	-	4 kV	-
SM203	-	4 kV	-
SM204	-	4 kV	-
SM205	-	4 kV	-
SM210	-	4 kV	-
SM211	-	4 kV	-
SM213	-	4 kV	-
SM214	-	4 kV	-
SM250	1,1 W	2000 V	-
SM400	1,1 W	2000 V	-
SM401	1 W	-	-
SM500	3,5 W	2000 V	-
SM501	3,5 W	-	-
SM600	1,1 W	2000 V	-
SM601	1,1 W	-	-
SRA00505	0,5 W	3 kV	-
SRA00605	0,5 W	3 kV	-
SRA00755	0,8 W	3 kV	-
SRA01005	0,7 W	3 kV	-
SRA01255	1,6 W	3 kV	-
SRA01505	1 W	3 kV	-
SRA02005	2,2 W	3 kV	-
SRA02505	2,6 W	3 kV	-
SRB00605	1 W	3 kV	-
SRB00755	1,2 W	3 kV	-
SRC04005	3,6 W	3 kV	-
SRC06005	5,5 W	3 kV	-
SRD08005	6 W	3 kV	-
SRD10005	8 W	3 kV	-
SRD15005	13,5 W	3 kV	-
SRE10005	11 W	3 kV	-
SRE12505	11 W	3 kV	-
SRE16005	14 W	3 kV	-
SRE20005	17,5 W	3 kV	-
SRF12505	7 W	3 kV	-
SRF16005	11 W	3 kV	-
SRF20005	14 W	3 kV	-
SRF25005	14 W	3 kV	-
SRG30005	16 W	3 kV	-
SRG40005	22 W	3 kV	-
SRH30005	23 W	3 kV	-
SRH40005	30 W	3 kV	-
SRI03005	3 W	3 kV	-
SRI04005	4 W	3 kV	-
SRI06005	4,2 W	3 kV	-
SRJ06005			