

Senzori pokreta i prisustva Vodič za narudžbe



:hager

Vanjski senzori pokreta

		Klasični bijeli		Klasični antracit		Komfort bijela		Komfort antracit	LED bijela (140° detekcija)	
									Lumen	
Ugao detekcije	140°	EE820	–	EE821	–	EE850	–	–	700	EE631
	200°	EE830	–	EE831	–	–	–	–	1200	EE632
	220°	–	–	–	–	–	EE860	EE861	2000	EE633
	360°	–	EE840	–	EE841	–	EE870	EE871	3000	EE634
Zaštita		IP55	IP55	IP55	IP55	IP55	IP55	IP55	IP55	
Vrsta kontakta		ON/OFF	ON/OFF	ON/OFF	ON/OFF	Bezpotenc.	Bezpotenc.	Bezpotenc.	ON/OFF	
Montaža		Zidni / Nadgradni	Zidni / Nadgradni	Zidni / Nadgradni	Zidni / Nadgradni	Zidni / Nadgradni	Zidni / Nadgradni	Zidni / Nadgradni	Zidni / Nadgradni	
Vertikalno podesiv		–	Da	–	Da	–	Da	Da	–	
Horizontalno podesiv		Da	–	Da	–	Da	–	Da	Da	
Visina montaže / Domet detekcije		2,5 m / Ø 16 m	2,5 m / Ø 12 m	2,5 m / Ø 16 m	2,5 m / Ø 12 m	2,5 m / Ø 16 m	2,5 m / Ø 16 m	2,5 m / Ø 16 m	2,5 m / 12 x 8 m	
Maks. domet na jednoj strani		8 m	6 m	8 m	6 m	10 m	10 m	10 m	4 m je Seite	
Jačina svjetlosti, podesiva		5 – 1000 Lux	5 – 1000 Lux	5 – 1000 Lux	5 – 1000 Lux	5 – 1000 Lux	5 – 1000 Lux	5 – 1000 Lux	10 – 1000 Lux	
Odlaganje, podesivo		5 s – 15 min	5 s – 15 min	5 s – 15 min	5 s – 15 min	5 s – 30 min	5 s – 30 min	5 s – 30 min	30 s – 15 min	
quickconnect		Da	–	Da	–	–	–	–	–	
Maks. visina montaže		4 m	2,5 m	4 m	2,5 m	4 m	4 m	4 m	LED boja	
Maks. frontalni domet		16 m	12 m	16 m	12 m	16 m	16 m	16 m	4000 K	
Odziv, podesivi		–	–	–	–	Da	Da	Da	Snaga	
Paralelni rad		Da	Da	Da	Da	Da	Da	Da	8 W	EE631
Radna temperatura		-20 – 55°C	-20 – 55°C	-20 – 55°C	-20 – 55°C	-20 – 55°C	-20 – 55°C	-20 – 55°C	12 W	EE632
Žarulje sa žarnom niti, halogene 230V		1500 W	1500 W	1500 W	1500 W	2300 W	2300 W	2300 W	20 W	EE633
LED / kompaktne fluorescentne sijalice		10 x 20 W	10 x 20 W	10 x 20 W	10 x 20 W	20 x 20 W	20 x 20 W	20 x 20 W	30 W	EE634
Fluorescentne sijalice (ballast)		290 W	400 W	290 W	400 W	400 W	400 W	400 W	Dimenzije (DxŠxV)	
Elektronski ballast		580 W	580 W	580 W	580 W	580 W	580 W	580 W	140 x 100 x 127 mm	EE631 EE632
Dimenzije (DxŠxV)		127 x 83 x 97 mm	153 x 91 x 134 mm	127 x 83 x 97 mm	153 x 91 x 134 mm	153 x 91 x 134 mm	153 x 91 x 134 mm	153 x 91 x 134 mm	140 x 164 x 127 mm	EE633
Dodaci		–	–	–	–	EE806	EE806	EE806	140 x 226 x 156 mm	EE634



Hager d.o.o

Igmanska bb
71320 Vogošća - Sarajevo, Bosna i Hercegovina
Tel.: +387 33 424 295, 297
Fax: +387 33 424 296
hagerbih@bih.net.ba
hager.ba

Zastupništvo Srbija

Tel/Fax: +381 11 4027 205
zlatan.rajic@hager.com
office.rs@hager.com
hager.rs

Predstavništvo Hrvatska

Mob.: +385 95 807 8466
+387 61 890 016
fikret.seferagic@hager.com
hager.hr

Predstavništvo Crna Gora

Mob.: +387 61 147 112
almir.colakovic@hager.com

Predstavništvo Kosovo i Albanija

Mob.: +387 61 812 886
avdo.niksic@hager.com
hager-ks.com
hager.al