

Interface Relay

Catalogue number:
EN145

Specifications:

Electrical

Control Coil

- Voltage rating - 12-24 V(DC)
- 12-24 V(AC/50Hz)
- Power consumption - 2VA

Output Contact

- Voltage rating - 240 V(AC)(50Hz)
- Current rating - 5A (AC1)

Mechanical

Operating temperature - 10 to 50°C

Connection capacity:

- flexible conductor - 4mm² max
- rigid conductor - 6mm² max

