



Primary Boards

	Dimensions (mm)		
	Height	Width	Depth
JF406B/G	1250	900	220
JF408B/G	1250	900	220
JF412B/G	1400	900	220
JF416B/G	1550	900	220
JF418B/G	1700	900	220
JF808B/G	1250	900	220
JF812B/G	1400	900	220
JF818B/G	1700	900	220
JF60204B/G	1250	900	220
JF80206B/G	1250	900	220
JF80404B/G	1250	900	220
JF80210B/G	1400	900	220
JF80408B/G	1400	900	220
JF80414B/G	1700	900	220
JF80612B/G	1700	900	220

Terminals

Neutral		Earth	Bond
2 x 9 x 50mm		2 x 9 x 50mm	1 x 3 x 50
2 x 12 x 50mm		2 x 12 x 50mm	1 x 3 x 50
2 x 18 x 50mm		2 x 18 x 50mm	1 x 3 x 50
2 x 24 x 50mm		2 x 24 x 50mm	1 x 3 x 50
2 x 12 x 50mm		2 x 12 x 50mm	1 x 3 x 50
2 x 18 x 50mm		2 x 18 x 50mm	1 x 3 x 50
2 x 27 x 50mm		2 x 27 x 50mm	1 x 3 x 50
2 x 6 x 50mm	2 x M8 Bolt	2 x 9 x 50mm	1 x 3 x 50
2 x 9 x 50mm	2 x M8 Bolt	2 x 12 x 50mm	1 x 3 x 50
2 x 6 x 50mm	4 x M8 Bolt	2 x 12 x 50mm	1 x 3 x 50
2 x 15 x 50mm	2 x M8 Bolt	2 x 18 x 50mm	1 x 3 x 50
2 x 12 x 50mm	4 x M8 Bolt	2 x 18 x 50mm	1 x 3 x 50
2 x 21 x 50mm	4 x M8 Bolt	2 x 27 x 50mm	1 x 3 x 50
2 x 18 x 50mm	6 x M8 Bolt	2 x 27 x 50mm	1 x 3 x 50

Cables outgoing ways:
25 - 50mm² CSA Flex
25 - 70mm² CSA Solid

MCCB Connections 400A M10
 630A M12

Earth 400A M10
 630A M10

Extension Boxes

	Dimensions (mm)		
	Height	Width	Depth
JF801E/G	300	900	220
JF803E/G	450	900	220
JF805E	300	900	158
JF806E	450	900	158

