

10A Rotary mech - SENSOR / MAN

Catalogue number:
WBM10RSN

WBM10RSN
Rotary mechanism

Specifications:

Regulatory


- Tested to AS/ NZS 3133:2008 + A1, AS/NZS 3100:2009
- Approval no : 1454

Electrical


- 10A, 240V, 50Hz rating
- M50

Mechanical

- External material UV stabilised polycarbonate
- Terminals accommodate 4 x 1.5mm cable



- A - Common terminal
- 1 - Sensor
- 2 - Off
- 3 - Manual



Markings

- S - Sensor
- O - Off
- M - Manual
- O - Off

Packaging

- Box qty 10
- Carton qty 400

Feature	Benefit
Rotoloc compatible	Mechanism will not pushback through plate into wall cavity
Terminal screws "backed off"	Ease of installation
Cable entries bevelled	Ease of installation
Complete mech assembled to rear of plate	Knob cannot be removed once in plate
Large graphics	Easy to read
Ergonomic grip	Easy to operate
UV stabilised, PC material	Does not fade, high impact strength