

10A dual socket outlet

Catalogue number:

WBP2S

Range:
Premiere

Specifications:

Regulatory

- Tested to AS/NZS 3133:2008 + A1, AS/NZS 3112:2004 + A1 AS/NZS 3100:2009
- Approval no : 1454

Electrical


- 10A, 240V, 50Hz rating

Mechanical

- External material UV stabilised polycarbonate
- Terminals accommodate 4 x 2.5mm cable

Packaging

- Box qty 10
- Carton qty 80



Feature	Benefit
Common & removable cover	Ease of painting, no dedicated cover for each reference
Transparent mounting grid	Ease of installation
Terminal screws "backed off"	Ease of installation
Cable entries aligned in 1 direction	Ease of installation
Cable entries bevelled	Ease of installation
Rocker arc shield	Reduces visible arc flash from switching
Chemical resistant rocker pivots	Increased resistance to chemical cleaners
High visibility "on" indicator	Ease of use
UV stabilised, PC material	Does not fade, high impact strength
Safety shutters	Mechanical protection of A/N contacts