



(GB)

IU\*\*  
IU\*\*-\*\*

Notice d'instructions  
User instructions  
Bedienungsanleitung  
Instrucciones de uso  
Instruções  
Bruksanvisning  
Gebruiksaanwijzing

ZD0835

Part No.	Without Door	Part No.	With Door
IU44-11	100A Switched Fuse	IU44-11D	100A Switched Fuse with Door AMD3
IU44-16	63A Switched Fuse	IU44-16D	63A Switched Fuse with Door AMD3
IU44-18	80A Switched Fuse	IU44-18D	80A Switched Fuse with Door AMD3

<b>Interface characteristics</b>
<b>Rated &amp; operational voltage (Un / Ue)</b> 230V a.c. 50Hz
<b>Rated insulation voltage (Ui)</b> 320V a.c. 50Hz
<b>Rated impulse withstand voltage (Uimp)</b> 4kV
<b>Rated current of the Assembly (InA)</b> 100A, 80A, 63A  Note: Dependent upon rating of main incoming device
<b>Rated current of an Outgoing circuit (Inc)</b> 100A, 80A 63A fuse
<b>Rated conditional short-circuit current of the ASSEMBLY (Icc)</b> 10kA fused conditional. 17kA pk
<b>Protection against electric shock</b> Consumer unit shall be installed in an electrical system conforming to the current edition of IEC 60364 / BS 7671
<b>Rated diversity factor (RDF) / Values of assumed loading</b> 1way = 1.0
<b>Rated frequency (fn)</b> 50 Hz
<b>Pollution degree</b> 2
<b>Types of system earthing for which the ASSEMBLY is designed</b> TNC-S, TN-S when installed in an electrical installation complying with BS 7671
<b>Indoor use only</b>
<b>Stationary ASSEMBLY</b>
<b>Degree of protection</b> IP2XC
<b>Intended use</b> Intended for use in commercial premises.
<b>Electromagnetic compatibility (EMC) classification</b> EMC Environment B
<b>External design</b> Wall-mounted, surface type, enclosed assembly.
<b>Mechanical impact protection</b> IK 05
<b>The type of construction</b> Fixed parts
<b>Type A DBO (Distribution board for use by ordinary persons)</b>

ZD0835