

# User Instructions

## Warranty

For details of the warranty on hager products, please refer to our terms and conditions.

The warranty is withdrawn if:  
After inspection by hager quality control dept the device is found to have been installed in a manner which is contrary to IEE wiring regulations and accepted practice within the industry at the time of installation.  
An explanation of defect must be included when returning goods.

**:hager**

Front

**RJ45 Jack**  
EIA/TIA 568B

1	White/Orange
2	Orange
3	White/Green
4	Blue
5	White/Blue
6	Green
7	White/Brown
8	Brown

**RJ11 Jack**  
EIA/TIA 568A

2	Blue/White
3	White/Blue
4	White/Red
5	Red/White

### Data Outlets

#### Mounting instruction

- White Moulded Range:** Remove screws and screw caps from rear of product.  
**Decorative Range:** Take the screws out of the poly bag.
- Strip 3" of cable jacket and position first pair according to color code. The center channel lets you preserve wire twisting to well within 5" of the termination point.
- As with the first pair position and terminate each subsequent pair one at a time until termination is complete.
- Connect cables ensuring all connections are both mechanically and electrically sound.
- Attach data outlet to wall box.
- If required press screw caps in to the fixing screw holes (**Decorative range has no screw caps**)
- Installation should **only be performed by a competent electrician** and comply with the local wiring regulations in force at the time of installation.
- Suitable for standard box depth  $\geq 25\text{mm}$ .

#### Checking of installation

A full functional test of the installation should be made in each data outlets.

WIS0075 (C)

Back — folded line

### Note:

- Size: 140(length) x 70(width)
- White background and black text
- Paper: 105g coated paper

C	WIS0075		Correct the "Oirange" to "Orange"		Andy Li	June/ 21 / 2012
B	WIS0075		Update the RJ11 jack to accord with samples		Leo	Nov./ 24 / 2011
Rev.	Component	No.	Description	CS No.	Author	Date
Matière / Werkstoff			Code	Épaisseur / Dicke	Volume / Volumen	Ind N° OC-OM/Pf-Nr.
105g coated paper					cm3	Date/Datum
Traitement / Behandlung			Code	Codification	Cotes sans tolérance suivant spécification N° 969019.00	Cotes inderogables Unüberschreibares Maß
				Sollysta	Maße 0. Toleranzen nach DIN	$Cm \geq 1,33 \quad Cmk > 1$
Dessine par / Gezeichnet		Date / Datum	Bezeichnung:			
Leo		September.1st,2011				
Contrôle par / Geprüft		Date / Datum	Désignation:			
			Sollysta Instruction sheet for data outlet			
	Echelle/Maßstab	N°	WIS0075		Production	Rev:C
	1:1	Nr.				
Huizhou hager Electric Ltd.	Format	Ersatz für				
	A4	Remplace				
Ce dessin est la propriété de la société HAGER, il ne peut être reproduit ou communiqué sans son autorisation.						