

P630 - x630
HXW031H/HXW036H

Information
Marking of MCCB and accessory must be in the same direction

OK

NOK

Tools:

- 4 - 5
- PH 1 - PH 2
- 3
- 10
- 14
- 7 mm


3P - 4P

- M5-16 mm
- x4
- x2
- x4
- x1
- x1
- x1
- x1
- x2
- x1
- x1
- x4

3P - 4P

Dimensions: 138, 125, 261, 141, 97, 234, 144.5, 184

mm



01 3P - 4P

TRIP

4

02a MCCB1 + MCCB2

02b

PH1 (+)

A, B, C, D

03



TRIP

04

AK, AL, BNF, UNF

x630








In: 630A Icu (t15V-) 25kA



Information
 Marking of MCCB and accessory must be in the same direction

OK

NOK



013

$L = L1 - X + 19,5$

$X = 19,5 \pm 2$

HXW912H	
L1	200
HXW913H	
L1	320
HXW915H	
L1	500

L1

mm

