

We **Hager Electro SAS**  
**BP3**  
**67215 OBERNAI CEDEX - FRANCE**

Declare that the product(s)

Designation

**KLIK Lighting Distribution System (4 pin)**

Type reference(s)

**KLIK 4 System ranges**  
**Marshalling Boxes : LDS**  
**Plug & Ceiling Roses : PCR2000 / CR64AX / P22 / P64 / S27 / S64**  
**Wireable & pre-wired plug leads**

Trademark

Hager

is (are) in conformity with the relevant United Kingdom legislation:

- SI 2012/3032 Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations 2012 (as amended)
  - SI 2016/1091 Electromagnetic Compatibility (EMC) Regulations 2016 (as amended)
  - SI 2016/1101 Electrical Equipment (safety) Regulations 2016 (as amended)
- .....
- .....

Standard(s) and/or relevant document(s) to which conformity is declared

Standard number + relevant amendments together with the edition dates

**BS 5733:2010+A1:2014**

**BS 6972:1988(Amd1)**

**BS EN IEC 63000:2018**

If applicable, mention here for radio products, the data about notified body. See RE legislation - Annex VI - point 7

**This declaration of conformity is issued under the sole responsibility of the manufacturer.**

**On behalf of Hager Electro SAS**

Name of signatory

Eddie Li

Function of signatory

Lab Manager - Group Quality & Environment

Place and date of issue

Huizhou, CN 08/10/2024

Signature



## UKCA DECLARATION OF CONFORMITY

No. UKCA 24.2963.10.08

### Type references

#### Klik 4 - Marshalling Boxes

Product Reference	Product Description
KLDS4	4 Way Klik Lighting Distribution Unit
KLDS6	6 Way Klik Lighting Distribution Unit
KLDS8	8 Way Klik Lighting Distribution Unit
KLDS10	10 Way Klik Lighting Distribution Unit
KLDS12	12 Way Klik Lighting Distribution Unit
KLDS4BLACK	4 Way Klik Lighting Distribution Unit – Black
KLDS6BLACK	6 Way Klik Lighting Distribution Unit – Black
KLDS8BLACK	8 Way Klik Lighting Distribution Unit – Black
KLDS10BLACK	10 Way Klik Lighting Distribution Unit – Black
KLDS12BLACK	12 Way Klik Lighting Distribution Unit – Black

## UKCA DECLARATION OF CONFORMITY

No. UKCA 24.2963.10.08

### Type references

#### Klik 4 - 3 Pin Pre-wired 6A Plug-in Ceiling Rose

Product Reference	Product Description
PCR2000/1.0	6A Plug-in Ceiling Rose with 0.75mm <sup>2</sup> Flexible Cord – 1 Metre PVC
PCR2000/2.0	6A Plug-in Ceiling Rose with 0.75mm <sup>2</sup> Flexible Cord – 2 Metre PVC
PCR2000/3.0	6A Plug-in Ceiling Rose with 0.75mm <sup>2</sup> Flexible Cord – 3 Metre PVC
PCR2000/4.0	6A Plug-in Ceiling Rose with 0.75mm <sup>2</sup> Flexible Cord – 4 Metre PVC
PCR2000/LSF/1.0	6A Plug-in Ceiling Rose with 0.75mm <sup>2</sup> Flexible Cord – 1 Metre LSZH
PCR2000/LSF/2.0	6A Plug-in Ceiling Rose with 0.75mm <sup>2</sup> Flexible Cord – 2 Metre LSZH
PCR2000/LSF/3.0	6A Plug-in Ceiling Rose with 0.75mm <sup>2</sup> Flexible Cord – 3 Metre LSZH
PCR2000/LSF/4.0	6A Plug-in Ceiling Rose with 0.75mm <sup>2</sup> Flexible Cord – 4 Metre LSZH
PCR2000/1.0PVC/2	6A Plug-in Ceiling Rose with 1mm <sup>2</sup> Flexible Cord – 2 Metre PVC
PCR2000/1.0PVC/3	6A Plug-in Ceiling Rose with 1mm <sup>2</sup> Flexible Cord – 3 Metre PVC
PCR2000/1.0PVC/4	6A Plug-in Ceiling Rose with 1mm <sup>2</sup> Flexible Cord – 4 Metre PVC
PCR2000/1.0PVC/5	6A Plug-in Ceiling Rose with 1mm <sup>2</sup> Flexible Cord – 5 Metre PVC
PCR2000/1.0LSF/2	6A Plug-in Ceiling Rose with 1mm <sup>2</sup> Flexible Cord – 2 Metre LSZH
PCR2000/1.0LSF/3	6A Plug-in Ceiling Rose with 1mm <sup>2</sup> Flexible Cord – 3 Metre LSZH
PCR2000/1.0LSF/4	6A Plug-in Ceiling Rose with 1mm <sup>2</sup> Flexible Cord – 4 Metre LSZH
PCR2000/1.0LSF/5	6A Plug-in Ceiling Rose with 1mm <sup>2</sup> Flexible Cord – 5 Metre LSZH

## UKCA DECLARATION OF CONFORMITY

No. UKCA 24.2963.10.08

### Type references

#### Klik 4 - 4 Pin (Including Auxiliary) Pre-wired 6A Plug-in Ceiling Rose

Product Reference	Product Description
CR64AX/1.0	6A Pre-wired Ceiling Rose with 0.75mm <sup>2</sup> Flexible Cord – 1 Metre PVC
CR64AX/2.0	6A Pre-wired Ceiling Rose with 0.75mm <sup>2</sup> Flexible Cord – 2 Metre PVC
CR64AX/3.0	6A Pre-wired Ceiling Rose with 0.75mm <sup>2</sup> Flexible Cord – 3 Metre PVC
CR64AX/4.0	6A Pre-wired Ceiling Rose with 0.75mm <sup>2</sup> Flexible Cord – 4 Metre PVC
CR64AX/LSF/1.0	6A Pre-wired Ceiling Rose with 0.75mm <sup>2</sup> Flexible Cord – 1 Metre LSZH
CR64AX/LSF/2.0	6A Pre-wired Ceiling Rose with 0.75mm <sup>2</sup> Flexible Cord – 2 Metre LSZH
CR64AX/LSF/3.0	6A Pre-wired Ceiling Rose with 0.75mm <sup>2</sup> Flexible Cord – 3 Metre LSZH
CR64AX/LSF/4.0	6A Pre-wired Ceiling Rose with 0.75mm <sup>2</sup> Flexible Cord – 4 Metre LSZH
CR64AX/1.0PVC/2	6A Pre-wired Ceiling Rose with 1mm <sup>2</sup> Flexible Cord – 2 Metre PVC
CR64AX/1.0PVC/3	6A Pre-wired Ceiling Rose with 1mm <sup>2</sup> Flexible Cord – 3 Metre PVC
CR64AX/1.0PVC/4	6A Pre-wired Ceiling Rose with 1mm <sup>2</sup> Flexible Cord – 4 Metre PVC
CR64AX/1.0PVC/5	6A Pre-wired Ceiling Rose with 1mm <sup>2</sup> Flexible Cord – 5 Metre PVC
CR64AX/1.0LSF/2	6A Pre-wired Ceiling Rose with 1mm <sup>2</sup> Flexible Cord – 2 Metre LSZH
CR64AX/1.0LSF/3	6A Pre-wired Ceiling Rose with 1mm <sup>2</sup> Flexible Cord – 3 Metre LSZH
CR64AX/1.0LSF/4	6A Pre-wired Ceiling Rose with 1mm <sup>2</sup> Flexible Cord – 4 Metre LSZH
CR64AX/1.0LSF/5	6A Pre-wired Ceiling Rose with 1mm <sup>2</sup> Flexible Cord – 5 Metre LSZH

## UKCA DECLARATION OF CONFORMITY

No. UKCA 24.2963.10.08

### Type references

#### Klik 4 - 3 Pin Pre-wired 6A Plugs

Product Reference	Product Description
P22/1.0	6A Pre-wired Plugs with 0.75mm <sup>2</sup> Flexible Cord – 1 Metre PVC
P22/2.0	6A Pre-wired Plugs with 0.75mm <sup>2</sup> Flexible Cord – 2 Metre PVC
P22/3.0	6A Pre-wired Plugs with 0.75mm <sup>2</sup> Flexible Cord – 3 Metre PVC
P22/4.0	6A Pre-wired Plugs with 0.75mm <sup>2</sup> Flexible Cord – 4 Metre PVC
P22/LSF/1.0	6A Pre-wired Plugs with 0.75mm <sup>2</sup> Flexible Cord – 1 Metre LSZH
P22/LSF/2.0	6A Pre-wired Plugs with 0.75mm <sup>2</sup> Flexible Cord – 2 Metre LSZH
P22/LSF/3.0	6A Pre-wired Plugs with 0.75mm <sup>2</sup> Flexible Cord – 3 Metre LSZH
P22/LSF/4.0	6A Pre-wired Plugs with 0.75mm <sup>2</sup> Flexible Cord – 4 Metre LSZH
P22/1.0PVC/2	6A Pre-wired Plugs with 1mm <sup>2</sup> Flexible Cord – 2 Metre PVC
P22/1.0PVC/3	6A Pre-wired Plugs with 1mm <sup>2</sup> Flexible Cord – 3 Metre PVC
P22/1.0PVC/4	6A Pre-wired Plugs with 1mm <sup>2</sup> Flexible Cord – 4 Metre PVC
P22/1.0PVC/5	6A Pre-wired Plugs with 1mm <sup>2</sup> Flexible Cord – 5 Metre PVC
P22/1.0LSF/2	6A Pre-wired Plugs with 1mm <sup>2</sup> Flexible Cord – 2 Metre LSZH
P22/1.0LSF/3	6A Pre-wired Plugs with 1mm <sup>2</sup> Flexible Cord – 3 Metre LSZH
P22/1.0LSF/4	6A Pre-wired Plugs with 1mm <sup>2</sup> Flexible Cord – 4 Metre LSZH
P22/1.0LSF/5	6A Pre-wired Plugs with 1mm <sup>2</sup> Flexible Cord – 5 Metre LSZH

## UKCA DECLARATION OF CONFORMITY

No. UKCA 24.2963.10.08

### Type references

#### Klik 4 - 4 Pin (Including Auxiliary) Pre-wired 6A Plugs - White

Product Reference	Product Description
P64AX/1.0	6A Pre-wired Plugs with 0.75mm <sup>2</sup> Flexible Cord – 1 Metre PVC
P64AX/2.0	6A Pre-wired Plugs with 0.75mm <sup>2</sup> Flexible Cord – 2 Metre PVC
P64AX/3.0	6A Pre-wired Plugs with 0.75mm <sup>2</sup> Flexible Cord – 3 Metre PVC
P64AX/4.0	6A Pre-wired Plugs with 0.75mm <sup>2</sup> Flexible Cord – 4 Metre PVC
P64AX/LSF/1.0	6A Pre-wired Plugs with 0.75mm <sup>2</sup> Flexible Cord – 1 Metre LSZH
P64AX/LSF/2.0	6A Pre-wired Plugs with 0.75mm <sup>2</sup> Flexible Cord – 2 Metre LSZH
P64AX/LSF/3.0	6A Pre-wired Plugs with 0.75mm <sup>2</sup> Flexible Cord – 3 Metre LSZH
P64AX/LSF/4.0	6A Pre-wired Plugs with 0.75mm <sup>2</sup> Flexible Cord – 4 Metre LSZH
P64AX/1.0PVC/2	6A Pre-wired Plugs with 1mm <sup>2</sup> Flexible Cord – 2 Metre PVC
P64AX/1.0PVC/3	6A Pre-wired Plugs with 1mm <sup>2</sup> Flexible Cord – 3 Metre PVC
P64AX/1.0PVC/4	6A Pre-wired Plugs with 1mm <sup>2</sup> Flexible Cord – 4 Metre PVC
P64AX/1.0PVC/5	6A Pre-wired Plugs with 1mm <sup>2</sup> Flexible Cord – 5 Metre PVC
P64AX/1.0LSF/2	6A Pre-wired Plugs with 1mm <sup>2</sup> Flexible Cord – 2 Metre LSZH
P64AX/1.0LSF/3	6A Pre-wired Plugs with 1mm <sup>2</sup> Flexible Cord – 3 Metre LSZH
P64AX/1.0LSF/4	6A Pre-wired Plugs with 1mm <sup>2</sup> Flexible Cord – 4 Metre LSZH
P64AX/1.0LSF/5	6A Pre-wired Plugs with 1mm <sup>2</sup> Flexible Cord – 5 Metre LSZH

## UKCA DECLARATION OF CONFORMITY

No. UKCA 24.2963.10.08

### Type references

#### Klik 4 - 4 Pin (Including Auxiliary) Pre-wired 6A Plugs - Red

Product Reference	Product Description
P64AXR/1.0	6A Pre-wired Plugs with 0.75mm <sup>2</sup> Flexible Cord – 1 Metre PVC
P64AXR/2.0	6A Pre-wired Plugs with 0.75mm <sup>2</sup> Flexible Cord – 2 Metre PVC
P64AXR/3.0	6A Pre-wired Plugs with 0.75mm <sup>2</sup> Flexible Cord – 3 Metre PVC
P64AXR/4.0	6A Pre-wired Plugs with 0.75mm <sup>2</sup> Flexible Cord – 4 Metre PVC
P64AXR/LSF/1.0	6A Pre-wired Plugs with 0.75mm <sup>2</sup> Flexible Cord – 1 Metre LSZH
P64AXR/LSF/2.0	6A Pre-wired Plugs with 0.75mm <sup>2</sup> Flexible Cord – 2 Metre LSZH
P64AXR/LSF/3.0	6A Pre-wired Plugs with 0.75mm <sup>2</sup> Flexible Cord – 3 Metre LSZH
P64AXR/LSF/4.0	6A Pre-wired Plugs with 0.75mm <sup>2</sup> Flexible Cord – 4 Metre LSZH
P64AXR/1.0PVC/2	6A Pre-wired Plugs with 1mm <sup>2</sup> Flexible Cord – 2 Metre PVC
P64AXR/1.0PVC/3	6A Pre-wired Plugs with 1mm <sup>2</sup> Flexible Cord – 3 Metre PVC
P64AXR/1.0PVC/4	6A Pre-wired Plugs with 1mm <sup>2</sup> Flexible Cord – 4 Metre PVC
P64AXR/1.0PVC/5	6A Pre-wired Plugs with 1mm <sup>2</sup> Flexible Cord – 5 Metre PVC
P64AXR/1.0LSF/2	6A Pre-wired Plugs with 1mm <sup>2</sup> Flexible Cord – 2 Metre LSZH
P64AXR/1.0LSF/3	6A Pre-wired Plugs with 1mm <sup>2</sup> Flexible Cord – 3 Metre LSZH
P64AXR/1.0LSF/4	6A Pre-wired Plugs with 1mm <sup>2</sup> Flexible Cord – 4 Metre LSZH
P64AXR/1.0LSF/5	6A Pre-wired Plugs with 1mm <sup>2</sup> Flexible Cord – 5 Metre LSZH

## UKCA DECLARATION OF CONFORMITY

No. UKCA 24.2963.10.08

### Type references

#### Klik 4 - 3 Pin Plug-in Ceiling Rose & Cover

Product Reference	Product Description
PCR2000	3 Pin Plug-in Ceiling Rose White
PCR2000BLACK	3 Pin Plug-in Ceiling Rose Black

#### Klik 4 - 4 Pin (including Auxiliary) Plug-in Ceiling Rose & Cover

Product Reference	Product Description
CR64AX	4 Pin Plug-in Ceiling Rose White
CR64AX/R	4 Pin Plug-in Ceiling Rose Red
A1	Ceiling Rose Cover White
A1/R	Ceiling Rose Cover Red
A1BLACK	Ceiling Rose Cover Black

#### Klik 4 - 3 Pin Plug

Product Reference	Product Description
P22	3 Pin Plug White
P22BLACK	3 Pin Plug Black

#### Klik 4 - 4 Pin (Including Auxiliary) Plug

Product Reference	Product Description
P64AX	4 Pin Plug White
P64AX/R	4 Pin Plug Red



## UKCA DECLARATION OF CONFORMITY

No. UKCA 24.2963.10.08

### Type references

#### Klik 4 - 3 Pin Plug Socket Outlets

Product Reference	Product Description
S27	3 Pin Round Socket White

#### Klik 4 - 4 Pin (Including Auxiliary) Plug Socket Outlets

Product Reference	Product Description
S64AX	4 Pin Round Socket White
S64BLACK	4 Pin Round Socket Black

#### Moulded Mounting Boxes

Product Reference	Product Description
MB2	Round Surface Box White

## UKCA DECLARATION OF CONFORMITY

No. UKCA 24.2963.10.08

### Evidence(s)

Documents listed below have been developed to assure that all essential requirements of applied directive(s) are fulfilled:

If the product is not in the scope of Radio Equipment directive, fulfil table 1a, if yes fulfil table.

Table 1a Risk Assessment for <b>Equipment without Radio</b>	Applicable: <input checked="" type="checkbox"/> Yes <input type="checkbox"/> No
Only designated standards published on GOV.UK ( <a href="https://www.gov.uk/guidance/designated-standards">https://www.gov.uk/guidance/designated-standards</a> ) are used:	No
Scope and classification fully covers the product (case 1 of Hager Group risk analysis) :	Yes
Comments :	Designated Before 2016
Hager Group risk analysis: Only if there is at least one "No", then you have to explain how you cover the essential requirements and fill the document <u>DMS034433</u> - Hager Group risk analysis)	DMS034433 followed using case 2 of Hager Group method:  Non-Designated Standard Used

Table 1b Risk Assessment for <b>Radio equipment</b>	Applicable: <input type="checkbox"/> Yes <input checked="" type="checkbox"/> No
Hager Group risk assessment: Fill document DMS063155	

### Evidence(s) / Evidence(s)

Documents listed below have been used in order to establish the conformity to the essential requirements of the relevant directives

Certificate(s) / test report(s):	Nemko Certificate C11 42534 HG Lab Test Report TRWA1308019 KLDS HG Lab Test Report TRWA1408004 PCR2000 HG Lab Test Report TRWA1612010 CR64AX HG Lab Test Report TRWA1612013 PCR2000 HG Lab Test Report LB 20 0017 PCR2000 HG Lab Test Report LB 20 0343 CR64AX
Mark approval(s):	None
Product documentation :	See Hager Website
Comments:	None

#### Signature (technical design)

**Name of signatory**

John Lee

**Function of signatory**

Business Development Manager

**Place and date of issue**

Huizhou, CN 08/10/2024

**Signature**



## UKCA DECLARATION OF CONFORMITY

No. UKCA 24.2963.10.08

### Designated Standards

Designated standard UKCA RoHS:

S.I. 2012 No. 3033	EN IEC 63000:2018	Technical documentation for the assessment of electrical and electronic products with respect to the restriction of hazardous substances	01/01/2021	0037/21
-----------------------	-------------------	--	------------	---------