

Adhesive smoke seal (3.5m)

Catalogue numbers:
JPASMSEAL1

Specifications:

Regulatory

- REACH and RoHS certified

Product Description

- 3.2mm thick closed cell EPDM foam tap with an adhesive on one side
- EPDM foam is non-staining, non-corrosive and electrically non-conductive
- EPDM foam is also non-toxic and flame retardant
- EPDM foam offers high temperature resistance(-40 C to 115 C) as well as resistance to UV light and ozone

Application Fields

- Ideal sealing solution for enclosure/switchboard
- Ideal sealing solution for electrical enclosure/switch cabinets

Materials

- Backing - EPDM rubber foam
- Type of adhesive - acrylic

Properties / Performance Values

Tensile strength	16N/cm
Hardness - Shore 00	34 STK
Temperature resistance min.	-40°C
Temperature resistance max.	115°C
Thermal conductivity z-direction	0.05 W/mK
Water resistance	Very good

Adhesion to values

Steel	5.5N/cm
-------	---------

