

h3+ P630

3P - 4P

x1

AX AX AX-AL
AX AX SHT
AL AL UVT

x4 (3P)
x6 (4P)

x6 (3P)
x8 (4P)

M6 x 100

x4

! ENERGY

MCCB 3P

HTC160H

Wrench and Screwdriver

3

PH1 / PH2

6 / 8

Dimensions

	A (mm)
3P	140
4P	185

Mounting

M6

PH2

6 Nm

214

45

mm

Operation Sequence: TRIP → OFF → ON → TRIP → OFF















A







B

Clack!

C

D





HYW001H 3P
HYW002H 4P

Cu
Al



	min.	max.
	400 A	630 A
	35 □	300 □

x3 (3P)
x4 (4P)

	35 □ → 95 □	120 □ → 300 □
L=28 mm	L=21 mm	L=21 mm
x3 (x4)	x3 (x4)	x3 (x4)

x4

+L+



01

HYW007H 3P
HYW008H 4P

Cu
Al

	min.	max.
	400 A - 630 A	
	35□	300□
	35□ → 95□	120□ → 300□
	L=28 mm x6 (x8)	L=21 mm x6 (x8)

01

02

03

01

HYW019H

3P - 4P

01

HYW050H 3P
HYW051H 4P

HYW021H 3P
HYW022H 4P

HYW052H 3P
HYW053H 4P

01

02

03

