

Hager Dream

Live your DREAM



1 gang switch

WGDL111 - 16AX 1 way
WGDL112 - 16AX 2 way
WGDL111N - 16AX 1 way w/ LED
WGDL112N - 16AX 2 way w/ LED



2 gang switch

WGDL121 - 16AX 1 way
WGDL122 - 16AX 2 way
WGDL121N - 16AX 1 way w/ LED
WGDL122N - 16AX 2 way w/ LED



3 gang switch

WGDL131 - 16AX 1 way
WGDL132 - 16AX 2 way
WGDL131N - 16AX 1 way w/ LED
WGDL132N - 16AX 2 way w/ LED



4 gang switch

WGDL141 - 16AX 1 way
WGDL142 - 16AX 2 way



1 gang press switch

WGDL111P - 10A
WGDL111NP - 10A w/ 220V LED
WGDL111NP-12V - 10A w/ 12V LED



2 gang press switch

WGDL121P - 10A
WGDL121NP - 10A w/ 220V LED
WGDL121NP-12V - 10A w/ 12V LED



3 gang press switch

WGDL131P - 10A
WGDL131NP - 10A w/ 220V LED
WGDL131NP-12V - 10A w/ 12V LED



Intermediate

WGDL113 - 10AX 1 gang



Dimmer

WGDEDR500 - 40-500W single 2 way



Fan control

WGDEFR250 - 250VA single



Bell & EXIT switch

WGDL111B - mark "bell symbol"
WGDL111E - mark "EXIT"



20AX DP control switch

WGDL2D1N - 20AX 1 gang w/ LED
WGDL2D2N - 20AX 2 gang w/ LED
WGDL2D12N - 20AX 1 gang 2 way w/ LED



32A/ 45A DP control switch

WGDR32D1 - 32A 1 gang w/ LED
WGDR45D1 - 45A 1 gang w/ LED



Connection unit

WGDR25 - 25A w/ flex outlet



Fused connection unit

WGDR13N - 13A fused w/ neon
+ flex outlet



Fused connection unit

WGDR13SN - 13A switched fused
w/ flex outlet, w/ neon



13A single socket outlet

WGDS113 - single
WGDS113S - single switched
WGDS113SN - single switched w/ LED



13A USB single socket outlet

WGDS113SUBS - single switched
+ 2 x USB charger
WGDS113S1USB - single switched
+ 1 x USB charger



13A twin socket outlet

WGDS213 - twin
WGDS213S - twin switched
WGDS213SN - twin switched w/ LED



13A USB twin socket outlet

WGDS213SUBS - twin switched
+ 2 x USB charger



10A/15A socket outlet

WGDS110US - 10A, 2 pin switched universal
WGDS210U - 10A, 2 pin + 2 pin universal
WGDS115S - 15A round pin switched



16A socket outlet

WGDS116EA - single Euro-American
WGDS216EA - twin Euro-American



16A German socket

WGDS116S - single German
w/ shutter



TV inlet/outlet

WGDT1TV - TV inlet/ outlet, 1 mod
WGDT1TVF - TV outlet, F type, 1 mod



TV & Data inlet/outlet

WGDT2TVRJ5 - TV inlet/ outlet + RJ45
cat5e 2 mod



RJ11 telephone outlet

WGDT1RJ - 1 mod
WGDT2RJ - 2 mod



RJ45 cat6 outlet

WGDT1RJ6 - 1 mod
WGDT1RJ6NM - 1 mod w/o symbol
WGDT2RJ6 - 2 mod
WGDT2RJ6NM - 2 mod w/o symbol



RJ45 cat5e outlet

WGDT1RJ5 - 1 mod
WGDT2RJ5 - 2 mod



RJ11 + RJ45 outlet

WGDT1RJ5 - RJ11+RJ45 cat5e 2 mod
WGDT2RJRJ6 - RJ11+RJ45 cat6 2 mod



Blank plate

WGDBP1 - blank plate



Sleeping light

WGDHSL - Sleeping light (0.25W)



Shaver socket

WGDSHR - 115/230V

Color ranges



Interstellar Grey
(IG)



Noble Bronze
(NB)



Knight Black
(KB)



Elegant Gold
(EG)

Remark: blue reference product - coming soon



Accommodation plate

WGDEV2 - 2 mod



Hotel range

WGHDHC - 16AX, DND & MUR w/ LED (Indoor)
WGHDHD - 4A DND & MUR indicator
w/ bell switch
WGDKHTM - 16A key tag-mechanical
WGDKHTRFID - 16A key tag- RFID



Hotel range

WGDDHIVA - HDMI+VGA
WGDDHRCASV - RCA+S-Video socket
WGDS3USB - USB charger
(1 x type C) + (2 x type A)
WGDDHUSB35 - USB + 3.5mm audio
WGDEE1 - Emergency switch
WGDEA6 - 6W Audio switch



Multi-gang frame

WGDC2 - 2 gang horizontal
WGDC3 - 3 gang horizontal
WGDC4 - 4 gang horizontal
WGDC5 - 5 gang horizontal



WA covers

XC9003 - IP55, single size
XC9004 - IP55, twin size

:hager