

Hager Inspire

Design for a better life



1 gang switch
WGCL111 - 16AX 1 way
WGCL112 - 16AX 2 way
WGCL111P - 10A Press



2 gang switch
WGCL121 - 16AX 1 way
WGCL122 - 16AX 2 way
WGCL121P - 10A Press



3 gang switch
WGCL131 - 16AX 1 way
WGCL132 - 16AX 2 way
WGCL131P - 10A Press



4 gang switch
WGCL141 - 16AX 1 way
WGCL142 - 16AX 2 way
WGCL141P - 10A Press



1 gang switch w/ fluorescence
WGCL111F - 16AX 1 way
WGCL112F - 16AX 2 way



2 gang switch w/ fluorescence
WGCL121F - 16AX 1 way
WGCL122F - 16AX 2 way



3 gang switch w/ fluorescence
WGCL131F - 16AX 1 way
WGCL132F - 16AX 2 way



4 gang switch w/ fluorescence
WGCL141F - 16AX 1 way
WGCL142F - 16AX 2 way



1 gang round switch
WGCR111 - 16AX 1 way
WGCR112 - 16AX 2 way
WGCR111P - 10A Press



2 gang round switch
WGCR121 - 16AX 1 way
WGCR122 - 16AX 2 way
WGCR121P - 10A Press



3 gang round switch
WGCR131 - 16AX 1 way
WGCR132 - 16AX 2 way
WGCR131P - 10A Press



Intermediate
WGCL113 - 10AX 1 gang



Bell & EXIT switch
WGCL111B - mark "bell symbol"
WGCL111E - mark "EXIT"



Dimmer
WGCEDR500 - 40-500W single 2 way



Fan control
WGCEFR250 - 250VA single



20AX DP control switch
WGCL2D1N - 20AX 1 gang with LED
WGCL2D2N - 20AX 2 gang with LED
WGCL2D12N - 20AX 1 gang 2 way w/ LED



32A/45A DP control switch
WGCR32D1 - 32A 1 gang w/ LED
WGCR45D1 - 45A 1 gang w/ LED



13A single socket outlet
WGCS113S - single switched
WGCS113SN - single switched w/ LED



13A USB single socket outlet
WGCS113SUSB - single switched
+ 2 x USB charger



13A twin socket outlet
WGCS213S - twin switched
WGCS213SN - twin switched w/ LED



13A USB twin socket outlet
WGCS213SUSB - twin switched
+ 2 x USB charge



15A socket outlet
WGCS115S - 15A round pin switched



16A German socket
WGCS116S - single German w/ shutter



16A socket outlet
WGCS116EA - single Euro-American
WGCS216EA - twin Euro-American



Shaver socket
WGCHSR - 115/230V



Hotel range
WGCHHIVA - HDMI+VGA
WGCHRCASV - RCA+S-Video socket
WGCS3USB - USB charger
WGCHUSB35 - USB + 3.5mm audio
(1 x type C) + (2 x type A)
WGCEE1 - Emergency switch
WGCEA6 - 6W Audio switch
WGCHDC - 16AX, DND & MUR w/ LED (Indoor)
WGCHKTM - 16A key tag-mechanical
WGCHKTRFID - 16A key tag- RFID



RJ45 cat6 outlet
WGCT1RJ6 - 1 mod
WGCT1RJ6NM - 1 mod w/o symbol
WGCT2RJ6 - 2 mod
WGCT2RJ6NM - 2 mod w/o symbol



RJ45 cat5e outlet
WGCT1RJ5 - 1 mod
WGCT2RJ5 - 2 mod



RJ11 telephone outlet
WGCT1RJ - 1 mod
WGCT2RJ - 2 mod



RJ11 + RJ45 outlet
WGCT2RJ5 - RJ11+RJ45 cat5e 2 mod
WGCT2RJ6 - RJ11+RJ45 cat6 2 mod



TV inlet/outlet
WGCT1TV - TV inlet/ outlet, 1 mod
WGCT1TVF - TV outlet, F type, 1 mod



TV & Data inlet/outlet
WGCT2TVRJ5 - TV inlet/ outlet + RJ45
cat5e 2 mod

Color ranges



Interstellar Grey
(IG)



Noble Bronze
(NB)



Knight Black
(KB)



Elegant Gold
(EG)

Remark: blue reference product - coming soon



Accommodation plate
WGCV2 - 2 mod



Blank plate
WGCBP1 - blank plate



Frame
WGCC2 - 2 gang
WGCC1S - 1 gang, square
WGCC1R - 1 gang, round



Multi-gang frame
Horizontal Vertical
WGCC2 - 2 gang WGCCV2 - 2 gang
WGCC3 - 3 gang WGCCV3 - 3 gang
WGCC4 - 4 gang
WGCC5 - 5 gang



WA covers
XC9003 - IP55, single size
XC9004 - IP55, twin size

:hager