

# Hager Muse

## Design for comfort and safety



**1 gang switch**

WGML111 - 16AX 1 way  
WGML112 - 16AX 2 way  
WGML111P - 10A Press



**2 gang switch**

WGML121 - 16AX 1 way  
WGML122 - 16AX 2 way  
WGML121P - 10A Press



**3 gang switch**

WGML131 - 16AX 1 way  
WGML132 - 16AX 2 way  
WGML131P - 10A Press



**4 gang switch**

WGML141 - 16AX 1 way  
WGML142 - 16AX 2 way  
WGML141P - 10A Press



**Intermediate**

WGML113 - 10AX 1 gang



**Bell & EXIT switch**

WGML111B - mark "bell symbol"  
WGML111E - mark "EXIT"



**Fan control**

WGMEFR250 - 250VA single



**Dimmer**

WGMEDR500 - 40-500W single 2 way



**20AX DP control switch**

WGML2D1N - 20AX 1 gang w/ LED  
WGML2D2N - 20AX 2 gang w/ LED  
WGML2D12N - 20AX 1 gang 2 way w/ LED



**32A/45A DP control switch**

WGMR32D1 - 32A 1 gang w/ LED  
WGMR45D1 - 45A 1 gang w/ LED



**Connection unit**

WGMR25 - 25A w/ flex outlet  
WGMR45 - 45A w/ flex outlet




**Fused connection unit**

WGMR13 - 13A fused w/ flex outlet  
WGMR13N - 13A fused w/ neon  
+ flex outlet



**Fused connection unit**

WGMR13S - 13A switched fused  
w/ flex outlet  
WGMR13SN - 13A switched fused  
w/ flex outlet, w/ neon



**13A single socket outlet**

WGMS113 - single unswitched  
WGMS113S - single switched  
WGMS113SN - single switched w/ LED



**13A USB single socket outlet**

WGMS113SUSB - single switched  
+ 2 x USB charger  
WGMS113S1USB - single switched  
+ 1 x USB charger




**13A twin socket outlet**

WGMS213 - twin unswitched  
WGMS213S - twin switched  
WGMS213SN - twin switched w/ LED



**13A USB twin socket outlet**

WGMS213SUSB - twin switched  
+ 2 x USB charger



**10A/15A socket outlet**

WGMS110US - 10A, 2 pin switched universal  
WGMS210U - 10A, 2 pin + 2 pin universal  
WGMS115S - 15A round pin switched



**16A socket outlet**

WGMS116EA - single Euro-American  
WGMS216EA - twin Euro-American



**16A German socket**

WGMS116S - single German w/ shutter



**RJ11 telephone outlet**

WGMT1RJ - 1 mod  
WGMT2RJ - 2 mod



**RJ45 cat6 outlet**

WGMT1RJ6 - 1 mod  
WGMT1RJ6-SG - RJ45 cat6  
(DATA marking) 1 mod  
WGMT1RJ6NM - 1 mod w/o symbol  
WGMT2RJ6 - 2 mod  
WGMT2RJ6NM - 2 mod w/o symbol



**RJ45 cat5e outlet**

WGMT1RJ5 - 1 mod  
WGMT2RJ5 - 2 mod



**RJ11 + RJ45 outlet**

WGMT2RJRJ5 - RJ11+RJ45 cat5e, 2 mod  
WGMT2RJRJ6 - RJ11+RJ45 cat6, 2 mod



**TV inlet/outlet**

WGMT1TV - TV inlet/outlet, 1 mod  
WGMT1TVF - TV outlet, F type, 1 mod



**TV & Data inlet/outlet**

WGMT2TVRJ5 - TV inlet/outlet + RJ45  
cat5e 2mod  
WGMT2TVRJ6-SG - TV inlet/outlet + RJ45  
cat6 (TV marking) 2 mod  
WGMT2TVFRJ6-SG - TV outlet, F type + RJ45  
cat6 (DATA marking) 2 mod



**USB charger**

WGMS3USB - USB charger  
(1 x typeC) + (2 x typeA)



**Hotel range**

WGMHDC - 16AX, DND & MUR  
w/ LED (Indoor)  
WGMMEA6 - 6W Audio switch  
WGMHKTM - 16A key tag-mechanical  
WGMHKTRFID - 16A key tag - RFID



**Door chime**

WXEDC01 - Electronic



**Blank plate**

WGMBP1 - blank plate  
WGMBP2 - size 2



**Frame**

WGMCV1 - 1 gang (Vertical) 52 x 65mm  
WGMC2 - 2 gang  
WGMC1 - 1 gang (Horizontal) 65 x 52mm  
WGMC1S - 1 gang (square) 52 x 52mm



**Multi-gang, horizontal**

WGMC2 - 2 gang  
WGMC3 - 3 gang  
WGMC4 - 4 gang  
WGMC5 - 5 gang

### Color ranges



White



Aurora Silver  
(AS)



Knight Black  
(KB)

Remark: blue reference product - coming soon



**Accommodation plate**

WGMVE2 - 2 modules



**WA covers**

XC9003 - IP55, single size  
XC9004 - IP55, twin size

**:hager**