

Hager Desire  
wiring accessories

# Elevate every moment



:hager



# Modern and minimalist

Our frameless range invites you to witness a canvas of possibilities, where the sophisticated simplicity accentuates the beauty of your spaces, setting a new benchmark for modern living.





## Frameless design

The ultra-slim, frameless design offers a seamless integration into any living space, where your spaces are not just designed but transformed with a timeless allure.



## High 16AX rating

The rated current of switch is 16AX, which meets the requirements of using electricity safely in all aspects.



## Socket with USB charger

The socket equipped with a 2.4A USB charger, which intelligently adapt to mobile devices with different power consumptions, ensure the charging safety and efficiency.



# Exceptional performance



## Engineered excellence in every interaction

Designed to meet and exceed the demands of the modern user, every product within the range guarantees reliability, consistency, and superior functionality that stands the test of time.





## Eco-packaging

Sustainability and eco-friendly solutions are our promise to our customers. That's why we adhere to environmental philosophy by only using sustainable recycled packaging material.



## USB protected against surge voltages

Protection against transient surge voltage for the USB circuits is provided at 2500Vac, 2.5 times higher than IEC requirement. USB output maintains at 5Vdc to ensure optimum safety for users and equipment being charged.











## Child-proof shutter

Having safety awareness all the time comes from the care for family members. The socket panel is designed with child lock, preventing unintended access by young children.

# Hager Desire








- Complies with IEC 60669-1 CB certificate
- 'AX' rated - No need to derate for fluorescent loads
- 16 AX (200W Self Ballasted Lamp (SBL) )
- Supplied with M3.5 x 25 mm long fixing screws
- Two way switches can be wired either 1 way or 2 way
- Capacity of each terminal:  
For 16AX/10A:  
3 x 1.5 mm<sup>2</sup>  
2 X 2.5 mm<sup>2</sup>  
For 20AX DP:  
2 X 4 mm<sup>2</sup>
- Terminal markings denote:  
L1 = one way  
L2 = two way  
L = common
- Material: Polycarbonate

		Description	Pack qty.	Cat. Ref. White	Cat. Ref. Knight Black
					
 WGFL111		<b>Large dolly switch</b>  16AX, 1 gang 1 way  16AX, 1 gang 2 way  16AX, 2 gang 1 way  16AX, 2 gang 2 way  16AX, 3 gang 1 way  16AX, 3 gang 2 way  16AX, 4 gang 2 way	10	<b>WGFL111</b>	<b>WGFL111KB</b>
 WGFL121				<b>WGFL112</b>	<b>WGFL112KB</b>
 WGFL131				<b>WGFL121</b>	<b>WGFL121KB</b>
 WGFL142				<b>WGFL122</b>	<b>WGFL122KB</b>
				<b>WGFL131</b>	<b>WGFL131KB</b>
				<b>WGFL132</b>	<b>WGFL132KB</b>
				<b>WGFL142</b>	<b>WGFL142KB</b>
 WGFL111B		10A, 1 gang bell switch mark "bell symbol"	10	<b>WGFL111B</b>	<b>WGFL111BKB</b>
 WGFL2D1N		<b>DP switch</b>  20AX, 1 gang with LED	10	<b>WGFL2D1N</b>	<b>WGFL2D1NKB</b>
<b>VAS (Value Added Service) *Please refer Hager</b>					
<u>Special marks</u>		<u>Abbreviation</u>			
"HOB"		HB			
"HOOD"		HD			
"WATER HEATER"		WH			
"SOLAR HEATER"		SH			
"BOOSTER PUMP"		BP			
"AIR CONDITIONER"		AC			
Example: "WATER HEATER" WH					
20AX 1 gang with LED				<b>WGFL2D1NWH</b>	<b>WGFL2D1NKBWH</b>










- Complies with BS1363 for 13A, MS1577 for 15A
- Supplied with M3.5 x 25 mm long fixing screws
- Capacity of each terminal: L, N, E : 3 X 4 mm²
- Integral rocker design of switched sockets provides clear red 'on' indication
- Material: Polycarbonate

		Description	Pack qty.	Cat. Ref. White	Cat. Ref. Knight Black
					
		<b>13A Socket outlets</b>			
 <div>WGFS113S      WGFS113S1USB</div>		13A single switched	10	<b>WGFS113S</b>	<b>WGFS113SKB</b>
		13A single switched + 1 x USB charger	8	<b>WGFS113S1USB</b>	<b>WGFS113S1USBKB</b>
		13A twin switched	5	<b>WGFS213S</b>	<b>WGFS213SKB</b>
 <div>WGFS213S</div>					
		<b>15A Socket outlets</b>			
 <div>WGFS115S</div>		15A round pin switched	10	<b>WGFS115S</b>	<b>WGFS115SKB</b>



- Supplied with M3.5 x 25 mm long fixing screws
- Material: Polycarbonate





		Description	Pack qty.	Cat. Ref. White	Cat. Ref. Knight Black
					
<b>Data / TV</b>					
		Single RJ45 Data Outlet Cat6	10	<b>WGFT1RJ6</b>	<b>WGFT1RJ6KB</b>
WGFT1RJ6	WGFT1TV	Single TV Inlet/Outlet	10	<b>WGFT1TV</b>	<b>WGFT1TVKB</b>
		Single TV Outlet F Type	10	<b>WGFT1TVF</b>	<b>WGFT1TVFKB</b>
		Twin TV Inlet/Outlet + RJ45 Cat6	10	<b>WGFT2TVRJ6</b>	<b>WGFT2TVRJ6KB</b>
WGFT1TVF	WGFT2TVRJ6	Twin TV Outlet F Type + RJ45 Cat6	10	<b>WGFT2TVFRJ6</b>	<b>WGFT2TVFRJ6KB</b>
					
WGFT2TVFRJ6					

- Complies with  
BS 5733  
IEC 60998-1  
IEC 60998-2-1

- Supplied with M3.5 x 25 mm  
long fixing screws

- Capacity of each terminal:  
L, N, E : 4 X 2.5 mm<sup>2</sup>  
2 X 4.0 mm<sup>2</sup>  
1 X 6.0 mm<sup>2</sup>

- Material: Polycarbonate

	Description	Pack qty.	Cat. Ref. White	Cat. Ref. Knight Black
				
 WGFR25	<b>Connection unit</b>			
	25A with flex outlet	10	<b>WGFR25</b>	<b>WGFR25KB</b>
 WGFVE3	<b>Accommodation plate</b>			
	3 mods, 67.5mm x 45mm	20	<b>WGFVE3</b>	<b>WGFVE3KB</b>







**Hager Engineering (M) Sdn Bhd**

K03-10-08, UOA Business Park,  
No.1 Jalan Pengaturcara U1/51A,  
40150 Shah Alam, Selangor,  
Malaysia

Tel : + (60) 3 5569 0727  
Fax : + (60) 3 5569 0728  
Email : [generalmy@hager.com](mailto:generalmy@hager.com)

[hager.my](http://hager.my)

Start your  
digital journey



**Warranty:**

A warranty period of 10 years\* is offered on Hager products, from date of manufacture, relating to any material or manufacturing defect.

The warranty is void if:

After inspection by Hager technical support department the device is found to have been installed in a manner which is contrary to IEC wiring regulations and accepted practice within the industry at the time of installation.

Warranty does not include damages or scratches caused due to inappropriate cleaning or use of any abrasive material.

An explanation of defect must be included when returning the goods.

\* Excludes electronic products, which have a warranty of 2 years.