

Hager Dream  
wiring accessories


# live your Dream



:hager



**Dream  
with  
ambition**



# Frameless design

The ultra-slim, frameless design allows the switch to be integrated into the wall; the simple and large panel makes the contact easy, and each touch creates the most pleasant moment.







# Hidden LED

Soft and discrete LED light to locate the switch as soon as you enter the room. No need to feel your way in the dark. Guided by the LED light, experience the convenience and safety.





# Multiple choices of color for your switch

Pursue uniqueness and elegance, white, elegant gold, interstellar grey, noble bronze and knight black, the color tone personifies the style and poise.





# Expert tips



**01**

## Frameless design

The ultrathin and frameless appearance design makes the switch integrate with the wall into an integral whole; the simple but huge rocker makes contact very easy, and each touch creates the most touching moment.



**02**

## Hidden LED

Soft and distinguishable LED light, you can find where the switch is located as soon as you enter the room, and you needn't feel your way in the dark to get up in the night. Guided by LED light, you will experience convenience and safety.



**03**

## Identification for power

humanized delayed power off is designed, which save power in a smart way. The insert tag switch has LED indicator, which makes it easy for you to find the slot in the dark. After power on, the indicator will turn off automatically.



**04**

## Noise reduction design

Noise reduction is designed for the large switch panel, which embodies the sound and hand feeling of the products imported from Europe. The design idea from multi-dimensions such as impression, light perception, sense of touch, and phonoreception makes the large rocker perfect.

**05**

## U type screwed terminals

Capacity of terminal can fit 2 x 4mm<sup>2</sup> or 3 x 2.5mm<sup>2</sup> flexible/ rigid wire. However, it is easy to wiring, high efficient for installation.

**06**

## Beehive-like support

Beehive structure has the advantages of super-strong intensity and light weight. It is accurately used for the installing support of the product, which makes it more firm, durable, and not deformed over time.



**07**

## Color-changeable switch ring

The switch rings of Dream series can change colors to match the interior decoration as you like, providing more possibilities for the overall design.



**08**

## IP55 waterproof box

The waterproof and dustproof functions reach the high waterproof level of IP55. The design of a transparent large space box provides more space for the power cable to turn naturally, realizing real waterproof at power consumption.



**09**

## Safety and stability

The international standard rated current of switch is 16AX, which ensures safer and more stable use of the switch.



**10**

#### Shutter

Having safety awareness all the time comes from the care for every family member. The socket panel is designed with child lock. Source isolating safety shutter is installed at the jacks to prevent children from putting their single finger in. It can completely block current.



**11**

#### Monobloc rocker & frame design

Rocker and the frame can be taken out by one time only, easy for installation. This is a perfect alignment of rockers all the time.



**12**

USB C + C / USB A + C socket outlet  
Charge up to three devices at once—no extra adapters needed. Available in single and twin switched versions.



**13**

Grade II safety isolating transformer is used, which makes transformation safer and products more durable.



**14**

#### Dust-protection Cover

Dust-protection cover is supplied for each product. It can be used for protecting the dust during decorating, keeping the product clean.



**15**

Ensuring communication quality  
The network socket ensures communication quality.



**16**

#### Eco-packaging

We adhere to environmental philosophy all the time and won international iF design award for the











**17**




Designed by European master  
Designed by Erwin van Handenhoven, who has won many international awards.














- Complies with BS EN 60669-1 IEC 60669-1 CB certificate
- 'AX' rated - No need to derate for fluorescent loads
- 10 AX (100W Self Ballasted Lamp (SBL) )
- 16 AX (200W Self Ballasted Lamp (SBL) )
- Supplied with M3.5 x 37 mm long fixing screws
- Capacity of each terminal: 3 x 1.5 mm<sup>2</sup> 2 X 2.5 mm<sup>2</sup>
- Two way switches can be wired either 1 way or 2 way
- Terminal markings denote: L1 = one way L2 = two way C = common
- Material: Polycarbonate

Description		Pack qty.	Cat. Ref. White	Cat. Ref. Interstellar Grey	Cat. Ref. Noble Bronze	Cat. Ref. Knight Black	Cat. Ref. Elegant Gold
<b>Large dolly switch</b>							
 WGDL111	16AX, 1 gang 1 way	10	WGDL111	WGDL111IG	WGDL111NB	WGDL111KB	WGDL111EG
 WGDL121 WGDL122	16AX, 1 gang 2 way	10	WGDL112	WGDL112IG	WGDL112NB	WGDL112KB	WGDL112EG
	16AX, 2 gang 1 way	10	WGDL121	WGDL121IG	WGDL121NB	WGDL121KB	WGDL121EG
	16AX, 2 gang 2 way	10	WGDL122	WGDL122IG	WGDL122NB	WGDL122KB	WGDL122EG
 WGDL131	16AX, 3 gang 1 way	10	WGDL131	WGDL131IG	WGDL131NB	WGDL131KB	WGDL131EG
 WGDL141 WGDL142	16AX, 3 gang 2 way	10	WGDL132	WGDL132IG	WGDL132NB	WGDL132KB	WGDL132EG
	16AX, 4 gang 1 way	10	WGDL141	WGDL141IG	WGDL141NB	WGDL141KB	WGDL141EG
	16AX, 4 gang 2 way	10	WGDL142	WGDL142IG	WGDL142NB	WGDL142KB	WGDL142EG








<b>Large dolly switch with LED</b>							
 WGDL111N	16AX, 1 gang 1 way	10	WGDL111N	WGDL111NIG	WGDL111NNB	WGDL111NKB	WGDL111NEG
 WGDL121N WGDL122N	16AX, 1 gang 2 way	10	WGDL112N	WGDL112NIG	WGDL112NNB	WGDL112NKB	WGDL112NEG
	16AX, 2 gang 1 way	10	WGDL121N	WGDL121NIG	WGDL121NNB	WGDL121NKB	WGDL121NEG
	16AX, 2 gang 2 way	10	WGDL122N	WGDL122NIG	WGDL122NNB	WGDL122NKB	WGDL122NEG
 WGDL131N	16AX, 3 gang 1 way	10	WGDL131N	WGDL131NIG	WGDL131NNB	WGDL131NKB	WGDL131NEG
 WGDL132N	16AX, 3 gang 2 way	10	WGDL132N	WGDL132NIG	WGDL132NNB	WGDL132NKB	WGDL132NEG

<b>Large dolly switch</b>							
 WGDL113	10AX, 1 gang, intermediate	10	WGDL113	WGDL113IG	WGDL113NB	WGDL113KB	WGDL113EG
 WGDL111B	10A, 1 gang, bell switch mark Bell symbol	10	WGDL111B	WGDL111BIG	WGDL111BNB	WGDL111BKB	WGDL111BEG
 WGDL111E	10A, 1 gang, press switch mark "EXIT"	10	WGDL111E	WGDL111EIG	WGDL111ENB	WGDL111EKB	WGDL111EEG

		Description	Pack qty.	Cat. Ref. White	Cat. Ref. Interstellar Grey	Cat. Ref. Noble Bronze	Cat. Ref. Knight Black	Cat. Ref. Elegant Gold
								
		<b>Press switch</b>						
 WGDL111P WGDL111NP	 WGDL111NP-12V	10A, 1 gang	10	<b>WGDL111P</b>	<b>WGDL111PIG</b>	<b>WGDL111PNB</b>	<b>WGDL111PKB</b>	<b>WGDL111PEG</b>
		10A, 2 gang	10	<b>WGDL121P</b>	<b>WGDL121PIG</b>	<b>WGDL121PNB</b>	<b>WGDL121PKB</b>	<b>WGDL121PEG</b>
		10A, 3 gang	10	<b>WGDL131P</b>	<b>WGDL131PIG</b>	<b>WGDL131PNB</b>	<b>WGDL131PKB</b>	<b>WGDL131PEG</b>
		<b>Press switch with 220V LED</b>						
 WGDL121P WGDL121NP	 WGDL121NP-12V	10A, 1 gang	10	<b>WGDL111NP</b>	<b>WGDL111NPIG</b>	<b>WGDL111NPNB</b>	<b>WGDL111NPKB</b>	<b>WGDL111NPEG</b>
		10A, 2 gang	10	<b>WGDL121NP</b>	<b>WGDL121NPIG</b>	<b>WGDL121NPNB</b>	<b>WGDL121NPKB</b>	<b>WGDL121NPEG</b>
		10A, 3 gang	10	<b>WGDL131NP</b>	<b>WGDL131NPIG</b>	<b>WGDL131NPNB</b>	<b>WGDL131NPKB</b>	<b>WGDL131NPEG</b>
		<b>Press switch with 12V LED</b>						
 WGDL131P WGDL131NP	 WGDL131NP-12V	10A, 1 gang	10	<b>WGDL111NP-12V</b>	<b>WGDL111NP-12VIG</b>	<b>WGDL111NP-12VNB</b>	<b>WGDL111NP-12VKB</b>	<b>WGDL111NP-12VEG</b>
		10A, 2 gang	10	<b>WGDL121NP-12V</b>	<b>WGDL121NP-12VIG</b>	<b>WGDL121NP-12VNB</b>	<b>WGDL121NP-12VKB</b>	<b>WGDL121NP-12VEG</b>
		10A, 3 gang	10	<b>WGDL131NP-12V</b>	<b>WGDL131NP-12VIG</b>	<b>WGDL131NP-12VNB</b>	<b>WGDL131NP-12VKB</b>	<b>WGDL131NP-12VEG</b>

## Hager Dream Dimmer and fan controller switches

- Complies with BS EN 60669-2-1 IEC 60669-2-1
- Supplied with M3.5 x 37 mm long fixing screws
- Capacity of each terminal: 3 x 1.5 mm<sup>2</sup>
- Material: Polycarbonate

		Description	Pack qty.	Cat. Ref. White	Cat. Ref. Interstellar Grey	Cat. Ref. Noble Bronze	Cat. Ref Knight Black	Cat. Ref Elegant Gold
								
		<b>Dimmer</b>						
		40-500W single, 2 way	6	<b>WGDEDR500</b>	<b>WGDEDR500IG</b>	<b>WGDEDR500NB</b>	<b>WGDEDR500KB</b>	<b>WGDEDR500EG</b>
<b>Fan control</b>								
250VA, single		6	<b>WGDEFR250</b>	<b>WGDEFR250IG</b>	<b>WGDEFR250NB</b>	<b>WGDEFR250KB</b>	<b>WGDEFR250EG</b>	

- Complies with  
BS EN 60669-1  
IEC 60669-1  
CB certificate

- 20 AX  
(250W Self Ballasted Lamp (SBL) )

- Supplied with M3.5 x 37 mm  
long fixing screws

- Capacity of each terminal:

**20AX**



L, N, E: 2 x 4 mm<sup>2</sup>

**32A, 45A**

L, N : 2.5 mm<sup>2</sup> ~ 16 mm<sup>2</sup>

E x 2 : 2.5 mm<sup>2</sup> ~ 16 mm<sup>2</sup>



- Material: Polycarbonate

	Description	Pack qty.	Cat. Ref. White	Cat. Ref. Interstellar Grey	Cat. Ref. Noble Bronze	Cat. Ref. Knight Black	Cat. Ref. Elegant Gold
	<b>DP switch</b> 20AX 1 gang 8	8	<b>WGDL2D1</b>	<b>WGDL2D1IG</b>	<b>WGDL2D1NB</b>	<b>WGDL2D1KB</b>	<b>WGDL2D1EG</b>
	20AX 2 gang 8	8	<b>WGDL2D2</b>	<b>WGDL2D2IG</b>	<b>WGDL2D2NB</b>	<b>WGDL2D2KB</b>	<b>WGDL2D2EG</b>

WGDL2D1

WGDL2D2

*Remark: Grey reference product - coming soon*

	<b>DP switch with LED</b>						
	20AX 1 gang 8	8	<b>WGDL2D1N</b>	<b>WGDL2D1NIG</b>	<b>WGDL2D1NNB</b>	<b>WGDL2D1NKB</b>	<b>WGDL2D1NEG</b>
	20AX 2 gang 8	8	<b>WGDL2D2N</b>	<b>WGDL2D2NIG</b>	<b>WGDL2D2NNB</b>	<b>WGDL2D2NKB</b>	<b>WGDL2D2NEG</b>
WGDL2D1N WGDL2D12N	20AX 1 gang 8 2 way	8	<b>WGDL2D12N</b>	<b>WGDL2D12NIG</b>	<b>WGDL2D12NNB</b>	<b>WGDL2D12NKB</b>	<b>WGDL2D12NEG</b>

WGDL2D1N  
WGDL2D12N

WGDL2D2N

Special marks	Abbreviation	Special marks	Abbreviation	Special marks	Abbreviation
"AIR CONDITONER"	AC	"HOB"	HB	"WASHER"	WS
"DISH WASHER"	DW	"HOOD"	HD	"WASHING MACHINE"	WM
"DRYER"	DR	"MICROWAVE"	MW	"WATER HEATER"	WH
"FRIDGE"	FR	"OVEN"	OV		

Example: **"WATER HEATER" WH**

20AX 1 gang **WGDL2D1WH WGDL2D1IGWH WGDL2D1NBWH WGDL2D1KBWH WGDL2D1EGWH**

	<b>Control switch with LED</b>						
	32A DP 8	8	<b>WGDR32D1</b>	<b>WGDR32D1IG</b>	<b>WGDR32D1NB</b>	<b>WGDR32D1KB</b>	<b>WGDR32D1EG</b>
	45A DP 8	8	<b>WGDR45D1</b>	<b>WGDR45D1IG</b>	<b>WGDR45D1NB</b>	<b>WGDR45D1KB</b>	<b>WGDR45D1EG</b>

WGDR32D1

WGDR45D1










- Complies with  
BS 5733  
IEC 60998-1  
IEC 60998-2-1  
BS 1363-4 (Fused connection units)

- Supplied with M3.5 x 37 mm  
long fixing screws


- Capacity of each terminal:  
**25A**  
L, N, E: 4 x 2.5 mm<sup>2</sup> or 2 x 4 mm<sup>2</sup>  
or 1 x 6 mm<sup>2</sup>

**13A FCU**  
L, N : 3 x 4.0 mm<sup>2</sup>  
E : 2 x 4.0 mm<sup>2</sup>

- Material: polycarbonate
- |   | Description                                       | Pack<br>qty. | Cat. Ref.<br>White  | Cat. Ref.<br>Interstellar<br>Grey   | Cat. Ref.<br>Noble<br>Bronze   | Cat. Ref<br>Knight<br>Black   | Cat. Ref<br>Elegant<br>Gold   |
|---|---|--------------|---|---|--|---|---|
|   |   |              |  |  |  |  |  |
|  | <b>Connection unit</b><br>25A with<br>flex outlet | 12           | <b>WGDR25</b>   | <b>WGDR25IG</b>   | <b>WGDR25NB</b>  | <b>WGDR25KB</b>   | <b>WGDR25EG</b>   |

WGDR25
- | Fused connection unit  |                                      |    |                |                  |                  |                  |                  |
|--|--------------------------------------|----|----------------|------------------|------------------|------------------|------------------|
|  | 13A fused<br>w/ LED +<br>flex outlet | 10 | <b>WGDR13N</b> | <b>WGDR13NIG</b> | <b>WGDR13NNB</b> | <b>WGDR13NKB</b> | <b>WGDR13NEG</b> |

WGDR13N

	13A switched fused w/ flex outlet w/ LED	10	<b>WGDR13SN</b>	<b>WGDR13SNIG</b>	<b>WGDR13SNNB</b>	<b>WGDR13SNKB</b>	<b>WGDR13SNEG</b>
---	---	----	-----------------	-------------------	-------------------	-------------------	-------------------

WGDR13SN
- Remark: Grey reference product - coming soon
- Subject to change without prior notice

15

## Hager Dream

### 5A and 10A socket outlets





- Complies with  
BS 547 (5A socket)  
SS 472 (5A socket)  
IEC 60884-1(10A socket)

- Supplied with M3.5 x 37 mm  
long fixing screws

- Capacity of each terminal:  
L, N, E : 3 X 2.5 mm<sup>2</sup> or  
2 X 4.0 mm<sup>2</sup>

- Integral rocker design of  
switched sockets provides  
clear red 'on' indication

- Material: Polycarbonate

	Description	Pack qty.	Cat. Ref. White	Cat. Ref. Interstellar Grey	Cat. Ref. Noble Bronze	Cat. Ref Knight Black	Cat. Ref Elegant Gold
	<b>Socket outlet</b> 5A round pin switched	8	<b>WGDS105S</b>	<b>WGDS105SIG</b>	<b>WGDS105SNB</b>	<b>WGDS105SKB</b>	<b>WGDS105SEG</b>
	10A 2 pin switched	10	<b>WGDS110US</b>	<b>WGDS110USIG</b>	<b>WGDS110USNB</b>	<b>WGDS110USKB</b>	<b>WGDS110USEG</b>

WGDS105S

WGDS110US

*Remark: Grey reference product - coming soon*

## Hager Dream

### 13A socket outlets









- Complies with  
BS 1363-2  
SS 145-2

- Supplied with M3.5 x 37 mm  
long fixing screws

- Capacity of each terminal:  
L, N, E : 3 X 2.5 mm<sup>2</sup> or  
2 X 4.0 mm<sup>2</sup>

- USB output current  
2.4A (Max)

- Material: Polycarbonate

	Description	Pack qty.	Cat. Ref. White	Cat. Ref. Interstellar Grey	Cat. Ref. Noble Bronze	Cat. Ref Knight Black	Cat. Ref Elegant Gold
	13A single	10	<b>WGDS113</b>	<b>WGDS113IG</b>	<b>WGDS113NB</b>	<b>WGDS113KB</b>	<b>WGDS113EG</b>
	13A single switched	10	<b>WGDS113S</b>	<b>WGDS113SIG</b>	<b>WGDS113SNB</b>	<b>WGDS113SKB</b>	<b>WGDS113SEG</b>
	13A single switched w/ LED	10	<b>WGDS113N</b>	<b>WGDS113NIG</b>	<b>WGDS113NNB</b>	<b>WGDS113NKB</b>	<b>WGDS113NEG</b>
	13A single switched 2 x USB chargers	8	<b>WGDS113SUSB</b>	<b>WGDS113SUSBIG</b>	<b>WGDS113SUSBNB</b>	<b>WGDS113SUSBKB</b>	<b>WGDS113SUSBEG</b>
	13A twin	10	<b>WGDS213</b>	<b>WGDS213IG</b>	<b>WGDS213NB</b>	<b>WGDS213KB</b>	<b>WGDS213EG</b>
	13A twin switched	10	<b>WGDS213S</b>	<b>WGDS213SIG</b>	<b>WGDS213SNB</b>	<b>WGDS213SKB</b>	<b>WGDS213SEG</b>
	13A twin switched w/ LED	10	<b>WGDS213N</b>	<b>WGDS213NIG</b>	<b>WGDS213NNB</b>	<b>WGDS213NKB</b>	<b>WGDS213NEG</b>
	13A twin switched 2 x USB chargers	10	<b>WGDS213SUSB</b>	<b>WGDS213SUSBIG</b>	<b>WGDS213SUSBNB</b>	<b>WGDS213SUSBKB</b>	<b>WGDS213SUSBEG</b>

WGDS113

WGDS113S

WGDS113N

WGDS113SUSB

WGDS213

WGDS213S

WGDS213N

WGDS213SUSB

*Remark: Grey reference product - coming soon*



WGDS113SUSBAC



WGDS213SUSBAC



WGDS113SUSBCC



WGDS213SUSBCC

Description	Pack qty.	Cat. Ref. White	Cat. Ref. Interstellar Grey	Cat. Ref. Noble Bronze	Cat. Ref. Knight Black	Cat. Ref. Elegant Gold
13A single switched 2 x USB A + C	8	WGDS113SUSBAC	WGDS113SUSBACIG	WGDS113SUSBACNB	WGDS113SUSBACBK	WGDS113SUSBACEG
13A twin switched 2 x USB A + C	coming soon					
13A single switched 2 x USB C + C	8	WGDS113SUSBCC	WGDS113SUSBCCIG	WGDS113SUSBCCNB	WGDS113SUSBCCBK	WGDS113SUSBCCEG
13A twin switched 2 x USB C + C	5	WGDS213SUSBCC	WGDS213SUSBCCIG	WGDS213SUSBCCNB	WGDS213SUSBCCBK	WGDS213SUSBCCEG
16A German socket w/ shutter	8	<b>WGDS116S</b>	<b>WGDS116SIG</b>	<b>WGDS116SNB</b>	<b>WGDS116SKB</b>	<b>WGDS116SEG</b>

## Hager Dream 15A and 16A socket outlets

- Complies with  
BS 546 (15A socket)  
SS 472 (15A socket)  
IEC 60884-1 (16A German socket)

- Supplied with M3.5 x 37 mm  
long fixing screws

- Capacity of each terminal:  
L, N, E : 3 X 2.5 mm<sup>2</sup> or  
2 X 4.0 mm<sup>2</sup>

- USB output current  
2.4A (Max)

- Integral rocker design of  
switched sockets provides  
clear red 'on' indication

- Material: Polycarbonate



WGDS115S



WGDS116S

Description	Pack qty.	Cat. Ref. White	Cat. Ref. Interstellar Grey	Cat. Ref. Noble Bronze	Cat. Ref. Knight Black	Cat. Ref. Elegant Gold
15A round pin switched	8	<b>WGDS115S</b>	<b>WGDS115SIG</b>	<b>WGDS115SNB</b>	<b>WGDS115SKB</b>	<b>WGDS115SEG</b>
16A German socket w/ shutter	8	<b>WGDS116S</b>	<b>WGDS116SIG</b>	<b>WGDS116SNB</b>	<b>WGDS116SKB</b>	<b>WGDS116SEG</b>



- Supplied with M3.5 x 37 mm  
long fixing screws

- Material: Polycarbonate

















		Description	Pack qty.	Cat. Ref. White	Cat. Ref. Interstellar Grey	Cat. Ref. Noble Bronze	Cat. Ref. Knight Black	Cat. Ref. Elegant Gold
		<b>RJ11 outlet</b>						
		1 mod	10	<b>WGDT1RJ</b>	<b>WGDT1RJIG</b>	<b>WGDT1RJNB</b>	<b>WGDT1RJKB</b>	<b>WGDT1RJEJ</b>
		2 mod	10	<b>WGDT2RJ</b>	<b>WGDT2RJIG</b>	<b>WGDT2RJNB</b>	<b>WGDT2RJKB</b>	<b>WGDT2RJEJ</b>
		<b>RJ45 outlet loose plate</b>						
		1 mod	20	<b>WGDT1RJ6LP</b>	<b>WGDT1RJ6LPIG</b>	<b>WGDT1RJ6LPNB</b>	<b>WGDT1RJ6LPKB</b>	<b>WGDT1RJ6LPEG</b>
		1 mod without symbol	20	<b>WGDT1RJ6LPNM</b>	<b>WGDT1RJ6LPNMIG</b>	<b>WGDT1RJ6LPNMNB</b>	<b>WGDT1RJ6LPNMKB</b>	<b>WGDT1RJ6LPNMEG</b>
		2 mod	20	<b>WGDT2RJ6LP</b>	<b>WGDT2RJ6LPIG</b>	<b>WGDT2RJ6LPNB</b>	<b>WGDT2RJ6LPKB</b>	<b>WGDT2RJ6LPEG</b>
		2 mod without symbol	20	<b>WGDT2RJ6LPNM</b>	<b>WGDT2RJ6LPNMIG</b>	<b>WGDT2RJ6LPNMNB</b>	<b>WGDT2RJ6LPNMKB</b>	<b>WGDT2RJ6LPNMEG</b>
		<b>Accommodation plate</b> SMATV plate 30		<b>WGDTSMATV</b>	<b>WGDTSMATVIG</b>	<b>WGDTSMATVNB</b>	<b>WGDTSMATVKB</b>	<b>WGDTSMATVEJ</b>
		<b>RJ45 cat6 outlet</b>						
		1 mod	10	<b>WGDT1RJ6</b>	<b>WGDT1RJ6IG</b>	<b>WGDT1RJ6NB</b>	<b>WGDT1RJ6KB</b>	<b>WGDT1RJ6EG</b>
		1 mod without symbol	10	<b>WGDT1RJ6NM</b>	<b>WGDT1RJ6NMIG</b>	<b>WGDT1RJ6NMNB</b>	<b>WGDT1RJ6NMKB</b>	<b>WGDT1RJ6NMEG</b>
		2 mod	10	<b>WGDT2RJ6</b>	<b>WGDT2RJ6IG</b>	<b>WGDT2RJ6NB</b>	<b>WGDT2RJ6KB</b>	<b>WGDT2RJ6EG</b>
		2 mod without symbol	10	<b>WGDT2RJ6NM</b>	<b>WGDT2RJ6NMIG</b>	<b>WGDT2RJ6NMNB</b>	<b>WGDT2RJ6NMKB</b>	<b>WGDT2RJ6NMEG</b>
		<b>RJ45 cat5e outlet</b>						
		1 mod	10	<b>WGDT1RJ5</b>	<b>WGDT1RJ5IG</b>	<b>WGDT1RJ5NB</b>	<b>WGDT1RJ5KB</b>	<b>WGDT1RJ5EG</b>
		2 mod	10	<b>WGDT2RJ5</b>	<b>WGDT2RJ5IG</b>	<b>WGDT2RJ5NB</b>	<b>WGDT2RJ5KB</b>	<b>WGDT2RJ5EG</b>
		<b>RJ11 + RJ45 cat5e outlet</b>						
		2 mod	10	<b>WGDT2RJRJ5</b>	<b>WGDT2RJRJ5IG</b>	<b>WGDT2RJRJ5NB</b>	<b>WGDT2RJRJ5KB</b>	<b>WGDT2RJRJ5EG</b>
		<b>RJ11 + RJ45 cat6 outlet</b>						
		2 mod	10	<b>WGDT2RJRJ6</b>	<b>WGDT2RJRJ6IG</b>	<b>WGDT2RJRJ6NB</b>	<b>WGDT2RJRJ6KB</b>	<b>WGDT2RJRJ6EG</b>
		<b>TV inlet/outlet + RJ45 cat5e</b>						
		2 mod	10	<b>WGDT2TVRJ5</b>	<b>WGDT2TVRJ5IG</b>	<b>WGDT2TVRJ5NB</b>	<b>WGDT2TVRJ5KB</b>	<b>WGDT2TVRJ5EG</b>
		<b>TV inlet/outlet</b>						
		1 mod	10	<b>WGDT1TV</b>	<b>WGDT1TVIG</b>	<b>WGDT1TVNB</b>	<b>WGDT1TVKB</b>	<b>WGDT1TVEJ</b>
		<b>TV inlet/outlet + RJ45 cat6</b>						
		2 mod	10	<b>WGDT2TVRJ6M</b>	<b>WGDT2TVRJ6IGM</b>	<b>WGDT2TVRJ6NBM</b>	<b>WGDT2TVRJ6KBM</b>	<b>WGDT2TVRJ6EGM</b>
		<b>TV outlet, F type</b>						
		1 mod	10	<b>WGDT1TVF</b>	<b>WGDT1TVFIG</b>	<b>WGDT1TVFNB</b>	<b>WGDT1TVFKB</b>	<b>WGDT1TVFEG</b>
		<b>TV outlet, F type + RJ45</b>						
		2 mod	10	<b>WGDT2TVFRJ6M</b>	<b>WGDT2TVFRJ6IGM</b>	<b>WGDT2TVFRJ6NBM</b>	<b>WGDT2TVFRJ6KBM</b>	<b>WGDT2TVFRJ6EGM</b>

- Complies with  
IEC 60669-1  
IEC 60669-2-1  
IEC 61558-2-5 (shaver)  
IEC 62368-1 (USB)

- 16 AX  
(200W Self Ballasted Lamp (SBL) )

- Supplied with M3.5 x 37 mm  
long fixing screws

- Material: Polycarbonate

	Description	Pack qty.	Cat. Ref. White	Cat. Ref. Interstellar Grey	Cat. Ref. Noble Bronze	Cat. Ref. Knight Black	Cat. Ref. Elegant Gold
							
	16AX DND & 8 MUR with LED (Indoor)	8	<b>WGDHDC</b>	<b>WGDHDCIG</b>	<b>WGDHDCNB</b>	<b>WGDHDCCKB</b>	<b>WGDHDCEG</b>
	4A DND & 10 MUR indicator w/ bell switch	10	<b>WGDHBD</b>	<b>WGDHBDIG</b>	<b>WGDHBDNB</b>	<b>WGDHBDKB</b>	<b>WGDHBDEG</b>
	16A key tag - mechanical	6	<b>WGDHKT</b>	<b>WGDHKTIG</b>	<b>WGDHKTNB</b>	<b>WGDHKTMB</b>	<b>WGDHKTMEG</b>
	16A key tag - RFID	6	<b>WGDHKTRFID</b>	<b>WGDHKTRFIDIG</b>	<b>WGDHKTRFIDNB</b>	<b>WGDHKTRFIDKB</b>	<b>WGDHKTRFIDEG</b>
	<b>HDMI+VGA</b>	10	<b>WGDHHIVA</b>	<b>WGDHHIVAIG</b>	<b>WGDHHIVANB</b>	<b>WGDHHIVAKB</b>	<b>WGDHHIVAEG</b>
	<b>USB chargers</b>						
	USB charger x 3 (4.2A)	8	<b>WGDS3USB</b>	<b>WGDS3USBIG</b>	<b>WGDS3USBNB</b>	<b>WGDS3USBKB</b>	<b>WGDS3USBEG</b>
	<b>USB + 3.5mm audio</b>	10	<b>WGDHUSB35</b>	<b>WGDHUSB35IG</b>	<b>WGDHUSB35NB</b>	<b>WGDHUSB35KB</b>	<b>WGDHUSB35EG</b>
	<b>Emergency switch</b>	8	<b>WGDEE1</b>	<b>WGDEE1IG</b>	<b>WGDEE1NB</b>	<b>WGDEE1KB</b>	<b>WGDEE1EG</b>
	<b>Audio switch</b>	6	<b>WGDEA6</b>	<b>WGDEA6IG</b>	<b>WGDEA6NB</b>	<b>WGDEA6KB</b>	<b>WGDEA6EG</b>
	<b>Sleeping light</b>	8	<b>WGDHSL</b>	<b>WGDHSLIG</b>	<b>WGDHSLNB</b>	<b>WGDHSLKB</b>	<b>WGDHSLEG</b>
	<b>Shaver socket</b>	1	<b>WGDHSR</b>	<b>WGDHSRIG</b>	<b>WGDHSRNB</b>	<b>WGDHSRKB</b>	<b>WGDHSREG</b>

	Description	Pack qty.	Cat. Ref. White	Cat. Ref. Interstellar Grey	Cat. Ref. Noble Bronze	Cat. Ref. Knight Black	Cat. Ref. Elegant Gold
<p>WGDC2</p> <p>WGDC3</p> <p>WGDC4</p> <p>WGDC5</p>	<b>Multi-gang frame</b>						
	2 gang horizontal	18	<b>WGDC2</b>	<b>WGDC2IG</b>	<b>WGDC2NB</b>	<b>WGDC2KB</b>	<b>WGDC2EG</b>
	3 gang horizontal	12	<b>WGDC3</b>	<b>WGDC3IG</b>	<b>WGDC3NB</b>	<b>WGDC3KB</b>	<b>WGDC3EG</b>
	4 gang horizontal	12	<b>WGDC4</b>	<b>WGDC4IG</b>	<b>WGDC4NB</b>	<b>WGDC4KB</b>	<b>WGDC4EG</b>
	5 gang horizontal	9	<b>WGDC5</b>	<b>WGDC5IG</b>	<b>WGDC5NB</b>	<b>WGDC5KB</b>	<b>WGDC5EG</b>
<p>WGDBP1</p>	<b>Blank plate</b>						
	1 gang	20	<b>WGDBP1</b>	<b>WGDBP1IG</b>	<b>WGDBP1NB</b>	<b>WGDBP1KB</b>	<b>WGDBP1EG</b>
<p>WGDE2</p>	<b>Accommodation plate</b>						
	1 gang 2 modules	12	<b>WGDE2</b>	<b>WGDE2IG</b>	<b>WGDE2NB</b>	<b>WGDE2KB</b>	<b>WGDE2EG</b>
<p>XC9003</p> <p>XC9004</p>	<b>WA covers (Transparent)</b>						
	IP55 single size	40	<b>XC9003</b>				
	IP55 twin size	40	<b>XC9004</b>				

## Doorbell

- Complies with  
IEC 61558-1  
IEC 61558-2-8  
IEC 60335-1

**XC001**  
Dimension:  
105mm (w) x 168mm (h) x 45mm (d)

Power source: 220-240V AC 50Hz  
Transformer output: 6V AC

- Only dingdong sound

	Description	Pack qty.	Cat. Ref.
<p>XC001</p>	<b>Doorbell</b>	1	<b>XC001</b>

# Success cases

The courage to try to innovate in architectural design; the design of excellence always brings together a lot of ideas; the pursuit of the ultimate detail and the admiration of superior quality. Today, whether in Munich, Berlin and Hamburg, or in Bolzano, Madrid and Seoul, these ideas can be traced in any building in the world. It is no coincidence that Hager switches and systems can be found in all of these places.

## China

Sofitel Shenyang Lido, Shenyang  
New World Beijing Hotel, Beijing  
Fairmont Beijing, Beijing  
Marriott Nanjing South Hotel, Nanjing  
Grand Hyatt, Hangzhou  
Park Hyatt Ningbo Resort & Spa, Ningbo  
The Peninsula, Shanghai  
Le Royal Meridien Hotel, Shanghai  
Swissôtel Grand Shanghai, Shanghai  
Mandarin Oriental Pudong, Shanghai  
Sofitel Shanghai Sheshan Oriental, Shanghai  
JW Marriott, Hangzhou  
Four Points by Sheraton Bijie, Guizhou  
Kempinski Hotel, Yinchuan  
New World Wuhan Hotel, Wuhan  
Mandarin Oriental Hotel Guangzhou  
Hyatt Place Shenzhen Airport, Shenzhen  
The Ritz-Carlton, Shenzhen  
InterContinental, Shenzhen  
Swissôtel, Foshan  
Shangri-La's Sanya Resort & Spa, Hainan

## Hong Kong & Macau

Sheraton Hotel Tung Chung  
Island Shangri-La, Hong Kong  
Penta Hotel  
Hotel ICON  
Royal Plaza Hotel  
Ritz Carlton Hotel  
Best Western Hotel (Causeway bay & Tsim Sha Tsui)  
Harbour Grand Hong Kong  
Hyatt Regency Hotel  
Harbourview Horizon Hotel  
Royal View Hotel  
Grand Lisboa Macau  
Studio City Macau  
Galaxy Macau

## Singapore

Grand Hyatt Hotel  
Goodwood Park  
Park Regis  
Ramada & Days Hotel Singapore at Zhongshan Park  
Hotel Fort Canning

## Malaysia

Genting Hotel, Genting Highlands  
JW Marriott Hotel, Kuala Lumpur  
WEIL Hotel Ipoh, Perak  
Alila Bangsar Kuala Lumpur, Kuala Lumpur  
Hilton Garden Inn Puchong, Selangor  
Alwaqf Hotel, Kelantan  
Kimberley Hotel, Penang  
Iconic Hotel, Penang  
VE Hotel & Residence, Bangsar South, Kuala Lumpur

## Indonesia

Westin Hotel, Jakarta  
Courtyard by Marriott, Bali  
Fairfield by Marriott Sunset Road, Bali  
The Ritz-Carlton, Bali Resort & Spa, Bali

## Vietnam

Novotel Nha Trang  
Sealink Phan Thiet  
Sheraton Da Nang  
Radison Blu Cam Ranh  
Movenpick Cam Ranh  
Melia Cam Ranh  
Hanoi Hotel

## India

Taj Palace, Mumbai  
Hyatt Place, Hyderabad  
Ritz Carlton Pune, Pune  
Lemon Tree, 3 hotels (Udaipur, Dehradun, Kolkata)  
Fairfield Marriott Kolkata, Kolkata

## Europe

Hotel Sacher, Vienna  
Hotel Lux Alpinae, St. Anton am Arlberg  
Hotel Schloss Elmau, Elmau  
Vigilius Mountain Resort, Lana  
Hotel Puerta l'America, Madrid  
Lloyd Hotel, Amsterdam  
Zentrum für Virtuelles  
Engineering ZVE, Stuttgart  
Herzogin Anna Amalia Bibliothek, Weimar  
minimum bulthaup, Berlin  
Privathaus, Berlin  
Hyatt Regency, Istanbul  
Şişli Marriott, Istanbul  
Sheraton Ateşehir, Istanbul  
Swissôtel, Istanbul  
Le Meridien, Istanbul  
Hilton, Izmir  
Crowne Plaza, Istanbul

## Other Countries

Sedona Hotel, Mandalay, Myanmar  
Four Seasons Hotel, Seychelles  
Makati Shangri-La Hotel, Manila







**Hager Engineering (M) Sdn Bhd**

K03-10-08, UOA Business Park,  
No.1 Jalan Pengaturcara U1/51A,  
40150 Shah Alam, Selangor,  
Malaysia

Tel : + (60) 3 5569 0727  
Fax : + (60) 3 5569 0728  
Email : [generalmy@hager.com](mailto:generalmy@hager.com)

[hager.com/my](http://hager.com/my)

Start your  
digital journey



**Warranty:**

A warranty period of 10 years\* is offered on Hager products, from date of manufacture, relating to any material or manufacturing defect.

The warranty is void if:

After inspection by Hager technical support department the device is found to have been installed in a manner which is contrary to IEC wiring regulations and accepted practice within the industry at the time of installation.

Warranty does not include damages or scratches caused due to inappropriate cleaning or use of any abrasive material.

An explanation of defect must be included when returning the goods.

\* Excludes electronic products, which have a warranty of 2 years.