

EU Declaration of Conformity No. 26.2177.02.26

We **Hager Electro SAS**
BP3
67215 OBERNAI CEDEX - FRANCE

declare that the product(s)
designation

Accessoires et auxiliaires pour Boîtiers Moulés
accessories and auxiliaries for MCCB's

type reference(s)

HXA, HXB, HXS, HXT, HXV, HXW, HYA, HYB, HYC, HYD, HYS, HYT, HYV, HYW,
HZC, HZC, HZF, HTC, HTD, HTG, SMC
Voir pages suivantes
see next pages

trademark

Hager

is (are) in conformity with the relevant Union harmonization legislation:

- Low Voltage Directive (LVD) No. 2014/35/EU
- Electromagnetic Compatibility Directive (EMCD) No. 2014/30/EU
- Directive on the Restriction of the use of certain Hazardous Substances (RoHS) No. 2011/65/EU amended by No. 2015/863/EU
- Packaging and Packaging Waste Regulation (PPWR) No. 2025/40/EU

.....

.....

Standard number + relevant amendments together with the edition dates and/or relevant document(s)

EN 60947-2 : 2017-10 + A1: 2020-02
EN 60947-5-1 : 2017-12
EN 63000 : 2018-12

If applicable, mention here for radio products, the data about notified body. See RED directive - Annex VI - point 7

We additionally confirm compliance with the EU Directives & Regulations, which are not linked to CE marking (if applicable).
See document DMS103207 'General EU Declaration of Conformity'.

This declaration of conformity is issued under the sole responsibility of the manufacturer.

On behalf of Hager Electro SAS - BP3 - 67215 OBERNAI CEDEX - FRANCE

Name of signatory

Eric BOVIN

Function of signatory

Certification Mandatee

Place and date of issue

Obernai, 15th June 2026

Signature



EU DECLARATION OF CONFORMITY

No. 26.2177.02.26

Type References:

Market Reference	Designation
HXA001H	SHT
HXA002H	SHT
HXA003H	SHT
HXA004H	SHT
HXA005H	SHT
HXA011H	UVR
HXA013H	UVR
HXA014H	UVR
HXA015H	UVR
HXA021H	Auxiliary contact AX
HXA024H	Alarm auxiliary contact AX-AL
HXA025H	Auxiliary contact AX Low Level
HXA026H	Alarm auxiliary contact AX Low Level
HXA027H	Alarm contact NO-NC right side (x630/P630)
HXA028H	Alarm contact-Low level NO-NC right side (x630/P630)
HXA030H	Direct rotary handle
HXA031H	Rotary handle on door
HXA037H	Padlocking kit for std handle
HXA039H	Padlocking kit
HXA051H	Delayed UVR
HXA053H	Delayed UVR
HXA054H	Delayed UVR
HXA055H	Delayed UVR
HXB010H	Set of Four Extended Straight Connections
HXB030H	Direct Rotary Handle
HXB031H	Rotary handle on door
HXB040H	Motor operator with auto-reset (K) = with key
HXB042H	Motor operator with auto-reset (K) = with key
HXB065H	Interlocking wire type kit (Kit= 2units+cable)
HXB066H	Mechanical interlock (1 front cover)
HXB068H	Electrical interlock for Motor operator
HXB069H	Electrical interlock for Motor operator
HXB070H	Cable for Mechanical interlock
HXB071H	Cable for Mechanical interlock
HXS030H	Direct rotary handle
HXS031H	Rotary handle on door
HXS032H	Direct rotary handle with interlocking
HXS034H	Rotary handle on door S0 for P160
HXS066H	Mechanical interlock (1 front cover)
HXS120H	AX/AL Energy (ACP only)
HXS121H	AX/AL E-nergy
HXS122H	AX/AL E-nergy low level

EU DECLARATION OF CONFORMITY

No. 26.2177.02.26

Type References:

HXS165H	Link interlock kit
HXS166H	Link interlock kit
HXS888H	Key Kit for Rotary handle
HXS900H	Handle size 0 IP55
HXS901H	Handle size 1 IP55
HXS902H	Handle size 1 IP65
HXS912H	Shaft 8x8mm 200mm (1H100820)
HXS913H	Shaft 8x10mm 320mm (1H100832)
HXS915H	Shaft 8x10mm 500mm (1H100850)
HXS916H	Shaft 8x10mm 500mm (1H100550)
HXS920H	Shaft guide for handle size 1&2 (unit)(1H290000)
HXS999H	Key kit (stand alone)
HXT030H	Direct rotary handle
HXT031H	Rotary handle on door
HXT032H	Direct rotary handle with interlocking
HXT034H	Rotary handle on door S0 for P250
HXT040H	Motor operator with auto-reset (K) = with key
HXT041H	Motor operator with auto-reset (K) = with key
HXT042H	Motor operator with auto-reset (K) = with key
HXT043H	Motor operator without auto-reset (K) = with key
HXT044H	Motor Operator P250 230-240VAC without Auto-Reset
HXT045H	Motor Operator P250 200-220VAC/DC with Auto-Reset
HXT046H	Motor Operator P250 100-110VAC/DC without Auto-Reset
HXT047H	Motor Operator P250 200-220VAC/DC without Auto-Reset
HXT048H	Motor operator with auto-reset (K) = with key
HXT049H	Motor operator without auto-reset (K) = with key
HXT040HK	Motor Operator P250 24VDC with Auto-Reset + key
HXT041HK	Motor Operator P250 100-110VAC/DC with Auto-Reset + key
HXT042HK	Motor Operator P250 230-240VAC with Auto-Reset + key
HXT043HK	Motor Operator P250 24VDC without Auto-Reset + key
HXT044HK	Motor operator without auto-reset (K) = with key
HXT045HK	Motor operator with auto-reset (K) = with key
HXT046HK	Motor operator without auto-reset (K) = with key
HXT047HK	Motor operator without auto-reset (K) = with key
HXT048HK	Motor Operator P250 48VDC with Auto-Reset +key
HXT049HK	Mot. P250 48VDC w/o Auto-R. +key
HXT066H	Mechanical interlock (1 front cover)
HXT165H	Link interlock kit
HXT166H	Link interlock kit
HXT890H	Key lock kit for Draw-out kit P250
HXV030H	Rotary handle P250hbc, direct
HXV031H	Rotary handle P250hbc, on door
HXV032H	Rotary handle P250hbc, direct with door lock
HXW888H	Key Kit for Rotary handle
HYA005H	Cage terminal 1 wire Cu/Al (external)

EU DECLARATION OF CONFORMITY

No. 26.2177.02.26

Type References:

HYA006H	Cage terminal 1 wire Cu/Al (external)
HYA010H	Straight terminal extension
HYA011H	Spread terminal extension
HYA012H	Spread terminal extension
HYA013H	Extended connection x160 4P collar
HYA014H	Spreader x160 3P collar
HYA015H	Spreader x160 4P collar
HYA019H	Interphase barrier
HYA021H	Terminal cover for straight term.
HYA022H	Terminal cover for straight term.
HYA023H	Terminal cover for spread term.
HYA024H	Terminal cover for spread term.
HYA025H	Terminal cover for rear & plug-in con.
HYA026H	Terminal cover for rear & plug-in con.
HYA027H	Terminal cover for cage terminal
HYA028H	Terminal cover for cage terminal
HYA029H	Terminal cover for straight term.
HYA030H	Terminal cover for straight term.
HYA031H	Rear connexion x160 3P
HYA032H	Rear connexion x160 4P
HYA033H	Rail Din adaptor
HYA035H	Connecting kit for Auxiliaries (0.75mm ²)
HYA036H	Rail Din Raiser for modular product
HYA040H	Front product adaptor x160-x250 (nose 2x1")
HYA086H	Compact Lugs 16mm ² D:8.5
HYA087H	Compact Lugs 25mm ² D:8.5
HYA088H	Compact Lugs 35mm ² D:8.5
HYA089H	Compact Lugs 50mm ² D:8.5
HYA090H	Compact Lugs 70mm ² D:8.5
HYA091H	Compact Lugs 95mm ² D:8.5
HYA131H	Rear connexion x160 3P for 63A to 160A
HYA132H	Rear connexion x160 4P for 63A to 160A
HYA200H	PM Base Plug In x160 3P
HYA250H	PM Auxiliary Circuit Terminal x160 - Panel side
HYA350H	PM Auxiliary circuit terminal -Body side- x160
HYB001H	Cage terminal 1 wire Cu/Al (integrated)
HYB002H	Cage terminal 1 wire Cu/Al (integrated)
HYB005H	Cage terminal 1 wire Cu/Al (external)
HYB006H	Cage terminal 1 wire Cu/Al (external)
HYB010H	Straight extension (x/P250-P250) 4P
HYB011H	Spreader (x/P250-P250) 3P
HYB012H	Spreader (x250-P250) 4P
HYB019H	Interphase barrier
HYB021H	Terminal cover for straight term.

EU DECLARATION OF CONFORMITY

No. 26.2177.02.26

Type References:

HYB022H	Terminal cover for straight term.
HYB023H	Terminal cover for spread term.
HYB024H	Terminal cover for spread term.
HYB025H	Terminal cover for rear & plug-in con.
HYB026H	Terminal cover for rear & plug-in con.
HYB027H	Terminal cover for cage terminal
HYB028H	Terminal cover for cage terminal
HYB031H	Rear connection (x/P250-P250) - 3P
HYB032H	Rear connection (x/P250-P250) - 4P
HYB033H	Rail Din adaptor
HYB092H	Compact Lugs 120mm ² D:8.5
HYB094H	Compact Lugs 150mm ² D:8.5
HYB200H	Plug-in Base x250 3P
HYB201H	Plug-in Base x250 4P
HYB250H	Auxiliary circuit terminal - Base side
HYB350H	Auxiliary circuit terminal - MCCB side
HYC250H	Auxiliary circuit terminal - Base side
HYC252H	Auxiliary circuit terminal - MCCB side
HYC253H	Auxiliary circuit terminal - MCCB side
HYC255H	Position Switch for Draw-out
HYC321H	Terminal Cover for Plug-in base
HYC322H	Terminal Cover for Plug-in base
HYC352H	Auxiliary circuit terminal - MCCB side
HYC353H	Auxiliary circuit terminal - MCCB side
HYS001H	Cage terminal 1 wire Cu/Al (integrated)
HYS002H	Cage terminal 1 wire Cu/Al (integrated)
HYS005H	Cage terminal 1 wire Cu/Al (external)
HYS006H	Cage terminal 1 wire Cu/Al (external)
HYS010H	Straight terminal extension
HYS011H	Spread terminal extension
HYS012H	Spread terminal extension
HYS013H	Straight terminal extension
HYS014H	Spread terminal extension
HYS015H	Spread terminal extension
HYS019H	Interphase barrier
HYS021H	Terminal cover for straight term.
HYS022H	Terminal cover for straight term.
HYS023H	Terminal cover for spread term.
HYS024H	Terminal cover for spread term.
HYS025H	Terminal cover for rear & plug-in con.
HYS026H	Terminal cover for rear & plug-in con.
HYS031H	Rear connection
HYS032H	Rear connection
HYS033H	Rail Din adaptor
HYS050H	Earth plate for Straight terminal cover

EU DECLARATION OF CONFORMITY

No. 26.2177.02.26

Type References:

HYS051H	Earth plate for Straight terminal cover
HYS052H	Earth plate for Spread terminal cover
HYS053H	Earth plate for Spread terminal cover
HYS055H	Cage terminal 6 wires Cu/Al (external)
HYS056H	Cage terminal 6 wires Cu/Al (external)
HYS060H	KIT TERMINAL COVER 3P (HYS025H + HYS021H + HYS050H)
HYS061H	KIT TERMINAL COVER 4P (HYS026H + HYS022H + HYS051H)
HYS105H	Cage terminal 1 wire Cu/Al (external)
HYS106H	Cage terminal 1 wire Cu/Al (external)
HYS131H	Rear connection
HYS132H	Rear connection
HYS155H	Cage terminal 6 wires Cu/Al (external)
HYS156H	Cage terminal 6 wires Cu/Al (external)
HYS200H	Plug-in Sockel P160 3P
HYS201H	Plug-in Sockel P160 4P
HYS256H	Safety trip
HYS257H	Safety trip h3+ P160 for QuadroSX/Unimes H Combiway
HYS300H	Plug-in adaptor for P160 3P (63-160A)
HYS301H	Plug-in adaptor for P160 4P (63-160A)
HYS310H	Plug-in adaptor for P160 3P (16-50A)
HYS311H	Plug-in adaptor for P160 4P (16-50A)
HYS321H	Terminal Cover for Plug-in base
HYS322H	Terminal Cover for Plug-in base
HYS328H	L connection
HYT001H	Cage terminal 1 wire Cu/Al (integrated)
HYT002H	Cage terminal 1 wire Cu/Al (integrated)
HYT005H	Cage terminal 1 wire Cu/Al (integrated)
HYT006H	Cage terminal 1 wire Cu/Al (integrated)
HYT007H	Cage terminal 2 or 4 wires Cu/Al (external)
HYT008H	Cage terminal 2 or 4 wires Cu/Al (external)
HYT019H	Interphase barrier
HYT021H	Terminal cover for straight term.
HYT022H	Terminal cover for straight term.
HYT023H	Terminal cover for spread term.
HYT024H	Terminal cover for spread term.
HYT025H	Terminal cover for rear & plug-in con.
HYT026H	Terminal cover for rear & plug-in con.
HYT033H	Rail Din adaptor
HYT050H	Earth plate for Straight terminal cover
HYT051H	Earth plate for Straight terminal cover
HYT052H	Earth plate for Spread terminal cover
HYT053H	Earth plate for Spread terminal cover
HYT060H	KIT TERMINAL COVER 3P (HYT025H + HYT021H + HYT050H)
HYT061H	KIT TERMINAL COVER 4P (HYT026H + HYT022H + HYT051H)

EU DECLARATION OF CONFORMITY

No. 26.2177.02.26

Type References:

HYT065H	Cage terminal 6 wires Cu/Al (external)
HYT066H	Cage terminal 6 wires Cu/Al (external)
HYT200H	Plug-in base
HYT201H	Plug-in base
HYT257H	Safety trip P250 QuadroSX/Combiway
HYT300H	Plug-in kit for MCCB
HYT301H	Plug-in kit for MCCB
HYT328H	L connection
HYT330H	Draw-out base
HYT331H	Draw-out base
HYT332H	Draw-out kit for MCCB
HYT333H	Draw-out kit for MCCB
HYV021H	Terminal cover for straight term.
HYV022H	Terminal cover for straight term.
HYV023H	Terminal cover for spread term.
HYV024H	Terminal cover for spread term.
HYV025H	Terminal cover for rear & plug-in con.
HYV026H	Terminal cover for rear & plug-in con.
HYV256H	Safety trip
HZC016H	Handle size 0 IP55 (1H711513)
HZC019	Extern.lock.kit Ronis
HZC020	Shaft guide for handle size 0 (unit)
HZF101	Shaft 5x5mm 200mm
HZF103	Shaft 5x5mm 320mm
HXW030H	Direct rotary handle for x630/P630
HXW032H	Direct rotary handle for x630/P630, with door lock
HXW031H	Rotary handle on door for x630/P630
HXW033H	Extended handle
HXW036H	Rotary handle on door for x630/P630 (red color)
HXW901H	Handle size 2 IP55 (1H212518)
HXW903H	Handle size 2 IP55 (red color)
HXW912H	Shaft 14x14mm 200mm (1H100820)
HXW913H	Shaft 14x14mm 320mm (1H100832)
HXW915H	Shaft 14x14mm 500mm (1H100850)
HXW920H	Shaft guide for handle size 1&2 (unit) (1H1290000)
HXW890H	Key Kit for Draw out
HXW040H	Motor operator with auto-reset (K) = with key
HXW041H	Motor operator with auto-reset (K) = with key
HXW042H	Motor operator with auto-reset (K) = with key
HXW043H	Motor operator without auto-reset (K) = with key
HXW046H	Motor operator without auto-reset (K) = with key
HXW044H	Motor operator without auto-reset (K) = with key
HXW040HK	Motor Operator x630/P630 with Auto-Reset + key
HXW041HK	Motor Operator x630/P630 with Auto-Reset + key
HXW042HK	Motor Operator x630/P630 with Auto-Reset + key

EU DECLARATION OF CONFORMITY

No. 26.2177.02.26

Type References:

HXW043HK	Motor Operator x630/P630 without Auto-Reset + key
HXW044HK	Motor Operator x630/P630 without Auto-Reset + key
HXW046HK	Motor Operator x630/P630 without Auto-Reset + key
HXW066H	Mechanical interlock (1 front cover)
HXW165H	Link interlock kit
HXW166H	Link interlock kit
HXW167H	Link interlock kit for Rotary
HXW168H	Link interlock kit for Rotary
HXD068H	Electrical interlock for Motor type A (h400-h630-x630-P630-h800-h1000)
HYW001H	Cage terminal 1 wire Cu/Al (integrated)
HYW002H	Cage terminal 1 wire Cu/Al (integrated)
HYW007H	Cage terminal 2 or 4 wires Cu/Al (external)
HYW008H	Cage terminal 2 or 4 wires Cu/Al (external)
HYW010H	Straight terminal extension
HYW013H	Straight terminal extension
HYW011H	Spread terminal extension
HYW014H	Spread terminal extension
HYW012H	Spread terminal extension
HYW015H	Spread terminal extension
HYW019H	Interphase barrier
HYW021H	Terminal cover for straight term.
HYW022H	Terminal cover for straight term.
HYW023H	Terminal cover for Spread terminal extension x630/P630 3P
HYW024H	Terminal cover for Spread terminal extension x630/P630 4P
HYW025H	Terminal cover for Rear & Plug-in connection x630/P630 3P
HYW026H	Terminal cover for Rear & Plug-in connection x630/P630 4P
HYW050H	Earth plate for Straight terminal cover
HYW051H	Earth plate for Straight terminal cover
HYW052H	Earth plate for Spread terminal cover
HYW053H	Earth plate for Spread terminal cover
HYW060H	KIT TERMINAL COVER 3P (HYW025H + HYW021H + HYW050H)
HYW061H	KIT TERMINAL COVER 4P (HYW026H + HYW022H + HYW051H)
HYW200H	Plug-in base
HYW201H	Plug-in base
HYW256H	Safety trip
HYW257H	Déclencheur de sécurité h3 x630/h3+ P630 for QuadroSX/Unimes H Combiway
HYW300H	Plug-in kit for MCCB
HYW301H	Plug-in kit for MCCB
HYW328H	L connection
HYW330H	Draw-out base
HYW331H	Draw-out base
HYW332H	Draw-out kit for MCCB
HYW333H	Draw-out kit for MCCB
HYD031H	Rear connection
HYD033H	Rear connection

EU DECLARATION OF CONFORMITY

No. 26.2177.02.26

Type References:

HYD032H	Rear connection
HYD034H	Rear connection
HYD321H	Terminal Cover for Plug-in base
HYD322H	Terminal Cover for Plug-in base
HTC100H	Side support h3+ for wire
HTC130H	OAC/PTA adaptator for h3+ length 1,20 m
HTC140H	Adaptador CIP 24V DC h3+ Energy 1,2m
HTC150H	Adaptador ZSI h3+ Energy 1,2m
HTC330H	Adaptador CIP h3+ Energy 0,5m
HTC340H	Adaptador CIP h3+ Energy 1,5m
HTC350H	CIP - Adaptor for h3+ length 3 m
HTC360H	CIP - Adaptor for h3+ length 5 m
HTC370H	CIP - Adaptor for h3+ length 10 m
HTC160H	NSP cable adaptor length 1,20 m
HTD010H	Energy OLED display
HTG467H	Résistance term. MODBUS RTU 120 Ohm RJ45
HYW350H	Auxiliary connectors
SMC120R	Résistance term. MODBUS RTU 120 Ohm

EU DECLARATION OF CONFORMITY

NO. 26.2177.02.26

Evidence(s)

Documents listed below have been used in order to establish the conformity to the essential requirements of the relevant directives:

Conformity report / evidence:	KRC-15299c / KRC 15332 / KRC-15357 / COD 20106050 / COD 1790621 / COD 19101584 KRC 5917-5 / KRC-15393 / KRC 5917-6 / COD 20106050 / COD 1790621 / 20-200LAB-BLK ROHS DECLARATION 22032 DIV ROHS DECLARATION N° 20220719Y DMS 039873 NL 43306-A1 / NL-45566 / NL_78002 / NL_74492 / NL_78783 / NL_78003 / NL_78784 / NL_74493 / NL_79254 / NL_57069 / NL_79255 accessoires h3+P1-P2-P4 and h TERASAKI for EU decl_28022022
Product documentation:	See Hager website
Comments:	None

Signature (technical design)

Name of signatory

Olivier PRADOURA

Function of signatory

Product Portfolio Director

Place and date of issue

Obernai, 15th June 2026

Signature

