



VE218F

### Enclosure, vector, IP5x

#### Technical Features

##### Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

##### Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

##### Electric current

Rated current	63 A
---------------	------

##### Equipment

Number of rails	2
Number of rows	2
Number of section in width	1
With lock	No
Has neutral terminal block	No

##### Capacity

Number of modules	36
-------------------	----

##### Functions

With conduit inlets	Yes
---------------------	-----

##### Dimensions

Height	452 mm
Width	418 mm
Depth	151 mm

##### Cover, door

Number of cabinet doors	1
Number of locks	0

##### Dimensions

Number of width units	18
-----------------------	----

##### Cover, door

Door/cover is transparent	No
---------------------------	----

##### Connection

Number of conduit inlets	15
--------------------------	----

##### Connectivity

Mounting type	Screw mounting
---------------	----------------

##### Materials

Material	Polystyrene (PS)
RAL code	7035
Colour	Light grey

##### Equipment

Has earthing terminal block	Yes
Has mounting plate	No

##### Materials

Ultraviolet-resistant	No
-----------------------	----

##### Safety

Protection class	Isolation class II
Impact resistance IK	IK08
Ingress Protection (IP) class	IP65

<b>Safety</b>	
Locking type	Snap on lock
	Without lock
Glow wire test	750 °C
<b>Sustainability</b>	
RoHS conform	Yes