



VE218AK

Enclosure, vector, IP65, 36 modules

Technical Features

Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Electric current

Rated current	63 A
---------------	------

Equipment

Number of rails	2
Number of rows	2
Number of section in width	1
With lock	No

Capacity

Number of modules	36
-------------------	----

Functions

With conduit inlets	Yes
---------------------	-----

Dimensions

Height	452 mm
Width	418 mm
Depth	151 mm

Cover, door

Number of cabinet doors	1
Number of locks	0

Dimensions

Number of width units	18
-----------------------	----

Cover, door

Door/cover is transparent	Yes
Cabinet door type	Single door

Connection

Number of conduit inlets	15
--------------------------	----

Materials

Material	Plastic
RAL code	7035
Colour	Light grey

Equipment

Has mounting plate	No
--------------------	----

Materials

Ultraviolet-resistant	No
-----------------------	----

Safety

Protection class	Isolation class II
Ingress Protection (IP) class	IP65
Locking type	Snap on lock Without lock
Glow wire test	750 °C
Protection class with door	IP65

Sustainability

RoHS conform

Yes