



VE218AK

Enclosure,vector,IP65,36modules

### Technical Features

#### Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

#### Installation, mounting

Suitable for outdoor usage	No
----------------------------	----

Mounting on	Surface mounting
-------------	------------------

#### Electric current

Rated current	63 A
---------------	------

#### Equipment

Number of rails	2
-----------------	---

Number of rows	2
----------------	---

Number of section in width	1
----------------------------	---

With lock	No
-----------	----

#### Capacity

Number of modules	36
-------------------	----

#### Functions

With conduit inlets	Yes
---------------------	-----

#### Dimensions

Height	452 mm
--------	--------

Width	418 mm
-------	--------

Depth	151 mm
-------	--------

#### Cover, door

Number of cabinet doors	1
-------------------------	---

Number of locks	0
-----------------	---

#### Dimensions

Number of width units	18
-----------------------	----

#### Cover, door

Door/cover is transparent	Yes
---------------------------	-----

#### Connection

Number of conduit inlets	15
--------------------------	----

#### Materials

Material	Plastic
----------	---------

RAL code	7035
----------	------

Colour	Light grey
--------	------------

#### Equipment

Has mounting plate	No
--------------------	----

#### Materials

Ultraviolet-resistant	No
-----------------------	----

#### Safety

Protection class	Isolation class II
------------------	--------------------

Ingress Protection (IP) class	IP65
-------------------------------	------

Locking type	Snap on lock Without lock
--------------	------------------------------

Glow wire test	750 °C
----------------	--------

#### Sustainability

RoHS conform	Yes
--------------	-----