



936752568



Ser push-button, 2 NO cont com inp term, Integro - Design Flow/Pure, chr m, lacq

#### Technical Features

##### Electric current

Switching current	10 A
Momentary contact current	10 A

##### Voltage

Rated voltage	250 V
---------------	-------

##### Architecture

Control/operation element	Double push button
Number of poles	2

##### Materials

Colour	Chrome
Surface finish	Matt
Material	Thermoplastic
Treatment	Chrome plated Varnished
Transparent	No

##### Dimensions

Height	55.50 mm
Width	55.50 mm
Depth	25 mm
Built-in depth	10 mm
Built-in depth flush-mounted boxes	13 mm

##### Controls and indicators

Number of buttons	2
Type of push button	Series push button
With feedback signal contact	No

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Accessories

Has labelling field	No
---------------------	----

##### Texts

Imprint	Without imprint
Terminal	Common input terminal
Type of connection	With screw terminals

##### Suitable for

integro	
---------	--

##### Sustainability

RoHS conform	Yes
--------------	-----