



dr48s4

### Din rail board, 3 row 48M, non-transparent door, surface, EU

#### Technical Features

##### Voltage

Nominal voltage	415 - 415 V
-----------------	-------------

##### Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

##### Power

Maximum power loss per cabinet at $\Delta T=20K$	32.02 W
--------------------------------------------------	---------

##### Equipment

Number of rails	3
Number of rows	3
With lock	No
Has neutral terminal block	Yes

##### Capacity

Number of modules	48
Number of half modules terminals per rail	32

##### Functions

Has protection main switch	No
With conduit inlets	Yes

##### Dimensions

Height	624 mm
Width	405 mm
Depth	115 mm
Built-in height	620 mm
Built-in width	400 mm

##### Cover, door

Number of cabinet doors	1
-------------------------	---

##### Dimensions

Built-in depth	110 mm
----------------	--------

##### Cover, door

Number of locks	0
-----------------	---

##### Dimensions

Number of width units	16
-----------------------	----

##### Cover, door

Door/cover is transparent	No
---------------------------	----

##### Connection

Number of conduit inlets	17
--------------------------	----

##### Connectivity

Mounting type	Screw mounting
---------------	----------------

##### Materials

Material	Steel
RAL code	9010
Colour	Grey white

##### Equipment

Has earthing terminal block	No
Has mounting plate	No

**Safety**

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP40
Locking type	Without lock
Glow wire test	960 °C

**Sustainability**

RoHS conform	Yes
--------------	-----