



VF218PF3

**Small distributor,golf,flush,2row,36M,IP40,MS-terminal,PE,white door**

**Technical Features**

**Voltage**

Nominal voltage 400 - 400 V

**Installation, mounting**

Suitable for outdoor usage No

Mounting on Flush mounting

**Electric current**

Rated current 63 A

**Equipment**

Number of rails 2

Number of rows 2

Number of section in width 1

With lock No

Has neutral terminal block No

**Capacity**

Number of modules 36

**Functions**

With conduit inlets Yes

**Dimensions**

Height 418 mm

Width 460 mm

Depth 97.50 mm

Built-in height 382 mm

Built-in width 426 mm

**Cover, door**

Number of cabinet doors 1

**Dimensions**

Built-in depth 72 mm

**Cover, door**

Number of locks 0

**Dimensions**

Number of width units 18

**Cover, door**

Door/cover is transparent No

Cabinet door type Single door

**Materials**

Material Plastic

RAL code 9010

Colour Pure white

**Equipment**

Has earthing terminal block Yes

Has mounting plate No

**Materials**

Ultraviolet-resistant No

**Safety**

Protection class Isolation class II

Ingress Protection (IP) class IP40

---

**Safety**

Locking type	Snap on lock Without lock
Glow wire test	650 °C
Protection class with door	IP40

**Sustainability**

RoHS conform	Yes
--------------	-----