



TRC301B



### Radio Window contact battery-powered, KNX, Quicklink, White

#### Technical Features

##### Architecture

Bus system	Radio frequent
------------	----------------

##### Settings

Supported configuration mode	ETS easy quicklink
------------------------------	--------------------------

##### Electric current

Number of entry circuits	2
--------------------------	---

##### Equipment

External signal voltage necessary	No
-----------------------------------	----

##### Connectivity

With bus system KNX radio	Yes
---------------------------	-----

##### Equipment

Radio frequency bidirectional	No
With battery	Yes
With HVAC control	No

##### Frequency

Frequency transmission	868 - 868 MHz
------------------------	---------------

##### Installation, mounting

Mounting on	Surface mounting
-------------	------------------

##### Lighting

LED controlling	Yes
-----------------	-----

##### Materials

Colour	White
RAL code	9010

##### Safety

Ingress Protection (IP) class	IP31
-------------------------------	------

##### Use conditions

Operating temperature	0 - 50 °C
-----------------------	-----------

##### Voltage

Input voltage	3 - 3 V
Type voltage supply	DC

##### Dimensions

Height	26 mm
Depth	30 mm

##### Texts

Installation mode	With adapters for magnet height compensation
Type of connection	With additional screw terminals for wired reed contacts