



TRC301B



Radio Window contact battery-powered, KNX, Quicklink, White

Technical Features

Architecture

Bus system Radio frequent

Settings

Supported configuration mode ETS
easy
quicklink

Electric current

Number of entry circuits 2

Equipment

External signal voltage necessary No

Connectivity

With bus system KNX radio Yes

Equipment

Radio frequency bidirectional No

With battery Yes

With HVAC control No

Frequency

Frequency transmission 868 - 868 MHz

Installation, mounting

Mounting on Surface mounting

Lighting

LED controlling Yes

Materials

Colour White

RAL code 9010

Safety

Ingress Protection (IP) class IP31

Use conditions

Operating temperature 0 - 50 °C

Voltage

Input voltage 3 - 3 V

Type voltage supply DC

Dimensions

Height 26 mm

Depth 30 mm

Texts

Installation mode With adapters for magnet height compensation

Type of connection With additional screw terminals for wired reed contacts