



TRC301B



**Radio Window contact battery-powered, KNX, Quicklink, White**

**Technical Features**

**Architecture**

Bus system	Radio frequent
------------	----------------

**Settings**

Supported configuration mode	ETS easy quicklink
------------------------------	--------------------------

**Electric current**

Number of entry circuits	2
--------------------------	---

**Equipment**

External signal voltage necessary	No
-----------------------------------	----

**Connectivity**

With bus system KNX radio	Yes
---------------------------	-----

**Equipment**

Radio frequency bidirectional	No
With battery	Yes
With HVAC control	No

**Frequency**

Frequency transmission	868 - 868 MHz
------------------------	---------------

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Lighting**

LED controlling	Yes
-----------------	-----

**Materials**

Colour	White
RAL code	9010

**Safety**

Ingress Protection (IP) class	IP31
-------------------------------	------

**Use conditions**

Operating temperature	0 - 50 °C
-----------------------	-----------

**Voltage**

Input voltage	3 - 3 V
Type voltage supply	DC

**Dimensions**

Height	26 mm
Depth	30 mm

**Texts**

Installation mode	With adapters for magnet height compensation
Type of connection	With additional screw terminals for wired reed contacts