



VML_SIZE_7

14 Way Hi Integrity 100A Switch 2*100A 30mA RCCB Type 2 SPD RKO

Technical Features

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Architecture

Number of poles	2
-----------------	---

Functions

Has protection main switch	Yes
Overvoltage protection	Yes

Capacity

Number of modules	14
-------------------	----

Electric current

Rated current	100 A
---------------	-------

Dimensions

Depth	100 mm
Height	246 mm
Width	478 mm
Thickness of sidewall	0.90 mm

Cover, door

Interlockable	No
Door/cover is transparent	No

Materials

RAL code	9010
Colour	Pure white
Material	Steel

Installation, mounting

Suitable for outdoor usage	No
----------------------------	----

Connection

Number of accessible phases	1
-----------------------------	---

Scope of delivery

Number of RCCB in enclosure	2
-----------------------------	---

Equipment

Number of rows	1
Number of rails	1
Extension possible	No

Safety

Impact resistance IK	IK05
Ingress Protection (IP) class	IP2XC