



WMGSDP2B

## 20A 1 Way Double Pole Switch Black

### Technical Features

#### Electric current

Switching current	20 A
-------------------	------

#### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

#### Voltage

Rated voltage	250 V
---------------	-------

#### Materials

Colour	Black
Surface finish	Glossy
Material	Urea formaldehyde
Treatment	Untreated

#### Identification

Assembly arrangement	Basic element with central cover plate
----------------------	--

#### Connectivity

Mounting type	Snap-on mounting
---------------	------------------

#### Controls and indicators

Number of buttons	1
-------------------	---

#### Dimensions

Dimensions	59 x 25 mm
Built-in depth	13.10 mm

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Architecture

Control/operation element	Single rocker
---------------------------	---------------

#### Electric current

Rated current	20 A
---------------	------

#### Texts

Lighting	Without lighting (cannot be illuminated)
Switch mode	2-pole

#### Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes