



WXPPS12B

IP66 10A 1 Gang Press Bell Switch

Technical Features

Electric current

Momentary contact current 10 A

Voltage

Rated voltage 250 V

Architecture

Number of poles 2

Materials

Colour Light grey

Surface finish Matt

Material Polycarbonate (PC)

Treatment Untreated

Transparent No

Dimensions

Height 90 mm

Width 90 mm

Depth 50 mm

Installation, mounting

Mounting on Surface mounting

Controls and indicators

Number of buttons 1

Type of push button Single push button

With feedback signal contact No

Connectivity

Type of connection Screw terminal

Safety

Ingress Protection (IP) class IP66

Accessories

Has labelling field No

Texts

Imprint Without imprint

Sustainability

REACH-SVHC free Yes

RoHS conform Yes