



TXA112



**Power supply 30V DC 640 mA**

**Technical Features**

**Capacity**

Number of modules 4

**Electric current**

Output current 640 mA

**Connectivity**

With bus system KNX radio No

**Voltage**

Operating voltage 230 - 230 V

Output voltage 28 - 32 V

**Connection**

Cross-section flexible conductor 0.75 - 2.5 mm<sup>2</sup>

Cross-section rigid conductor 0.75 - 2.5 mm<sup>2</sup>

**Use conditions**

Operating temperature -5 - 45 °C

**Connectivity**

Type of connection quickconnect

**Frequency**

Frequency 50 - 60 Hz

**Texts**

Fuse With electronic short-circuit and overload protection

Junction Protected earth conductor must be connected

Type of connection With quickconnect plug-in terminals

**Power supply**

Supply voltage 230 V AC

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes