



TXA112



### Power supply 30V DC 640 mA

#### Technical Features

##### Capacity

Number of modules 4

##### Electric current

Output current 640 mA

##### Connectivity

With bus system KNX radio No

##### Voltage

Operating voltage 230 - 230 V

Output voltage 28 - 32 V

##### Connection

Cross-section flexible conductor 0.75 - 2.5 mm<sup>2</sup>

Cross-section rigid conductor 0.75 - 2.5 mm<sup>2</sup>

##### Use conditions

Operating temperature -5 - 45 °C

##### Connectivity

Type of connection quickconnect

##### Frequency

Frequency 50 - 60 Hz

##### Texts

Fuse With electronic short-circuit and overload protection

Junction Protected earth conductor must be connected

Type of connection With quickconnect plug-in terminals

##### Power supply

Supply voltage 230 V AC

##### Dimensions

Number of width units 4

##### Sustainability

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes