



TXA114



**Power supply 1x 30V DC + 1x 24V DC**

**Technical Features**

**Capacity**

Number of modules	4
-------------------	---

**Connectivity**

With bus system KNX radio	No
---------------------------	----

**Voltage**

Operating voltage	230 - 230 V
-------------------	-------------

Output voltage	28 - 32 V
----------------	-----------

**Connection**

Cross-section flexible conductor	0.75 - 2.5 mm <sup>2</sup>
----------------------------------	----------------------------

Cross-section rigid conductor	0.75 - 2.5 mm <sup>2</sup>
-------------------------------	----------------------------

**Use conditions**

Operating temperature	-5 - 45 °C
-----------------------	------------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Texts**

Fuse	With electronic short-circuit and overload protection
------	---

Junction	Protected earth conductor must be connected
----------	---

Type of connection	With quickconnect plug-in terminals
--------------------	-------------------------------------

**Power supply**

Supply voltage	230 V AC
----------------	----------

**Dimensions**

Number of width units	4
-----------------------	---

**Sustainability**

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----