



SPK700

Surge protection IT for satellite TV

Technical Features

Installation, mounting

Mounting on	DIN rail
Nominal tightening torque	1 - 1 Nm

Standards

Requirement class IEC 61643	C1
	C2
	C3
	D1
	B2

Voltage

Rated operational voltage $U_e$	14 - 18 V
Continuous operating voltage $U_c$ according to IEC 61643-1	20 V
Voltage protection level $U_p$ according to IEC 61643-1	0.50 kV

Electric current

Nominal discharge current $I_n$ 8 - 20 $\mu$ s C2 IEC 61643	2.50 kA
Max. discharge ( $I_{max}$ ) L-N(PEN)/ N-PE	2.5 kA

Dimensions

Height	31.50 mm
Width	144.90 mm
Depth	71.50 mm

Use conditions

Operating temperature	-25 - 55 °C
-----------------------	-------------

Equipment

With remote signalling contact	No
--------------------------------	----

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes