



SPK700

Surge protection IT for satellite TV

Technical Features

Installation, mounting

Mounting on	DIN rail
Nominal tightening torque	1 - 1 Nm

Standards

Requirement class IEC 61643	C1 C2 C3 D1 B2
-----------------------------	----------------------------

Voltage

Rated operational voltage U_e	14 - 18 V
Continuous operating voltage U_c according to IEC 61643-1	20 V
Voltage protection level U_p according to IEC 61643-1	0.50 kV

Electric current

Nominal discharge current I_n 8 - 20 μ s C2 IEC 61643	2.50 kA
Max. discharge (I_{max}) L-N(PEN)/ N-PE	2.5 kA

Dimensions

Height	31.50 mm
Width	144.90 mm
Depth	71.50 mm

Use conditions

Operating temperature	-25 - 55 °C
-----------------------	-------------

Equipment

With remote signalling contact	No
--------------------------------	----

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes