Product Datasheet
JK212BDFG



JK212BDFG

JK212 80 Module Side DIN Box Glazed

Technical Features

Installation, mounting	
Suitable for outdoor usage	No
Mounting on	Surface mounting
Electric current	
Rated current IN	250 A
Equipment	
Number of rows	5
With lock	Yes
Has neutral terminal block	Yes
Capacity	
Number of modules	80
Dimensions	
Height	1100 mm
Width	465 mm
Depth	165.50 mm
Cover, door	
Number of cabinet doors	1
Dimensions	
Number of width units	80
Cover, door	
Door/cover is transparent	Yes
Materials	
Material	Steel
RAL code	7035
Colour	Light grey
Equipment	
Has earthing terminal block	Yes
Safety	
Protection class	Isolation class III
Impact resistance IK	IK05
Ingress Protection (IP) class	IP3X
Locking type	Key lock Quarter turn lock
Sustainability	
RoHS conform	Yes