



SBN325

3-pole, 25A Modular Switch

Technical Features

Architecture

Number of poles	3
Neutral position	Without neutral
Type of pole	3P

Electric current

Rated current	25 A
Acceptable current rating AC21 category A	25 A
Acceptable current rating AC21 category B	25 A
Acceptable current rating AC22 category A	25 A
Acceptable current rating AC22 category B	25 A
Rated short-circuit making capacity Icm under 415 V AC according to IEC 60947-3	0.52 kA
Rated short-time withstand current Icw 1s IEC 60947	0.37 kA
Rated conditional short-circuit current Inc with fuse according to IEC/EN 3000A/80A gG parallel 32A gG 60669-2-4	

Installation, mounting

Nominal tightening torque	1.80 - 1.80 Nm
---------------------------	----------------

Voltage

Rated operational voltage Ue	400 - 400 V
Type voltage supply	AC
Rated insulation voltage Ui	440 V

Installation, mounting

Type of bottom connection for modular devices	Screw terminal
---	----------------

Voltage

Rated impulse withstand voltage Uimp	4000 V
--------------------------------------	--------

Capacity

Number of modules	2
-------------------	---

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Dimensions

Height	83 mm
Width	35 mm
Depth	68 mm
Dimensions	83 x 35 mm

Equipment

Number of NO contacts	3
Number of NC contacts	0

Use conditions

Operating temperature	-20 - 70 °C
Storage/transport temperature	-40 - 80 °C

Connection

Cross-section flexible conductor	1.5 - 10 mm ²
Cross-section rigid conductor	1.5 - 16 mm ²

Endurance

Number of mechanical operations	200000
Electrical durability at nominal load in AC21 in operating cycles	25000
Electrical durability at nominal load in AC22 in operating cycles	25000

Power

Total power loss under IN	2.70 W
Power loss per pole at In	0.90 W

Connectivity

Down connection alignment for modular devices	Shifted terminal
Top connection alignment for modular devices	Shifted terminal

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes