



ESC443

**Contactor 40A, 3NO+1NC, 230V~50Hz**

**Technical Features**

**Connection**

Type of contacts	3NO+1NC
------------------	---------

**Electric current**

Rated current	40 A
---------------	------

**Capacity**

Number of modules	3
-------------------	---

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Voltage**

Rated impulse withstand voltage Uimp	4000 V
Rated insulation voltage Ui	440 V
Rated operational voltage Ue	400 - 400 V
Command voltage AC	230 - 230 V
Command voltage DC	0 - 0 V

**Use conditions**

Operating temperature	-10 - 50 °C
-----------------------	-------------

**Use**

Category of use	AC-7a/AC-7b
-----------------	-------------

**Use conditions**

Storage/transport temperature	-40 - 80 °C
-------------------------------	-------------

**Endurance**

Number of mechanical operations	100000
Electric endurance in number of cycles	30000

**Power**

Total power loss under IN	11.80 W
Inrush power absorbed	62.50 VA

**Dimensions**

Height	85 mm
Width	54 mm
Depth	60 mm

**Connection**

Number of contacts	4
--------------------	---

**Equipment**

Number of NO contacts	3
Number of NC contacts	1
With switch for manual switch	No

**Connection**

Cross-section flexible conductor	1.5 - 16 mm <sup>2</sup>
Cross-section rigid conductor	1.5 - 25 mm <sup>2</sup>

**Architecture**

Number of poles	4
-----------------	---

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes