



VML\_SIZE\_7

### Design 10, 18 way 100A SW SPD

#### Technical Features

##### Installation, mounting

Mounting on	Surface mounting
-------------	------------------

##### Architecture

Number of poles	2
-----------------	---

##### Functions

Has protection main switch	Yes
Overvoltage protection	No

##### Capacity

Number of modules	38
-------------------	----

##### Electric current

Rated current	100 A
---------------	-------

##### Dimensions

Depth	100 mm
Height	246 mm
Width	478 mm
Thickness of sidewall	1 mm

##### Cover, door

Interlockable	No
Door/cover is transparent	No

##### Materials

RAL code	9010
Colour	Pure white
Material	Steel

##### Installation, mounting

Suitable for outdoor usage	No
----------------------------	----

##### Connection

Number of accessible phases	1
-----------------------------	---

##### Scope of delivery

Number of RCCB in enclosure	2
-----------------------------	---

##### Equipment

Number of rows	1
Number of rails	1
Extension possible	No

##### Safety

Impact resistance IK	IK05
Ingress Protection (IP) class	IP2XC