



SPK900

Surge protection RJ45 for Ethernet and VoIP networks

Technical Features

Installation, mounting

Mounting on	DIN rail
-------------	----------

Standards

Requirement class IEC 61643	C1 C2 C3 D1 B2
-----------------------------	----------------------------

Voltage

Continuous operating voltage $U_c$ according to IEC 61643-1	3.30 V
Voltage protection level $U_p$ according to IEC 61643-1	0.10 kV

Electric current

Nominal discharge current $I_n$ 8 - 20 $\mu s$ C2 IEC 61643	0.91 kA
Max. discharge ( $I_{max}$ ) L-N(PEN)/ N-PE	10 kA

Dimensions

Height	102 mm
Width	25 mm
Depth	63.5 mm

Use conditions

Operating temperature	-40 - 70 °C
-----------------------	-------------

Equipment

With remote signalling contact	No
--------------------------------	----

Sustainability

RoHS conform	Yes
--------------	-----