



SPK900

**Surge protection RJ45 for Ethernet and VoIP networks**

**Technical Features**

**Installation, mounting**

Mounting on DIN rail

**Standards**

Requirement class IEC 61643 C1  
C2  
C3  
D1  
B2

**Voltage**

Continuous operating voltage  $U_c$  according to IEC 61643-1 3.30 V  
Voltage protection level  $U_p$  according to IEC 61643-1 0.10 kV

**Electric current**

Nominal discharge current  $I_n$  8 - 20  $\mu$ s C2 IEC 61643 0.91 kA  
Max. discharge ( $I_{max}$ ) L-N(PEN)/ N-PE 10 kA

**Dimensions**

Height 102 mm  
Width 25 mm  
Depth 63.5 mm

**Use conditions**

Operating temperature -40 - 70 °C

**Equipment**

With remote signalling contact No

**Sustainability**

RoHS conform Yes