



TXA111



Power supply 30V DC 320 mA

Technical Features

Capacity

Number of modules 4

Electric current

Output current 320 mA

Connectivity

With bus system KNX radio No

Voltage

Operating voltage 230 - 230 V

Output voltage 28 - 32 V

Connection

Cross-section flexible conductor 0.75 - 2.5 mm²

Cross-section rigid conductor 0.75 - 2.5 mm²

Use conditions

Operating temperature -5 - 45 °C

Connectivity

Type of connection quickconnect

Frequency

Frequency 50 - 60 Hz

Texts

Fuse With electronic short-circuit and overload protection

Junction Protected earth conductor must be connected

Type of connection With quickconnect plug-in terminals

Power supply

Supply voltage 230 V AC

Sustainability

REACH-SVHC free Yes

RoHS conform Yes