



WFSS81PSW

13A 1 Gang Double Pole Switched Socket Polished Steel White Insert

Technical Features

Voltage

| | |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

Electric current

| | |
|---------------|------|
| Rated current | 13 A |
|---------------|------|

Materials

| | |
|----------------|-----------------|
| Colour | Silver |
| Surface finish | Glossy |
| Material | Stainless steel |

Dimensions

| | |
|--------|----------|
| Height | 86 mm |
| Width | 86 mm |
| Depth | 25.80 mm |

Installation, mounting

| | |
|-------------------------------|----------------|
| Mounting on | Flush mounting |
| Mounting-/Connection Position | Horizontal |

Connectivity

| | |
|--------------------|----------------|
| Type of connection | Screw terminal |
| Mounting type | Screw mounting |

Equipment

| | |
|-----------------------------------|------------------|
| Connector/plug type socket outlet | British Standard |
| Rotated central insert | No |
| With hinged lid | No |
| With round protective earth pin | No |
| With signal lamp | No |

Accessories

| | |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

Capacity

| | |
|-------------------|---|
| Number of modules | 0 |
|-------------------|---|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Functions

| | |
|---------------------------|----|
| With orientation lighting | No |
| With function lighting | No |

Identification

| | |
|--------------|----|
| With imprint | No |
|--------------|----|

Texts

| | |
|------------|-----------------------------|
| Cover | Full cover plate |
| Wiring | With earth connection |
| Protection | Enhanced contact protection |

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |