



WMCS3PIF

10A 3P Ceiling Switch Marked FAN

Technical Features

Installation, mounting

Mounting on Flush mounting

Voltage

Rated voltage 250 V

Materials

Colour White

Surface finish Glossy

Material Urea formaldehyde

Treatment Untreated

Identification

Assembly arrangement Basic element with full cover plate

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 0

Dimensions

Dimensions 86 x 86 mm

Built-in depth 23 mm

Electric current

Rated current 10 A

Texts

Lighting Without lighting (cannot be illuminated)

Switch mode 3-pole

Sustainability

REACH-SVHC free Yes

RoHS conform Yes