



16611949

**Rocker f.accessible const., guide f.mouth-held rod,lens,S.1/B.3/B.7,p.wh.m.plas.**

### Technical Features

#### Architecture

Control/operation element	Rocker with mouth rod guiding
---------------------------	-------------------------------

#### Materials

Colour	Polar white
RAL code	9010
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated

#### Dimensions

Height	54.90 mm
Width	55.70 mm
Depth	22 mm

#### Connectivity

Mounting type	Clamp mounting
---------------	----------------

#### Equipment

Monitoring window/light outlet	Yes
--------------------------------	-----

#### Accessories

Has labelling field	No
---------------------	----

#### Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK05

#### Texts

Imprint	Without imprint
Installation mode	Clamp fastening
Lighting	For lighting and monitoring circuit
Push button	Also for KNX applications: push-button, 1-gang, and group push-button, 1-gang
Rocker switch/rocker push-button	For rocker push-buttons For change-over/intermediate switch

#### Suitable for

S.x/B.x	
---------	--

#### Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes