



EMN001



IP20



Stair case time lag switch

Technical Features

Voltage

Rated operational voltage U _e	230 - 230 V
--	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Electric current

Rated current	16 A
---------------	------

Capacity

Number of modules	1
-------------------	---

Connectivity

Type of connection	Screw terminal Wire connection
--------------------	-----------------------------------

Installation, mounting

Mounting on	DIN rail
-------------	----------

Lighting

Max. load fluorescent lamp parallel compensated	1000 VA
Max. load fluorescent lamp	3600 VA

Use conditions

Operating temperature	-10 - 55 °C
-----------------------	-------------

Connection

Cross-section flexible conductor	1 - 6 mm ²
Cross-section rigid conductor	1.5 - 10 mm ²

Settings

Time delay	30 S - 10 Min
------------	---------------

Dimensions

Width	17.50 mm
Depth	64 mm

Power

230 V incandescent and halogen lamp	2300 W
-------------------------------------	--------

Texts

Junction	For 3 and 4-conductor circuit (automatic detection)
Switch mode	NO contact
Installation mode	For mounting on DIN rail
Type of connection	With screw terminals

Sustainability

Halogen free	Yes
RoHS conform	Yes