



JN204BG

250A 4 Way 125A Outgoers Glazed

Technical Features

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Electric current

Rated current	250 A
---------------	-------

Equipment

With lock	No
Has neutral terminal block	Yes

Dimensions

Height	950 mm
Width	710 mm
Depth	178.40 mm

Cover, door

Number of cabinet doors	1
Door/cover is transparent	Yes

Materials

Material	Steel
RAL code	7035 9001
Colour	Light grey

Equipment

Has earthing terminal block	Yes
-----------------------------	-----

Safety

Protection class	Isolation class III
Impact resistance IK	IK05
Ingress Protection (IP) class	IP30
Locking type	Key lock Quarter turn lock

Sustainability

RoHS conform	Yes
--------------	-----